



GreenSpace Accent, elbow

RS342B LED27S/830 PSU-E WB II WH

GreenSpace Accent Elbow - LED Module, system flux 2700 lm - 830 warm white - Power supply unit external (PSU) - Wide beam - Safety class II - White

Lighting is one of the key assets that can help retailers and building operators achieve their cost targets. Until now, many have been reluctant to switch from CDM to LED technology because the efficiency, initial investment, installation process, light level and/or quality of light of new LED solutions were not on par with their CDM existing solutions. This is no longer the case, thanks to GreenSpace Accent. Now, retailers and building operators can make the switch and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings compared to their existing CDM installation – all for a reasonable initial investment. And GreenSpace Accent's regular cut-out makes retrofit installation quick and easy. For food and fashion retailers, GreenSpace Accent elbow is also available with special light recipes to further enhance the store ambiance and to show the produce and goods on offer in the very best light: Fresh Food Champagne is the perfect LED solution for displaying fruit, vegetables, cheese, bread and pastries in a warm lighting ambiance; Fresh Food Meat creates the best light setting for meat enhancement in a cool natural ambiance; CrispWhite is the clear choice for fashion retailers to make colors appear rich and intense while keeping whites bright.

Product data

General Information		Cap base	- [-]
Number of light sources	1 [1 pc]	Light source replaceable	No
Lamp family code	LED27S [LED Module, system flux 2700 lm]	Number of gear units	1 unit
Beam angle of light source	120 °	Gear	-
Light source colour	830 warm white	Driver/power unit/transformer	PSU-E [Power supply unit external (PSU)]

GreenSpace Accent, elbow

Driver included	Yes
Optic type	WB [Wide beam]
Optical cover/lens type	ACC [Acrylic bowl/cover clear]
Luminaire light beam spread	36°
Control interface	-
Connection	Push-in connector and pull relief
Cable	-
Protection class IEC	Safety class II
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	NO [-]
CE mark	CE mark
ENEC mark	ENEC mark
UL mark	No
Warranty period	5 years
Constant light output	No
Number of products on MCB	34
RoHS mark	RoHS mark
Product Family Code	RS342B [GreenSpace Accent Elbow]

Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Inrush current	18.6 A
Inrush time	0.24 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Aluminium
Reflector material	Polycarbonate
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Polyamide
Optical cover/lens finish	Clear
Overall length	228 mm
Overall width	193 mm
Overall height	156 mm
Overall diameter	193 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux	2700 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	100 lm/W
Init. Corr. colour temperature	3000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.43, 0.40) SDCM<3
Initial input power	27 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	1 %
Median useful life L70B50	70000 h
Median useful life L80B50	50000 h
Median useful life L90B50	25000 h

Application Conditions


Ambient temperature range	+10 to +40 °C
Average ambient temperature	25 °C
Maximum dimming level	Not applicable
Suitable for random switching	No

Product Data

Full product code	871869625518600
Order product name	RS342B LED27S/830 PSU-E WB II WH
EAN/UPC – product	8718696255186
Order code	25518600
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910500456530
Net weight (piece)	1.600 kg


GreenSpace Accent, elbow

Dimensional drawing




GreenSpace Accent RS340B-RS343B


Photometric data



IFAS1_RS342B1xLED27S830WB



IFCC1_RS342B1xLED27S830WB



IFPC1_RS342B1xLED27S830WB

GreenSpace Accent, elbow

