



Maxos LED inserts for TTX400

4MX400 581 LED80S/840 PSD WB WH

Maxos LED Retrofit for TTX400 - 1 unit for TL-D 58 W - LED Module, system flux 8000 lm - 840 neutral white - Power supply unit with DALI interface - Wide beam - White

Customers in the industrial and retail sectors are looking for general lighting solutions with a justifiable payback, while meeting all relevant norms for supermarkets and industry applications. For a limited investment, Maxos LED inserts for TTX400 offer best-in-class energy savings while delivering high lux levels at the required color temperatures and glare factors. The minimalistic Maxos LED inserts for TTX400 comprise exchangeable mid-power LED boards to be mounted on a standard TTX400 trunking rail. A choice of wide, medium and double asymmetric beam lenses means flexibility in light distribution. Compared with a conventional fluorescent installation, this highly efficient LED solution offers full payback in less than three years. And the benefits keep coming: our upgradable LED engine platform makes Maxos LED inserts for TTX400 a truly future-proof solution.

Product data

General Information			
Number of light sources	1 [1 pc]	Gear	-
Lamp family code	LED80S [LED Module, system flux 8000 lm]	Driver/power unit/transformer	PSD [Power supply unit with DALI interface]
Beam angle of light source	120 °	Driver included	Yes
Light source colour	840 neutral white	Optic type	WB [Wide beam]
Cap base	- [-]	Optical cover/lens type	PM [PMMA bowl/cover]
Light source replaceable	No	Luminaire light beam spread	90°
Number of gear units	1 unit	Emergency lighting	No [-]
		Control interface	DALI

Maxos LED inserts for TTX400

Connection	Connection unit 5-pole
Cable	-
Protection class IEC	Safety class I
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	D [For mounting on easily flammable surfaces]
CE mark	CE mark
ENEC mark	ENEC mark
UL mark	No
Warranty period	5 years
Constant light output	No
Number of products on MCB	24
RoHS mark	RoHS mark
Product Family Code	4MX400 [Maxos LED Retrofit for TTX400]

Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Inrush current	21 A
Inrush time	0.28 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Trunking length	581 [1 unit for TL-D 58 W]
Housing material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	1528 mm
Overall width	63 mm
Overall height	50 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	--------------------------

Mech. impact protection code	IK02 [0.2 J standard]
------------------------------	------------------------

Initial Performance (IEC Compliant)

Initial luminous flux	8000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	151 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Initial input power	53 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	1 %
Median useful life L70B50	70000 h
Median useful life L80B50	50000 h
Median useful life L90B50	25000 h

Application Conditions

Ambient temperature range	-20 to +35 °C
Average ambient temperature	35 °C
Maximum dimming level	1%
Suitable for random switching	Not applicable

Product Data

Full product code	403073267280699
Order product name	4MX400 581 LED80S/840 PSD WB WH
EAN/UPC – product	4030732672806
Order code	67280699
Numerator – quantity per pack	1
Numerator – packs per outer box	3
Material no. (12NC)	910629167326
Net weight (piece)	1.895 kg

