



GentleSpace Green Warehouse system

BY471X GRN250S/840 MB GC ACW SI

GentleSpace GreenWarehouse - LED GreenLine system flux 25000
lm - 840 neutral white - Medium beam - Clear glass - ActiLume
wireless - Silver

This dedicated system makes it easy for warehouse developers and facility managers to achieve maximum energy savings. It seamlessly integrates state-of-the-art LED lighting with an easy-to-use and reliable networked control solution. When the situation on the work floor changes, settings such as dimming levels and timing can be changed wirelessly by the end-users themselves. Luminaires can be combined in groups across the layout, and re-zoning them does not require a hardware change, thus minimizing commissioning costs. The system delivers savings over and above the actual efficiency of the LEDs and is future-proof. Easy to understand, easy to design-in, and easy to use, the GreenWarehouse is simplicity itself.

Product data

General Information		Optical cover/lens type	GC [Clear glass]
Number of light sources	16 [16 pcs]	Luminaire light beam spread	40° x 40°
Lamp family code	GRN250S [LED GreenLine system flux 25000 lm]	Embedded control	ACW [ActiLume wireless]
Beam angle of light source	114 °	Control interface	-
Light source colour	840 neutral white	Connection	External connector
Light source replaceable	Yes	Cable	Cord 0.5 m with cable connector 3-pole
Number of gear units	2 units	Protection class IEC	Safety class I
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]	Mounting	SMT [Suspension set twin, triangle]
Driver included	Yes	Glow-wire test	Temperature 650 °C, duration 5 s
Optic type	MB [Medium beam]	Flammability mark	D [For mounting on easily flammable surfaces]

GentleSpace Green Warehouse system

CE mark	CE mark
ENEC mark	ENEC mark
Design award-winner marking	Design Award Winner 2014
Warranty period	5 years
Constant light output	No
Number of products on MCB	6
RoHS mark	RoHS mark
Product Family Code	BY471X [GentleSpace GreenWarehouse]

Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Inrush current	9.6 A
Inrush time	2.3 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Stainless steel
Optical cover/lens finish	Clear
Overall length	647 mm
Overall width	450 mm
Overall height	211 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]

Initial Performance (IEC Compliant)

Initial luminous flux	25000 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	152 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	165 W
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.5 %
Median useful life L70B50	70000 h
Median useful life L80B50	50000 h
Median useful life L90B50	25000 h


Application Conditions

Ambient temperature range	-20 to +45 °C
Average ambient temperature	25 °C
Maximum dimming level	10%
Suitable for random switching	Yes (relates to presence/ movement detection and daylight harvesting)

Product Data

Full product code	871869632141600
Order product name	BY471X GRN250S/840 MB GC ACW SI
EAN/UPC – product	8718696321416
Order code	32141600
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910930205899
Net weight (piece)	16.100 kg

Dimensional drawing



GentleSpace Warehouse system BY470X/BY471X

GentleSpace Green Warehouse system

