



760042036 | MGS500-BLK-318

**GigaSPEED X10D® MGS500 Series Category 6A U/UTP Information Outlets (bulk), blue**

## **OBSOLETE**

This product was discontinued on: **December 1, 2011**

### Replaced By

760110981  
MGS600-BULK-318

GigaSPEED X10D® MGS600 Series Information Outlet, blue, 100 pack

## Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D®
Product Type	Modular jack
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

Depth	30.48 mm   1.20 in
Height	20.32 mm   0.80 in
Width	20.32 mm   0.80 in

## Electrical Specifications

ANSI/TIA Category	6A
Contact Resistance Variation, maximum	20 mOhm
Contact Resistance, maximum	100 mOhm
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL

760042036 | MGS500-BLK-318

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Cable Type	U/UTP (unshielded)
Color	Blue
Brand	GigaSPEED X10D®   SYSTIMAX®
Package Quantity	100

## Mechanical Specifications

Conductor Gauge, solid	22 AWG   24 AWG
Conductor Gauge, stranded	22 AWG   24 AWG
Conductor Type	Solid   Stranded
Material Type	Copper alloy   High-impact, flame retardant, thermoplastic
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf   133 N
Rear Termination Contact Plating	Nickel
Rear Termination Type	IDC
Wiring	T568A   T568B

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system