



760111385 | 360-PM-GS5-2U

SYSTIMAX 360™ GigaSPEED X10D® PATCHMAX® GS5 Category 6A U/UTP Patch Panel, 24 port

- Available for use with the DYMO® labeling solution

OBSOLETE

This product was discontinued on: July 1, 2011

Replaced By

760102251

360-PM-GS6-2U-24

SYSTIMAX 360™ GigaSPEED X10D® PATCHMAX® GS6 Category 6A U/UTP Patch Panel, 24 port

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D® SYSTIMAX 360™
Product Type	Copper patch panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth, with cable management	10.50 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Height	88.90 mm 3.50 in
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

760111385 | 360-PM-GS5-2U

Total Ports, quantity	24
Cable Type	U/UTP (unshielded)
Brand	GigaSPEED X10D® PATCHMAX® SYSTIMAX 360™ SYSTIMAX®
Color	Cool gray Satin chrome
Modules, quantity	4
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	2

Mechanical Specifications

Conductor Gauge, solid	22 AWG 24 AWG
Conductor Gauge, stranded	22 AWG 24 AWG
Conductor Type	Solid Stranded
Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf 133 N
Rear Termination Contact Plating	Nickel
Rear Termination Type	IDC
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system