



760163774 | 360-iP-1100-E-2U-BLANK
SYSTIMAX 360™ iPatch® 1100 Evolve Panel, 48 port without modules

OBSOLETE

This product was discontinued on: June 30, 2015

Replaced By

760201160
360-iP-1100-E-2U-BLANK SYSTIMAX 360™ iPatch® 1100 Evolve Panel, 48 port without modules

Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch® SYSTIMAX 360™
Product Type	Copper patch panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	38.10 mm 1.50 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Height	44.45 mm 1.75 in
Weight	0.73 kg 1.60 lb
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6 6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA CE cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

760163774 | 360-iP-1100-E-2U-BLANK

Intelligence Type	iPatch® enabled
Total Ports, quantity	48
Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Color	Cool gray
Includes	Eight "A" labels Eight #12-24 mounting screws Forty-eight cable ties Instruction sheet Panel Two cable management bars
Package Quantity	1

Mechanical Specifications

Panel Style	Straight
Material Type	ABS Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf 133 N
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system