


10-bit digital video



Description

The ComNet™ FVT/FVR1001 series video transmitter/receiver supports the transmission of short-haul quality 10-bit digital video over one multimode or single mode optical fiber. This module is universally compatible with major CCTV camera manufacturers. Plug-and-play design ensures ease of installation and no electrical or optical adjustments are ever required. Bi-color (Red/Green) LED indicators are provided for rapidly ascertaining equipment operating status. Packaged in the exclusive ComNet ComFit housing, these units may be either wall or rack-mounted, or may be DIN-rail mounted by the addition of ComNet model DINBKT1 adaptor plate.

Features

- 10-bit Digital Video Transmission
- Compatible with all NTSC, PAL, or SECAM CCTV camera systems
- Full Color Compatibility
- Exceeds RS-250C Short-Haul quality
- No In-field electrical or optical adjustments
- Bi-color (Red/Green) LED status indicators provide rapid indication of critical operating parameters
- Integrated WDM for greater product reliability
- Voltage transient protection on all power and signal input/output lines provides unconditional protection from power surges and other voltage transient events.
- Distances up to 69 km (43 miles) without repeaters
- Tested and certified by an independent laboratory for full compliance with the environmental requirements (ambient operating temperature, mechanical shock, vibration, humidity with condensation, high-line/low-line voltage conditions and transient voltage protection) of NEMA TS-1/TS-2 and the Caltrans Specification for Traffic Signal Control Equipment.
- Hot-Swappable Modules
- Automatic resettable fuses on all power lines
- Lifetime Warranty

Applications

- CCTV



specifications

VIDEO

Video Input:	1V pk-pk (75 ohms)
Overload:	>1.5V pk-pk
Bandwidth:	5 Hz - 10 MHz
Differential Gain:	<2%
Differential Phase:	<0.7°
Tilt:	<1%
Signal-to-Noise Ratio (SNR):	>67 dB @ Maximum Optical Loss Budget
Max. RG-59 COAX Distance:	100m (300ft) Camera to Fiber Optic Module to maintain 6Mhz Bandwidth

WAVELENGTH

1310 nm, Multimode and Single Mode

NUMBER OF FIBERS

1

LED INDICATORS

- Optical - Video - Power

CONNECTORS

Optical:	ST
Power:	Terminal Block
Video:	BNC (Gold Plated Center-Pin)

ELECTRICAL & MECHANICAL

Power:	8-15 VDC @ 2 W
Surface Mount:	From Rack
Rack Mount:	1
Number of Rack Slots:	Automatic Resettable Solid-State Current Limiters
Current Protection:	Meets IPC Standard
Circuit Board:	6.1 × 5.3 × 1.1 in., (15.5 × 13.5 × 2.8 cm)
Size (in./cm) (L×W×H):	<2 lb./0.9 kg
Shipping Weight:	

ENVIRONMENTAL

MTBF:	>100,000 hours
Operating Temp:	-40° C to +75° C
Storage Temp:	-40° C to +85° C
Relative Humidity:	0% to 95% (non-condensing)†

† May be extended to condensation conditions by adding suffix '/C' to model number for conformal coating.




MADE IN THE
USA

PART NUMBER	DESCRIPTION	FIBERS REQUIRED	FIBER	OPTICAL PWR BUDGET	MAX. DISTANCE‡	# RACK SLOTS
FVT1001M1	Video Transmitter (1310 nm)	1	Multimode 62.5/125µm	16 dB	3 km (2 miles)	1
FVR1001M1	Video Receiver (1310 nm)					
FVT1001S1	Video Transmitter (1310 nm)	1	Single Mode 9/125µm	23 dB	69 km (43 miles)	1
FVR1001S1	Video Receiver (1310 nm)					
Accessories	9 Volt DC Plug-in Power Supply, 90-264 VAC, 50/60 Hz (Included)					
Options	Add '/C' for Conformally Coated Circuit Boards (Extra charge, consult factory)					
	DIN-Rail Mounting Adaptor Plate Kit – With mounting hardware (Optional, order model DINBKT1)					

NOTE: This product requires a fiber installation with a minimum 30 dB connector return loss. The use of Super Polish Connectors is recommended.

‡ Distance may be limited by optical dispersion.

Complies with FDA Performance Standard for Laser Products, Title 21, Code of Federal Regulations, Subchapter J
In a continuing effort to improve and advance technology, product specifications are subject to change without notice.



comnet
Communication Networks

3 CORPORATE DRIVE | DANBURY, CT 06810 | USA
T: 203.796.5300 | F: 203.796.5303 | TECH SUPPORT: 1.888.678.9427 | INFO@COMNET.NET
8 TURNBERRY PARK ROAD | GILDERSOME | MORLEY | LEEDS, UK LS27 7LE
T: +44 (0)113 307 6400 | F: +44 (0)113 253 7462 | INFO-EUROPE@COMNET.NET