


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART # 	TAB SIZE		WIRE RANGE		COLOR	DIMENSIONS in. [mm]					TOOL CHART								
	ENGLISH in.	METRIC mm	ENGLISH AWG	METRIC mm ²		MAX. WIRE INSUL. DIA.	L ± .03 [0,8]	W ± .01 [0,3]	H ± .01 [0,3]	D ± .01 [0,3]	PRESSES: CP-861, CP-862, CP-871	APPLICATOR DIES: CA9, CA-800EZ							
DNFR18250FIB-KD	.250 X .032	6,3 X 0,8	22-18	0,5-1,0	RED		.178 [4,52]	.57 [14,5]	.37 [9,4]	.21 [5,3]	.60 [15,2]	CD-800-9 CD9-9C							
DNFR18205FIB-KD	.205/.187 X .032	5,2/4,8 X 0,8																	
DNFR18206FIB-KD	.205/.187 X .020	5,2/4,8 X 0,5																	
DNFR14250FIB-KD	.250 X .032	6,3 X 0,8	16-14	1,5-2,5	BLUE														
DNFR14205FIB-KD	.205/.187 X .032	5,2/4,8 X 0,8																	
DNFR14206FIB-KD	.205/.187 X .020	5,2/4,8 X 0,5																	


NOTES:

- USED FOR:
 - STRANDED COPPER WIRE ONLY
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
 - 600V. MAX. BLDG WIRE
 - 6-12 LBS INITIAL INSERTION/WITHDRAWAL FORCE
- WIRE STRIP LENGTH:

11/32 ^{+1/32}₋₀ [8,7 ^{+0,8}₋₀]
- MATERIAL:
 - STAMPING: CDA 260 BRASS, TIN PLATED
 - HOUSING: TYPE 6/6 NYLON
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
- CURL SLOTS: DNFR18205FIB, DNFR18206FIB, DNFR14205FIB, DNFR14206FIB ONLY.



						TITLE	
						FEMALE DISCONNECTS, NYLON FULLY INSULATED - RIGHT ANGLE REEL SMART 	
						CUSTOMER DRAWING	
						ITEM REVISION NAME	
							N41124BA/11
						DATASET FILE NAME	
							N41124BA_DC/11 - A41124_REV11
--	---	---	---	---	ADDED "REEL SMART" TO DRAWING TITLE.	----	
11	2/22/18	BWG	SKB	JADE	 REVISED DIMENSION LOCATION OF HOUSING WIDTH. REMOVED TITLE BLOCK TOLERANCES.	019464/00	
10	10.10.12	JBN	LCA	VMB	ADDED METRIC EQUIVALENT. CHANGE PACKAGING NOTE. ADDED TOOLS CHART. UPDATED DRAWING TO CURRENT STANDARDS.	A41124	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE		FEMALE DISCONNECTS, NYLON FULLY INSULATED - RIGHT ANGLE REEL SMART 	
CUSTOMER DRAWING			
ITEM REVISION NAME			
	N41124BA/11		
DATASET FILE NAME			
	N41124BA_DC/11 - A41124_REV11		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± --- .XX ± ---		SEE NOTES	
.XXX ± --- ANGLES ± ---		DRAWING NUMBER:	
		A41124	
DRAWN BY	DATE	CHK	SCALE
MG	-	-	N.T.S.
SHT 1 OF 1		SIZE	
A			