



## Falcon WiNG Sensors Leak Detection

RLE has revolutionized the wireless sensor market with the launch of the WiNG wireless platform. A complete system of sensors, gateway manager, and range extenders monitors your facility for changes in temperature and humidity and allows you to fine tune your environment to meet energy efficiency goals, maintain optimal equipment performance parameters, and ensure your facility's operating as expected.

WiNG leak detection sensors are a valuable addition to this product line, and leverage our patented leak detection technology to protect your facility from intrusive water and chemical leaks. The WiNG-LD wireless sensor can be coupled with a spot detector or any of our leak detection sensing cables to detect and report leaks in any facility.

WiNG sensors are compact and unobtrusive, yet provide an industry leading battery life - sensor batteries will last up to 12 years at room temperatures. WiNG sensors maintain this extended battery life while communicating readings to the WiNG-MGR web interface every 10-20 seconds; we knew it was important to our customers that we didn't sacrifice data responsiveness in order to extend our battery life.

The WiNG system has an unprecedented transmission range between sensors and manager: up to 100 feet through multiple walls, up to 270 feet through one wall, and up to 600 feet indoor, direct line of sight. While this range is more than ample for most situations, sometimes applications require signals to be pushed through more complex physical or noisy RF environments. The WiNG-RXT range extender can be implemented in these situations to add up to 1,000 feet direct line of sight transmission distance to the application.

### Features

- Proprietary wireless design
- Monitor for leaks with one of the following configurations:
  - One SD-Z1 spot detector
  - One SD-Z spot detector and up to an additional 50 feet (15m) of leak detection sensing cable
  - Up to 100 feet (30.5m) of leak detection sensing cable
- Available as an 868MHz or 900MHz sensor
- A transmission range between manager and sensors that is second to none:
  - Up to 100 feet (30.5m) through multiple walls
  - Up to 270 feet (82.3m) through one wall
  - Up to 600 feet (183m) direct line of sight
  - Add up to 1,000 feet (305m) direct line of sight with each range extender
- Unparalleled sensor battery life:
  - Up to 5 years across full operating range: -13°F to 185°F (-25°C to 85°C)
  - Up 8 years at temperatures up to 122°F (50°C)
  - Up to 12 year battery life at room temperature
- Polling rate of 10-20 seconds

# Monitoring & Notification

[www.rletech.com](http://www.rletech.com)

# WiNG-LD Sensor Specifications

<b>Power</b>	3.6V AA lithium battery
<b>Battery Life</b>	Up to 5 years when system spans full operating temperature range. Up to 8 years at room temperatures up to 122°F (50°C) Up to 12 years at room temperature
<b>Shelf Life</b>	10 years in quiescent mode with battery installed
<b>Transmission</b> Interval Frequency Range	10-20 seconds (random) Available in 868MHz and 900MHz configurations Up to 600ft line of sight
<b>Leak Detection Input</b> Compatibility Sensor Response Time Cable Break Detection Cable Sensitivity	Accepts up to 100ft (30.5m) of sensing cable, 50ft (15m) of sensing cable and one SD-Z spot detector, or 1 SD-Z1 spot detector. Compatible with all RLE sensing cables and the SD-Z and SD-Z1 spot detectors. < 20 seconds Yes Configurable
<b>Operating Environment</b> Temperature Humidity Altitude	-13°F to 185°F (-25°C - 85°C) 0% to 90% RH (Non-condensing) -200 ft to 15,000 ft (-70m to 4572m) max.
<b>Mounting</b>	Free standing, zip ties, screw and keyhole - spaced 2.5" (6.4cm), junction box - 2 screws spaced 3.28" (8.3cm)
<b>Dimensions and Weight</b>	4.4"L x 2.5"W x 1.5"H (11.2cmL x 6.4cmW x 3.8cmH), 0.2lb (0.10kg)
<b>Certifications and Standards</b>	CE UL61010, CSA 22.2 #61010, IEC 61326-1, FCC 47CFR 15B, IC ICES-003, EN 61000-3-2, EN61000-3-3, ETSI EN 301 489-1, ETSI EN 301 489-3; FCC ID: X7J-A11072401; IC: 8975A-A11072401

