XBR-000139-C Brocade 4GBase-SX SFP MMF 850nm, 300m Reach, LC



XBR-000139-C

4Gbps SFP Transceiver

Features

- Up to 4Gb/s data links
- Duplex LC connector
- Hot-pluggable SFP footprint
- 850nm VCSEL Laser transmitter
- RoHS compliant and Lead Free
- Up to 300m on 50/125μm MMF
- Metal enclosure for lower EMI
- Single +3.3V power supply
- Low power dissipation <800mW
- Commercial and industrial operating temperature optional
- SFP MSA SFF-8074i Complaint

Applications

1x Fibre Channel

Product Description

This Brocade® XBR-000139-C compatible SFP transceiver provides 4Gbs-SW throughput up to 300m over multimode fiber (MMF) using a wavelength of 850nm via an LC connector. It is guaranteed to be 100% compatible with the equivalent Brocade® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. It is built to meet or exceed the specifications of Brocade®, as well as to comply with MSA (Multi-Source Agreement) standards to ensure seamless network integration. This transceiver is Trade Agreements Act (TAA) compliant. We stand behind the quality of our products and proudly offer a limited lifetime warranty.

ProLab's SFP transceivers are RoHS compliant and lead-free.

Regulatory Compliance


- ESD to the Electrical PINs: compatible with MIL-STD-883 Method 3015.
- ESD to the Duplex LC Receptacle: compatible with IEC 61000-4-2.
- Immunity compatible with IEC 61000-4-3.
- EMI compatible with FCC Part 15 Class B EN55022 Class B (CISPR 22B) VCCI Class B.
- Laser Eye Safety compatible with FDA 21CFR 1040.10 and 1040.11 EN60950, EN (IEC) 60825-1,2.
- RoHs compliant with 2002/95/EC 4.1&4.2 2005/747/EC.

Pin Descriptions

Pin	Symbol	Name/Descriptions	Ref.
1	VeeT	Transmitter Ground (Common with Receiver Ground)	1
2	TX Fault	Transmitter Fault.	
3	TX Disable	Transmitter Disable. Laser output disabled on high or open.	2
4	MOD DEF (2)	Module Definition 2. Data line for Serial ID.	3
5	MOD_DEF (1)	Module Definition 1. Clock line for Serial ID.	3
6	MOD_DEF (0)	Module Definition 0. Grounded within the module.	3
7	Rate Select	No connection required.	
8	LOS	Loss of Signal indication. Logic 0 indicates normal operation.	4
9	VeeR	Receiver Ground (Common with Transmitter Ground)	1
10	VeeR	Receiver Ground (Common with Transmitter Ground)	1
11	VeeR	Receiver Ground (Common with Transmitter Ground)	1
12	RD-	Receiver Inverted DATA out. AC Coupled.	
13	RD+	Receiver Non-inverted DATA out. AC Coupled.	
14	VeeR	Receiver Ground (Common with Transmitter Ground)	1
15	VccR	Receiver Power Supply.	
16	VccT	Transmitter Power Supply.	
17	VeeT	Transmitter Ground (Common with Receiver Ground)	1
18	TD+	Transmitter Non-Inverted DATA in. AC Coupled.	
19	TD-	Transmitter Inverted DATA in. AC Coupled.	
20	VeeT	Transmitter Ground (Common with Receiver Ground)	1


Notes:

- 1. Circuit ground is internally isolated from chassis ground.
- 2. Laser output disabled on TX Disable >2.0V or open, enabled on TX Disable <0.8V.
- 3. Should be pulled up with 4.7k-10kohms on host board to a voltage between 2.0V and 3.6V. MOD_DEF (0) pulls line low to indicate module is plugged in.
- 4. LOS is open collector output. Should be pulled up with 4.7k-10kohms on host board to a voltage between 2.0V and 3.6V. Logic 0 indicates normal operation; logic 1 indicates loss of signal.



Pin-out of connector Block on Host board

Recommend Circuit Schematic



Absolute Maximum Ratings

Parameter	Symbol	Min.	Max.	Unit
Supply Voltage	Vcc	-0.5	4.0	V
Storage Temperature	TS	-40	85	°C
Operating Humidity	RH	5	95	%

Recommended Operating Conditions

Parameter	Symbol	Min.	Тур.	Max.	Unit
Power Supply Voltage	Vcc	3.13	3.30	3.47	V
Power Supply Current	Icc			250	mA
Case Operating Temperature – Commercial	Тс	0		70	°C
Case Operating Temperature – Industrial	Ti	-40		85	°C
Data Rate (Fibre Channel)			4		Gbps
50/125μm MMF	L			300	m

Electrical Characteristics (TOP=25°C, Vcc=3.3V)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Notes		
Transmitter	Transmitter							
Input differential impedance	Rin		100		Ω	1		
Single ended data input swing	Vin, pp	250		1200	mV			
TX Disable-High		Vcc-1.3		Vcc	V			
TX Disable-Low		Vee		Vee+0.8	V			
TX Fault-High		Vcc-0.5		Vcc	V			
TX Fault-Low		Vee		Vee+0.5	V			
Receiver								
Single ended data output swing	Vout, pp	300	400	800	mV	2		
Data output rise time	tr			175	ps	3		
Data output fall time	tf			175	ps	3		
LOS-High		Vcc-0.5		Vcc	V			
LOS-Low		Vee		Vee+0.5	V			

Notes:

- 1. AC coupled.
- 2. Into 100-ohm differential termination.
- 3. 20% 80%

Optical and Electrical Characteristics


Parameter	Symbol	Min.	Тур.	Max.	Unit	Notes	
Transmitter							
Average Output Power	РО	-7.3		-1	dBm	1	
Optical Wavelength	λ	830	850	860	nm		
Spectral Width	σ			0.85	nm		
Optical Rise/Fall Time	tr/tf			260	ps	2	
Total Jitter	TJ			200	ps		
Optical Extinction Ratio	ER	9			dB		
Receiver	Receiver						
Receiver Sensitivity	RSENS			-9.9	dBm	3,4	
Maximum Received Power	RX _{MAX}	0			dBm		
Centre Wavelength	λC	770		860	nm		
LOS De-Assert	LOSD			-20	dBm		
LOS Assert	LOSA	-30			dBm		
LOS Hysteresis		0.5		5	dB		

Notes:

- 1. Class 1 Laser Safety.
- 2. Unfiltered, 20%-80%. Complies with GE and 1x FC eye masks when filtered.
- 3. Measured with conformance signals defined in FC-PI-2 Rev. 10.0 specifications.
- 4. Measured with PRBS 2⁷-1 at 10⁻¹⁰ BER.


Mechanical Specifications

Small Form Factor Pluggable (SFP) transceivers are compatible with the dimensions defined by the SFP Multi-Sourcing Agreement (MSA).



EEPROM Information

EEPROM memory map specific data field description is as below:



Digital Diagnostic Monitoring Interface

Five transceiver parameter values are monitored. The following table defines the monitored parameter's accuracy.

Parameter	Range	Accuracy	Calibration
Temperature	0°C to 70°C (C)	±3°C	Internal
	-40°C to 85°C (I)	-	
Voltage	2.97V to 3.63V	±3%	Internal
Bias Current	0mA to 100mA	±10%	Internal
TX Power	-7.3dBm to -1dBm	±3dB	Internal
RX Power	-9.9dBm to 0dBm	±3dB	Internal