





REVISIONS				
REV.	DESCRIPTION	ECN	DATE	APPROVED
G	REFER TO ECN	11339	1/29/13	KCB



MAXIMUM CHARACTERISTICS

SURGE:
50kA IEC 1000-4-5 8/20 μ s WAVEFORM 500 JOULES

TURN-ON:
330Vdc $\pm$ 20%

TURN-ON TIME:
1.5ns FOR 2kV/ns

FREQUENCY RANGE:
1.5MHz TO 700MHz

VSWR:
 $\leq$ 1.1:1 @ 1.5MHz TO 700MHz

INSERTION LOSS:
 $\leq$ 0.1dB OVER FREQUENCY RANGE

TEMPERATURE:
-45°C TO +85°C STORAGE/OPERATING +50°C

CE COMPLIANT

CUSTOMER APPROVAL: _____ DATE: _____

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS TOLERANCES: FRACTIONS=± 1/32 .XX=± .03 ANGLES=± 1° .XXX=± .010 NOTICE: THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF POLYPHASER CORPORATION. ALL RIGHTS RESERVED. THIRD-ANGLE PROJECTION 	DRAWN DS	DATE 12/23/94					SHEET 1 OF 1
	ENG APPD J. JONES	12/23/94					SCALE 1:1
	PRODUCT MGR		TITLE CUSTOMER PRINT IS-NEMP-C0 CUSTOMER SPECIFICATION				REV G
	MARKETING APPD N. JOHN	12/23/94					
	PROJECT NO.						
DOCUMENT NAME IS-NEMP-C0-C	SIZE A	CAGE 30992	PROD CAT RFP	PART NUMBER IS-NEMP-C0			

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.