

DRAWING NO. SD211939		4		3		2		1						
CATALOG NUMBER	I.D. EXPANDED		I.D. AFTER RECOVERY		WALL THICKNESS		CONDUCTOR RANGE	STANDARD REEL SIZE (FEET)	REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
	IN.	mm	IN.	mm	IN.	mm			B	10/25/13	UPDATE FORMAT PER M/U.	33752	RB	DS
HS_116T48PF	.062	1.6	.032	0.8	.018	0.45	#18	4						
HS_116T300PF	.062	1.6	.032	0.8	.018	0.45	#18	25						
HS_116T1200PF	.062	1.6	.032	0.8	.018	0.45	#18	100						
HS_332T48PF	.094	2.4	.046	1.2	.020	0.51	#18-16	4						
HS_332T300PF	.094	2.4	.046	1.2	.020	0.51	#18-16	25						
HS_332T1200PF	.094	2.4	.046	1.2	.020	0.51	#18-16	100						
HS_18T48PF	.125	3.2	.062	1.6	.020	0.51	#18-14	4						
HS_18T300PF	.125	3.2	.062	1.6	.020	0.51	#18-14	25						
HS_18T1200PF	.125	3.2	.062	1.6	.020	0.51	#18-14	100						
HS_316T48PF	.187	4.8	.093	2.4	.020	0.51	#18-12	4						
HS_316T300PF	.187	4.8	.093	2.4	.020	0.51	#18-12	25						
HS_316T1200PF	.187	4.8	.093	2.4	.020	0.51	#18-12	100						
HS_14T48PF	.250	6.4	.125	3.2	.025	0.64	#14-10	4						
HS_14T300PF	.250	6.4	.125	3.2	.025	0.64	#14-10	25						
HS_14T1200PF	.250	6.4	.125	3.2	.025	0.64	#14-10	100						
HS_38T48PF	.375	9.5	.187	4.7	.025	0.64	#8-6	4						
HS_38T300PF	.375	9.5	.187	4.7	.025	0.64	#8-6	25						
HS_38T1200PF	.375	9.5	.187	4.7	.025	0.64	#8-6	100						
HS_12T48PF	.500	12.7	.250	6.4	.025	0.64	#6-2	4						
HS_12T300PF	.500	12.7	.250	6.4	.025	0.64	#6-2	25						
HS_12T1200PF	.500	12.7	.250	6.4	.025	0.64	#6-2	100						
HS_34T48PF	.750	19	.375	9.5	.030	0.76	#1-3/0	4						
HS_34T300PF	.750	19	.375	9.5	.030	0.76	#1-3/0	25						
HS_34T1200PF	.750	19	.375	9.5	.030	0.76	#1-3/0	100						
HS_100T48PF	1.000	25.4	.500	12.7	.030	0.76	2/0-300	4						
HS_100T300PF	1.000	25.4	.500	12.7	.030	0.76	2/0-300	25						
HS_100T1200PF	1.000	25.4	.500	12.7	.030	0.76	2/0-300	100						
HS_150T48PF	1.500	38.1	.750	19	.035	0.89	2/0-350	4						
HS_150T1200PF	1.500	38.1	.750	19	.035	0.89	2/0-350	100						
HS_200T48PF	2.000	50.8	1.000	25.7	.040	1.02	250-500	4						
HS_200T1200PF	2.000	50.8	1.000	25.7	.040	1.02	250-500	100						

NOTES:

1. MATERIAL: THIN WALL POLYOLEFIN HEAT SHRINK TUBING.

2. TO ORDER: EX:BHS 116T48PF

B - BLACK

BL - BLUE

C - CLEAR

G - GREEN

R - RED

W - WHITE

Y - YELLOW

3. ALL HEAT SHRINK TUBING MEETS UL224 AND CSA C22.2 NO. 198.1

4. CONTINUOUS OPERATING TEMPERATURE: -131°F (-55°C) TO 275°F (135°C)

5. SHRINK TEMPERATURE: 284°F (120°C)

6. 2:1 SHRINK RATIO.

7. RATED VOLTAGE: 600V

8. SHRINK INSTRUCTIONS:

A) THE ARTICLE TO BE COVERED MUST BE CLEAN AND DRY.

B) INSERT THE ARTICLE TO BE COVERED INTO TUBING.

C) APPLY HEAT TO THE TUBING WITH A BACK AND FORTH MOTION FROM END TO END.

D) REMOVE HEAT AS SOON AS THE TUBING BEGINS TO ASSUME THE SHAPE OF THE ARTICLE.

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

THIN WALL HEAT SHRINK

ITEM NO: --

CAT NO: HS-T-PF (TABLE)

SCALE: N/A

DRAWN BY: R. BOISVERT 12/18/98

CHECKER: P. LAPONIUS 1/07/99

DSN APPVL: D. WALTERS 12/10/98

MFG APPVL: --

QC APPVL: S. GRAY 12/15/98

MKT APPVL: P. MITCHELL 12/11/98

PROD FAM: --

PROJECT #: --

DOCUMENT TYPE: Sales

REL LEVEL: AutoCAD

SIZE

C

DRAWING NO

SD211939

REV

B

SHEET 1 OF 1