

AXIS P3717-PLE

8 MP multidirectional camera with IR for 360° coverage

AXIS P3717-PLE Network Camera is a compact 8-megapixel camera with four varifocal lenses enabling overview and detailed surveillance. With one IP address and one network cable, the four-camera-in-one unit provides a flexible, cost-effective solution for multidirectional surveillance. 360° IR illumination, Forensic WDR and Lightfinder technology provides excellent video quality in any light conditions. Each camera head can be individually positioned (pan, tilt, roll and twist) along a circular track. Remote zoom and focus makes it easy to install and the clear cover, with no sharp edges, ensures undistorted views in all directions. The camera comes with an integrated weathershield.

- > **8 MP, 360° multidirectional camera, one IP address**
- > **360° IR illumination and remote zoom and focus**
- > **Axis Lightfinder and Forensic WDR**
- > **Flexible positioning of four varifocal camera heads**
- > **Axis Zipstream for reduced bandwidth and storage needs**



AXIS P3717-PLE

Camera		Casing
Image sensor	4 x 1/2.8" progressive scan RGB CMOS	IP66-, IP67-, NEMA 4X-rated, IK09 impact-resistant, aluminium and plastic casing with polycarbonate hard-coated dome, sunshield (PC/ASA) Color: white NCS S 1002-B For repainting instructions of casing and impact on warranty, contact your Axis partner.
Lens	Varifocal, 3–6 mm, F1.8–2.6 4x1080p capture mode: Horizontal field of view: 96°–49° Vertical field of view: 53°–27° Diagonal field of view: 113°–55° Motorized focus, motorized zoom	Mounting Mounting bracket with junction box holes (double gang box, single gang box, 4" octagon junction box and 4" square junction box) ½" (M20) conduit side entry ¾" (M25) conduit adapter included
Day and night	Automatically removable infrared-cut filter	Sustainability PVC free
Minimum illumination	Color: 0.17 lux at 50 IRE F1.8 B/W: 0.04 lux at 50 IRE F1.8, 0 lux with IR illumination on	Memory 1024 MB RAM, 512 MB Flash
Shutter time	1/32500 s to 2 s with 50 Hz 1/32500 s to 2 s with 60 Hz	Power Power over Ethernet (PoE) IEEE 802.3at Type 2 Class 4 IR illumination on: class 4, typical 11.1 W, max 17.0 W IR illumination off: class 3, typical 8.6 W, max 11.0 W
Camera angle adjustment	Pan ±90°, tilt 5–65°, rotation 5–95°, twist ±20°	Connectors RJ45 10BASE-T/100BASE-TX PoE
Video		IR illumination Four individually controllable IR with power-efficient, long-life 850 nm IR LEDs Range of reach 15 m (49.2 ft) or more depending on the scene
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, Main and High Profiles Motion JPEG	Storage Support for microSD/microSDHC/microSDXC card Dual SD cards Support for SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com
Resolution	4 x 1920x1080 (4 x HDTV 1080p) to 160x90	Operating conditions -30 °C to 50 °C (-22 °F to 112 °F) Humidity 10–100% RH (condensing)
Frame rate	Up to 25/30 fps (50/60 Hz)	Storage conditions -40 °C to 65 °C (-40 °F to 149 °F)
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Axis Zipstream technology in H.264 Controllable frame rate and bandwidth VBR/MBR H.264	Approvals EMC EN 55032 Class A, EN 50121-4, IEC 62236-4, EN 61000-3-2, EN 61000-3-3, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, RCM AS/NZS CISPR 32 Class A, KC KN32 Class A, KC KN35 Safety IEC/EN/UL 62368-1, IEC/EN/UL 60950-22 Environment IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-27, IEC 60068-2-78, IEC/EN 60529 IP66/67, IEC/EN 62262 IK09, NEMA 250 Type 4X Other IEC 62471
Image settings	Saturation, contrast, brightness, sharpness, Forensic WDR, white balance, exposure control, exposure zone, fine tuning of behavior at low light, rotation: 0°, 90°, 180°, 270° including Corridor Format, dynamic text and image overlay, Polygon privacy mask, compression	Dimensions Height: 91.5 mm (3.6 in) ø 255 mm (10.04 in)
Network		Weight 2.0 kg (4.4 lb)
IP address	One IP address for all channels	Included accessories RJ45 mounting tool, screw bit T20, Installation guide, Windows® decoder 1-user license
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, digest authentication, user access log, centralized certificate management	Optional accessories AXIS T94N01D Pendant Kit, Axis mounts and cabinets For more accessories, see www.axis.com
Supported protocols	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP™, SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH	Video management software AXIS Companion, AXIS Camera Station, video management software from Axis' Application Development Partners available on www.axis.com/vms
System integration		Languages English, Simplified Chinese, Traditional Chinese, French, German, Italian, Japanese, Korean, Polish, Portuguese, Russian, Spanish
Application Programming Interface	Open API for software integration, including VAPIX® and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF® Profile S and ONVIF® Profile G, specification at onvif.org	Warranty Axis 3-year warranty, see www.axis.com/warranty
Analytics	Included AXIS Video Motion Detection, active tampering alarm Supported AXIS Perimeter Defender ^b , AXIS Guard Suite including AXIS Motion Guard, AXIS Fence Guard, and AXIS Loitering Guard Support for AXIS Camera Application Platform enabling installation of third-party applications, see www.axis.com/acap	
Event triggers	Detectors, hardware, input signal, storage, system, time, analytics, edge storage events	
Event actions	Day/night vision mode, overlay text, record video, send images, send notification, send SNMP trap, send video clip, status LED File upload: FTP, HTTP, HTTPS, network share, SFTP and email Notification: email, HTTP, HTTPS, TCP and SNMP trap	
Data streaming	Event data	
Built-in installation aids	Pixel counter, focus assistant, remote focus, remote zoom	
General		

- a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (openssl.org), and cryptographic software written by Eric Young (ey@cryptsoft.com).
b. One sensor only

Environmental responsibility:

www.axis.com/environmental-responsibility