

ABB general purpose drives

ACS310, 0.5 to 30 hp/0.37 to 22 kW

ABB general purpose drives, ACS310, are dedicated to variable torque applications such as booster pumps and centrifugal fans.

The drive design includes a powerful set of features which benefit pump and fan applications including built-in PID controllers and PFC (pump and fan control) that varies the drive's performance in response to changes in pressure, flow or other external data. The drives also have pre-programmed protection functions such as pipe cleaning for preventive maintenance.



The ACS310 drives provide built-in energy efficiency features. Energy savings can be easily monitored using the built-in energy calculators, that display energy savings in kilowatt hours and saved carbon dioxide emissions. The savings can also be displayed in local currencies.

Among the energy efficiency calculators is an energy optimizer that helps to improve system's energy efficiency while operating at partial loads. Load analyzer is a built-in statistical tool to analyze the drive as well as motor dimensioning and further analyze the process energy efficiency and operation. Even the drive's internal fan is controlled by software to reduce noise and losses, improving energy efficiency.

These features, combined with pre-programmed application macros, an intuitive user interface and several assistant screens, speed up the installation, parameter setting and commissioning of the drive.

Highlights

- Pump and fan features such as pump and fan control (PFC and SPFC)
- Pipe cleaning and fill functions
- Energy efficiency calculators
- Energy optimizer
- Load analyzer for optimized dimensioning of the drive, motor and process
- Embedded Modbus EIA-485 fieldbus interface
- FlashDrop tool for fast parameter setting
- Unified height and depth
- Full output current at 50 °C ambient
- Short parameter menu view

Voltage and power range

- 1-phase, 200 to 240 V $\pm$ 10%:
0.5 to 5 hp (0.37 to 4 kW)
- 3-phase, 200 to 240 V $\pm$ 10%:
0.5 to 15 hp (0.37 to 11 kW)
- 3-phase, 380 to 480 V $\pm$ 10%:
0.5 to 30 hp (0.37 to 22 kW)

Applications

- Booster pumps
- Irrigation systems
- Level control
- Centrifugal fans

Options

- Basic and Assistant control panels
- FlashDrop tool for fast cold configuration
- MREL-01 Relay output extension module
- SREA-01 Ethernet adapter
- DriveWindow Light PC tool

Power and productivity
for a better world™



Ratings				Type designation	Frame size
P_N hp	P_N kW	$I_{2N}^{(1)}$ A	$I_{LD}^{(2)}$ A		
1-phase AC supply, 200 to 240 V					
0.5	0.37	2.4	2.3	ACS310-01X-02A4-2	R0
1.0	0.75	4.7	4.5	ACS310-01X-04A7-2	R1
1.5	1.1	6.7	6.5	ACS310-01X-06A7-2	R1
2.0	1.5	7.5	7.2	ACS310-01x-07A5-2	R2
3.0	2.2	9.8	9.4	ACS310-01x-09A8-2	R2
5.0	4.0	16.5	15.0	ACS310-03U-50A8-2*	R4
3-phase AC supply, 200 to 240 V					
0.5	0.37	2.6	2.4	ACS310-03X-02A6-2	R0
0.75	0.55	3.9	3.5	ACS310-03X-03A9-2	R0
1	0.75	5.2	4.7	ACS310-03X-05A2-2	R1
1.5	1.1	7.4	6.7	ACS310-03X-07A4-2	R1
2	1.5	8.3	7.5	ACS310-03X-08A3-2	R1
3	2.2	10.8	9.8	ACS310-03X-10A8-2	R2
5	4	19.4	17.6	ACS310-03X-19A4-2	R2
7.5	5.5	26.8	24.4	ACS310-03X-26A8-2	R3
10	7.5	34.1	31.0	ACS310-03X-34A1-2	R4
15	11	50.8	46.2	ACS310-03X-50A8-2	R4
3-phase AC supply, 380 to 480 V					
0.5	0.37	1.3	1.2	ACS310-03X-01A3-4	R0
0.75	0.55	2.1	1.9	ACS310-03X-02A1-4	R0
1	0.75	2.6	2.4	ACS310-03X-02A6-4	R1
1.5	1.1	3.6	3.3	ACS310-03X-03A6-4	R1
2	1.5	4.5	4.1	ACS310-03X-04A5-4	R1
3	2.2	6.2	5.6	ACS310-03X-06A2-4	R1
5	4	9.7	8.8	ACS310-03X-09A7-4	R1
7.5	5.5	13.8	12.5	ACS310-03X-13A8-4	R3
10	7.5	17.2	15.6	ACS310-03X-17A2-4	R3
15	11	25.4	23.1	ACS310-03X-25A4-4	R3
20	15	34.1	31	ACS310-03X-034A-4	R4
25	18.5	41.8	38	ACS310-03X-41A8-4	R4
30	22	48.4	44	ACS310-03X-48A4-4	R4

10% overloadability for one minute every ten minutes.



Voltage and power connection	1-phase, 200 to 240 V ± 10%: 0.5 to 5 hp (0.37 to 4 kW) 3-phase, 200 to 240 V ± 10%: 0.5 to 15 hp (0.37 to 11 kW) 3-phase, 380 to 480 V ± 10%: 0.5 to 30 hp (0.37 to 22 kW)
Frequency	48 to 63 Hz
Motor connection	
Motor types	Asynchronous induction motors
Voltage	3-phase, from 0 to U_{supply}
Frequency	0 to 500 Hz
Switching frequency	4, 8, 12 and 16 kHz (derated)
Type of control	Scalar U/f Linear, squared and user definable U/f profiles Energy optimizer
Serial communication	
Fieldbus	Modbus RTU EIA-485 and EIA-232 Modbus TCP with SREA-01 option module
Environmental limits	
Degree of protection	IP20/Optional NEMA 1 enclosure
Ambient temperature	14 to 122 °F (-10 to +50 °C), no frost allowed
Product compliance	
Markings	CE and C-Tick approvals UL, cUL and GOST R RoHS compliant
Directives	Low Voltage Directive 2006/95/EC Machinery Directive 2006/42/EC EMC Directive 2004/108/EC
Harmonics	For reducing THD in partial loads and to comply with EN/IEC 61000-3-12 with external AC input chokes
EMC	Class C3 (2 nd environment unrestricted distribution) built-in as standard Class C2 and C1 with external optional EMC filters

Typical I/O connections		ACS310: X1
Ramp pair sel	Const. Speed 1	9 +24 V
	Fwd / Rev	10 GND
	Start / Stop	11 DCOM
		12 DI1
		13 DI2
		14 DI3
		15 DI4
		16 DI5

Wiring diagram for ACS310: X1:

- Motor terminals: +24 V, 0 V, and a control line.
- ACS310: X1 connector pins:
 - Pin 9: +24 V
 - Pin 10: GND
 - Pin 11: DCOM
 - Pin 12: DI1
 - Pin 13: DI2
 - Pin 14: DI3
 - Pin 15: DI4
 - Pin 16: DI5
- Motor label: Const. speed 1

Power and productivity
for a better world™

