


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N



WEIGHT

CFPL1**Y

.60 LB/10 PCS.
(273.9 G/10 PCS.)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. PART INCLUDES:
 - 1- FACEPLATE
 - 2- MOUNTING SCREW
 - 2- LABEL
 - 2- LABEL COVER
4. DIMENSIONS IN [] ARE IN METRIC.

| | | | |
|---|----------|---|-------|
| PRODUCT SPEC | | PACKAGING SPEC | |
| N/A | | N/A | |
| PART NUMBER | | WORK INSTRUCTION | |
| CFPL1**Y | | N/A | |
| INSPECTION INSTRUCTION NUMBER | | FMEA & CONTROL PLAN NUMBER | |
| N/A | | N/A | |
| TITLE | | | |
| MINI-COM 1 POSITION VERTICAL CLASSIC SERIES FACEPLATE WITH LABEL/COVER | | | |
| CUSTOMER DRAWING | | | |
| ITEM REVISION NAME | |  | |
| 00128LAB/00 | | | |
| DATASET FILE NAME | | | |
| 00128LAB_DC02/00A | | MATERIAL: | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] | | ABS | |
| .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 ° | | DRAWING NUMBER: | |
|  | | 00128LAB-02 | |
| THIRD ANGLE PROJECTION | | | |
| DRAWN BY | DATE | CHK | SCALE |
| BJN | 10-26-16 | SCAL | NONE |
| SHT 1 OF 1 | | SIZE | |
| | | A | |

2

1

| | | | | | | |
|-----|----------|-----|------|-----|------------------------|-------------|
| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
| R | 10-26-16 | BJN | SCAL | MMR | RELEASED TO PRODUCTION | 00128LAB-02 |

B

A

A

A