



New product
for 2018



3 year
ext. warranty*



JC17039WH

Classification

Class 1
IP54 | 240V

Lamp

E27 15W Max
Lamp not supplied


Finishes

Anthracite (**BLK**), White (**WH**)

Construction

Body: Aluminium
Diffuser: Glass

JC17039



All data sheets and installation sheets
available at jcc.co.uk

Glazed Post Box

Architectural exterior LED lighting

- Stylish, contemporary design
- Durable die-cast aluminium construction
- Toughened glass post top with E27 lamp holder
- IP54 protection against dust and moisture
- Matching finish to the Architectural Exterior range
- Suitable for use with LED lamps



Code	Description
------	-------------

JC17039	Glazed Post Box
---------	-----------------

For Anthracite add **BLK** suffix, for White add **WH** suffix

*Requires online registration.