



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. PRIMARY DIMENSIONS ARE IN MILLIMETERS.
3. EQUIPMENT RAILS (E-RAILS) ARE SET TO 738mm [29.1"] FROM THE FACTORY. E-RAILS ARE INFINITELY ADJUSTABLE, FROM A MINIMUM OF 128mm APART, TO A MAXIMUM FOUND IN THE CHART ON SHEET 2.
4. CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANAGEMENT AND PATCH PANEL PRODUCTS.
5. EIA UNIVERSAL STANDARD HOLE PROGRESSION ON EQUIPMENT RAILS
6. PARTS SUPPLIED:
 - BASE CABINET
 - FRONT CURVED PERFORATED SINGLE HINGE DOOR, 69% OPEN AREA, OPENS UP TO 165° WHEN GANGED
 - REAR PERFORATED SPLIT DOOR, 69% OPEN AREA, OPENS UP TO 150° WHEN GANGED
 - EQUIPMENT RAILS FRONT & REAR (E-RAILS) (SEE CHART ON SHEET 2)
 - PDU MOUNTING / CABLE MANAGEMENT BRACKETS (CMB)
 - SWIVEL CASTERS
 - HARDWARE KIT CONTAINING:
 - (40) M6 CAGE NUTS
 - (40) M6 PHILIPS HEAD SCREWS
 - (4) GANGING BRACKETS
 - (8) M5 TORX (T25) THREAD CUTTING SCREWS
 - (4) RINGS OF CABINET LOCK KEYS WITH (2) KEYS PER RING.
 - LEVELING LEGS
 - INSTRUCTION SHEET
7. RACK UNIT SPACING NUMERALS ARE PRINTED ON EQUIPMENT MOUNTING RAILS, NUMBERS UP
8. FULLY BONDED STRUCTURE WHEN ASSEMBLED PER INSTRUCTIONS.
9. STATIC LOAD RATING 1500 Kg (3300 LBS)
10. ROLLING LOAD RATING 500 Kg (1102 LBS)

							TITLE NET-VERSE D-TYPE CABINET 600 WIDE X 42/45/48 RU X 1000mm/1200mm DEEP (DN6****) CUSTOMER DRAWING				
							ITEM REVISION NAME 00083FAA/01				
							DATASET FILE NAME 00083FAA_DC_01B				
01B	6-7-18	LEE	DWR	SJP	ADDED 48RU	V09001RP	 THIRD ANGLE PROJECTION				
01A	5/4/18	MEX-JAGC	DWR	SJP	ADDED SHEET #7 ADDED HARDWARE KIT TO PARTS SUPPLIED	V09001RG/00					
00A	11-16-16	LEE	MCIS		RELEASED TO PRODUCTION	V09001BI/03					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY LEE	DATE 11-16-16	CHK MCIS	SCALE NONE	MATERIAL: N/A
										DRAWING NUMBER: 00083FAA-DC	SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	DESCRIPTION	FRAME HEIGHT	FRAME DEPTH	E-RAIL MAXIMUM SPACING	SIDE PANELS	CABINET UNPACKAGED WEIGHT	CABINET SHIPPING WEIGHT
DN6219*	NET-VERSE D-TYPE CABINET 600mm WIDE X 42RU X 1000mm DEEP	1998.0 (78.66)	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	00	82 Kg/EACH 180 LBS/EACH	113 Kg/EACH 249 LBS/EACH
DN6212*	NET-VERSE D-TYPE CABINET 600mm WIDE X 42RU X 1000mm DEEP	1998.0 (78.66)	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	02	121 Kg/EACH 266 LBS/EACH	150 Kg/EACH 331 LBS/EACH
DN6229*	NET-VERSE D-TYPE CABINET 600mm WIDE X 42RU X 1200mm DEEP	1998.0 (78.66)	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	00	86 Kg/EACH 190 LBS/EACH	116 Kg/EACH 256 LBS/EACH
DN6222*	NET-VERSE D-TYPE CABINET 600mm WIDE X 42RU X 1200mm DEEP	1998.0 (78.66)	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	02	131 Kg/EACH 289 LBS/EACH	164 Kg/EACH 362 LBS/EACH
DN6519*	NET-VERSE D-TYPE CABINET 600mm WIDE X 45RU X 1000mm DEEP	2131.4 (83.91)	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	00	85 Kg/EACH 188 LBS/EACH	114 Kg/EACH 251 LBS/EACH
DN6512*	NET-VERSE D-TYPE CABINET 600mm WIDE X 45RU X 1000mm DEEP	2131.4 (83.91)	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	02	125 Kg/EACH 275 LBS/EACH	156 Kg/EACH 344 LBS/EACH
DN6529*	NET-VERSE D-TYPE CABINET 600mm WIDE X 45RU X 1200mm DEEP	2131.4 (83.91)	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	00	89 Kg/EACH 196 LBS/EACH	125 Kg/EACH 276 LBS/EACH
DN6522*	NET-VERSE D-TYPE CABINET 600mm WIDE X 45RU X 1200mm DEEP	2131.4 (83.91)	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	02	135 Kg/EACH 297 LBS/EACH	175 Kg/EACH 386 LBS/EACH
DN6819*	NET-VERSE D-TYPE CABINET 600mm WIDE X 48RU X 1000mm DEEP	2264.7 (89.16)	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	00	88 Kg/EACH 194 LBS/EACH	119 Kg/EACH 262 LBS/EACH
DN6812*	NET-VERSE D-TYPE CABINET 600mm WIDE X 48RU X 1000mm DEEP	2264.7 (89.16)	1000.0 (39.37)	738 (29.1) WITH CMB 871 (34.3) WITHOUT CMB	02	129 Kg/EACH 284 LBS/EACH	160 Kg/EACH 353 LBS/EACH
DN6829*	NET-VERSE D-TYPE CABINET 600mm WIDE X 48RU X 1200mm DEEP	2264.7 (89.16)	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	00	92 Kg/EACH 202 LBS/EACH	128 Kg/EACH 282 LBS/EACH
DN6822*	NET-VERSE D-TYPE CABINET 600mm WIDE X 48RU X 1200mm DEEP	2264.7 (89.16)	1200.0 (47.24)	938 (36.9) WITH CMB 1071 (42.2) WITHOUT CMB	02	139 Kg/EACH 306 LBS/EACH	175 Kg/EACH 386 LBS/EACH


NOTE: "*" DENOTES COLOR - ADD SUFFIX "B" FOR BLACK AND "W" FOR WHITE


						TITLE NET-VERSE D-TYPE CABINET 600 WIDE X 42/45/48RU X 1000mm/1200mm DEEP (DN6****) CUSTOMER DRAWING						
						ITEM REVISION NAME 00083FAA/01						
						DATASET FILE NAME 00083FAA_DC_01B						
						MATERIAL: N/A						
						DRAWING NUMBER: 00083FAA-DC						
01B 6-7-18 LEE DWR SJP SEE SHEET 1 FOR REVISIONS V09001RP						 THIRD ANGLE PROJECTION						
01A 5/4/18 MEX-JAGC DWR SJP SEE SHEET 1 FOR REVISIONS V09001RG/00												
00A 11-16-16 LEE MCIS SEE SHEET ONE FOR REVISIONS V09001BI/03												
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 7	SIZE
							LEE	11-16-16	MCIS	NONE		A

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





							TITLE		NET-VERSE D-TYPE CABINET 600 WIDE X 42/45/48RU X 1000mm/1200mm DEEP (DN6****) CUSTOMER DRAWING			
							ITEM REVISION NAME		00083FAA/01			
							DATASET FILE NAME		00083FAA_DC_01B			
01B	6-7-18	LEE	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP	 THIRD ANGLE PROJECTION		DRAWING NUMBER: 00083FAA-DC		MATERIAL: N/A	
01A	5/4/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00						
00A	11-16-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09001BI/03						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 3 OF 7	
							LEE	11-16-16	MCIS	NONE	A	

2

1

D:\10100DA\16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





FRONT DOOR, REAR DOOR,
AND SIDE PANELS NOT SHOWN

							TITLE NET-VERSE D-TYPE CABINET 600 WIDE X 42/45/48RU X 1000mm/1200mm DEEP (DN6****) CUSTOMER DRAWING							
							ITEM REVISION NAME 00083FAA/01				PANDUIT			
							DATASET FILE NAME 00083FAA_DC_01B							
01B	6-7-18	LEE	DWR	SJP	SEE SHEET 1 FOR REVISIONS		V09001RP				MATERIAL: N/A			
01A	5/4/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS		V09001RG/00							
00A	11-16-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS		V09001BI/03							
											THIRD ANGLE PROJECTION			
											DRAWING NUMBER: 00083FAA-DC			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY LEE		DATE 11-16-16	CHK MCIS	SCALE NONE	SHT 4 OF 7		SIZE A

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



SOME PARTS REMOVED FOR CLARITY

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01B	6-7-18	LEE	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP
01A	5/4/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00
00A	11-16-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09001BI/03

TITLE		NET-VERSE D-TYPE CABINET 600 WIDE X 42/45/48RU X 1000mm/1200mm DEEP (DN6****) CUSTOMER DRAWING	
ITEM REVISION NAME		00083FAA/01	
DATASET FILE NAME		00083FAA_DC_01B	
MATERIAL:		N/A	
DRAWING NUMBER:		00083FAA-DC	
DRAWN BY	DATE	CHK	SCALE
LEE	11-16-16	MCIS	NONE
THIRD ANGLE PROJECTION		SHT 5 OF 7	
SIZE		A	

2

1

B

A



SI/000DA/16


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TOP CAP OPENING CABLE CAPACITY								
	AREA		CABLE CAPACTIY* (CABLE DIA)					
	CM ²	IN ²	CAT 6A (8.99mm)	CAT 6A (7.87mm)	CAT 6A (7.54mm)	CAT 6 (6.35mm)	CAT 5e (4.75mm)	FIBER (3mm)
84mm × 476mm FRONT AND REAR OPENINGS (EACH)	339.6	61.9	251	328	358	504	902	2261

* CAPACITY CALCULATION ASSUMES 40% FILL FACTOR

							TITLE NET-VERSE D-TYPE CABINET 600 WIDE X 42/45/48RU X 1000mm/1200mm DEEP (DN6****) CUSTOMER DRAWING					
							ITEM REVISION NAME 00083FAA/01					
							DATASET FILE NAME 00083FAA_DC_01B					
01B	6-7-18	LEE	DWR	SJP	SEE SHEET 1 FOR REVISIONS□	V09001RP	 THIRD ANGLE PROJECTION				MATERIAL: N/A	
01A	5/4/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00					DRAWING NUMBER: 00083FAA-DC	
00A	11-16-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09001BI/03						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY LEE	DATE 11-16-16	CHK MCIS	SCALE NONE	SHT 6 OF 7	SIZE A

2


1

SI/VD00DA/16

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


FROM CENTER OF TOP
MOUNTING BUTTON TO TOP CAP:

42RU 137.5 [5.4]
45RU 204.1 [8.0]
48RU 114.2 [4.5]



REAR VIEW

RIGHT VIEW



TOP VIEW

PDU FIT:
MAXIMUM WIDTH OF 63mm FOR (2) PDU'S
MOUNTED ON ONE BRACKET,
OR (1) 130mm WIDE PDU.

PDU'S WILL ENTER EIA AREA BEHIND REAR
EQUIPMENT RAILS.

SOME
COMPONENTS
REMOVED
FOR CLARITY

TITLE		NET-VERSE D-TYPE CABINET 600 WIDE X 42/45/48RU X 1000mm/1200mm DEEP (DN6****) CUSTOMER DRAWING	
ITEM REVISION NAME		00083FAA/01	
DATASET FILE NAME		00083FAA_DC_01B	
MATERIAL:		N/A	
DRAWING NUMBER:		00083FAA-DC	
THIRD ANGLE PROJECTION		DRAWN BY: LEE DATE: 11-16-16 CHK: MCIS SCALE: NONE	
SHT 7 OF 7		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01B	6-7-18	LEE	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RP
01A	5/4/18	MEX-JAGC	DWR	SJP	SEE SHEET 1 FOR REVISIONS	V09001RG/00
00A	11-16-16	LEE	MCIS		SEE SHEET ONE FOR REVISIONS	V09001BI/03