



USB 3.0 to Video Adapters

- Designed for compatibility with USB 3.0 ports
- Resolutions supported up to 2560x1600
- Functions like an external video card
- Available in VGA, DVI, HDMI and DisplayPort




Specifications: USB 3.0 to Video Adapters

Electrical Characteristics:

USB Specification:	3.0
Max Video Resolution Supported:	2560x1600
Operating Systems Supported:	Windows XP, Vista (32 & 64bit), 7 (32 & 64bit), 8
Power Mode:	Bus powered
Power Consumption:	340mA
Supported Modes:	Extended Desktop (Default), Mirrored, Primary Display

Physical Characteristics:

Dimensions:	84.3 x 55.2 x 17.8mm
Operation Temperature:	10°C–40°C
Storage Temperature:	-20°C–70°C
Relative Humidity:	<85% Non-Condensing
Housing:	Plastic
Approvals:	CE compliant for RoHS2



Part Number	Description	Weight (Kg)
81930	USB 3.0 to VGA Video Adapter—External Video Card	0.181
81931	USB 3.0 to DVI Video Adapter—External Video Card	0.181
81932	USB 3.0 to HDMI Video Adapter—External Video Card	0.187
81933	USB 3.0 to DisplayPort Video Adapter—External Video Card	0.180

