


ALL-TEMP(K) INDUSTRITE® Power

Festoon and Reeling Power Cable / -40° C to 90° C / 8 AWG - 1000 KCMIL Thermoset Jacket / 2000V



Application



ALL-TEMP(K) INDUSTRITE® Power Cable is designed and manufactured for use in continuous flexing, twisting, and other abusive physical applications where flame, abrasion, chemicals, moisture, impact, tearing, and temperature extremes are considerations. Applications include portable power, spring and motor driven reels, festoon systems, power tracks, cable tenders, cranes and hoists.

ALL-TEMP(K) INDUSTRITE® cables are suitable for use indoors and outdoors on magnet cranes, barges, milling machines, mining equipment, and oil rigs, and are suitable for installations in water including aerator ponds.

Specifications and Ratings

- Rated for Continuous Operation at -40° C to 90° C
- UL Listed (E130231) Type W 2000 volts 90° C Wet or Dry
- Certified CSA (LL231593) Type W, 2000 volt, FT1 and FT5
- UL Festooning
- RoHS Compliant

Construction Options

Consult factory for cables designed and manufactured in a variety of alternative constructions for specific applications,

Options include:

- Overall Shields and Armor
- composite Conductors
- Fiber Optic Components
- Cold Temperature Thermoset Jacket Compound for -50°C Rating
- MSHA Approval
- Green/Yellow Stripe Neutral



Design Parameters

CONDUCTORS: Extra-flexible rope stranding (Class K), soft-drawn uncoated copper per ASTM B-3, ASTM B-172, and UL-62 offers high flexibility, extended flex-life and reduced copper fatigue/conductor breakage.

SEPARATOR: Separator tape for easy stripping.

INSULATION: Black thermoset (EPDM) insulation. Excellent physical and electrical properties, insulation has printed color code for easy conductor identification, suitable for use in extreme flexing applications.

CABLING: Conductors are cabled with non-wicking, non-hygroscopic fillers, without a separator which allows pressure-extruded jacket to fill interstices and prohibits conductor displacement during flexing operations.

JACKET: Available in stock with black, oil and flame-resistant, double-layer, reinforced thermoset jacket per UL-62 and ANSI/NEMA WC 58 ICEA S-95-381, suitable for use indoors and outdoors in abusive flexing applications where oil, chemicals, and extreme temperatures are considerations.

Available Jacket Colors:



Note: The use of basket-weave grips, a minimum of 12" in length, is recommended for prolonging cable life.

Single conductor versions are available from 8 AWG to 1000 KCMIL.

Prysmian Group

700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | na.prysmiangroup.com

Sales and Distribution:

22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444



A brand of the



ALL-TEMP(K) INDUSTRIRITE® Power

Festoon and Reeling Power Cable / -40° C to 90° C / 8 AWG - 1000 KCMIL / Thermoset Jacket / 2000V

Part Number	Conductor Number	Conductor Size	Stranding	Nominal Insulation Thickness in (mm)	Nominal Jacket Thickness in (mm)	Nominal Cable O.D. in (mm)	Ampacity ¹	Minimum Bend Diameter in (mm)	Approximate Cable Weight Lbs/Mft (Kg/Km)
K13377C	2	8 AWG	168/30	.060 (1.5)	.110 (2.8)	.810 (20.6)	83	7 (177.8)	343 (511)
K13378C	3	8 AWG	168/30	.060 (1.5)	.135 (3.4)	.910 (23.1)	73	7 (177.8)	471 (701)
K13379C	4	8 AWG	168/30	.060 (1.5)	.135 (3.4)	.990 (25.1)	57	8 (203.2)	637 (948)
K13380C	6	8 AWG	168/30	.060 (1.5)	.155 (3.9)	1.180 (30.0)	57	9 (228.6)	948 (1411)
K13371C	2	6 AWG	266/30	.060 (1.5)	.125 (3.2)	.930 (23.6)	110	7 (177.8)	498 (741)
K13372C	3	6 AWG	266/30	.060 (1.5)	.140 (3.6)	1.010 (25.7)	97	8 (203.2)	607 (904)
K13373C	4	6 AWG	266/30	.060 (1.5)	.140 (3.6)	1.100 (27.9)	77	9 (228.6)	862 (1283)
K13374C	6	6 AWG	266/30	.060 (1.5)	.155 (3.9)	1.310 (33.3)	77	11 (279.4)	1144 (1703)
K13365C	2	4 AWG	420/30	.060 (1.5)	.155 (3.9)	1.080 (27.4)	145	9 (228.6)	681 (1014)
K13366C	3	4 AWG	420/30	.060 (1.5)	.170 (4.3)	1.170 (29.7)	127	9 (228.6)	875 (1303)
K13367C	4	4 AWG	420/30	.060 (1.5)	.170 (4.3)	1.270 (32.3)	100	10 (254.0)	1135 (1690)
K13368C	6	4 AWG	420/30	.060 (1.5)	.190 (4.8)	1.520 (38.6)	100	12 (304.8)	1629 (2425)
K13360C	2	2 AWG	665/30	.060 (1.5)	.190 (4.8)	1.270 (32.3)	194	10 (254.0)	1040 (1548)
K13361C	3	2 AWG	665/30	.060 (1.5)	.190 (4.8)	1.340 (34.0)	169	11 (279.4)	1280 (1906)
K13362C	4	2 AWG	665/30	.060 (1.5)	.200 (5.1)	1.480 (37.6)	135	12 (304.8)	1636 (2436)
K13356C	2	1 AWG	836/30	.080 (2.0)	.170 (4.3)	1.440 (36.6)	226	12 (304.8)	1325 (2973)
K13357C	3	1 AWG	836/30	.080 (2.0)	.170 (4.3)	1.510 (38.4)	197	12 (304.8)	1680 (2501)
K13358C	4	1 AWG	836/30	.080 (2.0)	.180 (4.6)	1.680 (42.7)	158	13 (330.2)	2135 (3179)
K13353C	3	1/0 AWG	1045/30	.080 (2.0)	.170 (4.3)	1.710 (43.4)	228	13 (330.2)	1841 (2741)
K13354C	4	1/0 AWG	1045/30	.080 (2.0)	.170 (4.3)	1.790 (45.5)	183	14 (333.6)	2446 (3642)
K13350C	3	2/0 AWG	1330/30	.080 (2.0)	.200 (5.1)	1.750 (44.5)	264	14 (333.6)	2232 (3323)
K13351C	4	2/0 AWG	1330/30	.080 (2.0)	.200 (5.1)	1.980 (49.0)	211	15 (381.0)	3268 (4865)
K13347C	3	3/0 AWG	1672/30	.080 (2.0)	.240 (6.1)	1.890 (48.0)	306	15 (381.0)	2852 (4246)
K13348C	4	3/0 AWG	1672/30	.080 (2.0)	.240 (6.1)	2.070 (52.6)	244	17 (431.8)	3611 (5376)
K13343C	3	4/0 AWG	2107/30	.080 (2.0)	.170 (4.3)	2.040 (51.8)	352	16 (406.4)	3458 (5148)
K13344C	4	4/0 AWG	2107/30	.080 (2.0)	.170 (4.3)	2.260 (57.4)	282	18 (457.2)	4546 (6768)
SINGLE CONDUCTOR CABLES (TYPE W 2000V)									
K13376C	1	8 AWG	168/30	.060 (1.5)	.075 (5.3)	.448 (11.4)	80	4 (101.6)	133 (198)
K13370C	1	6 AWG	266/30	.060 (1.5)	.095 (2.4)	.520 (13.2)	110	4 (101.6)	190 (283)
K13364C	1	4 AWG	420/30	.060 (1.5)	.095 (2.4)	.570 (14.5)	145	5 (127.0)	253 (376)
K13359C	1	2 AWG	665/30	.060 (1.5)	.095 (2.4)	.635 (16.1)	200	5 (127.0)	350 (521)
K13355C	1	1 AWG	836/30	.080 (2.0)	.095 (2.4)	.735 (18.7)	223	6 (152.4)	449 (668)
K13161C	1	1/0 AWG	1045/30	.080 (2.0)	.095 (2.4)	.780 (19.8)	265	6 (152.4)	535 (796)
K13162C	1	2/0 AWG	1330/30	.080 (2.0)	.095 (2.4)	.820 (20.8)	310	7 (177.8)	638 (949)
K13345C	1	3/0 AWG	1672/30	.080 (2.0)	.095 (2.4)	.850 (21.6)	365	7 (177.8)	759 (1129)
K13163C	1	4/0 AWG	2107/30	.080 (2.0)	.095 (2.4)	.980 (24.9)	420	8 (203.2)	940 (1399)
K13164C	1	250 kcmil	2499/30	.095 (2.4)	.095 (2.4)	1.065 (27.1)	460	9 (228.6)	1113 (1656)
K13165C	1	300 kcmil	2989/30	.095 (2.4)	.095 (2.4)	1.150 (29.2)	525	9 (228.6)	1300 (1985)
K13341C	1	400 kcmil	3990/30	.095 (2.4)	.095 (2.4)	1.260 (32.0)	645	10 (254.0)	1669 (2484)
K13167C	1	500 kcmil	5054/30	.095 (2.4)	.095 (2.4)	1.375 (34.9)	730	11 (279.4)	2059 (3064)
K23647C	1	600 kcmil	5985/30	.110 (2.8)	.095 (2.4)	1.540 (39.1)	810	12 (304.8)	2453 (3650)
K23648C	1	750 kcmil	7581/30	.110 (2.8)	.095 (2.4)	1.690 (42.9)	918	14 (355.6)	3024 (4500)
K13340C	1	1000 kcmil	10101/30	.110 (2.8)	.095 (2.4)	1.830 (46.5)	1095	15 (381.0)	3888 (5786)

¹Ampacity based on single cable in free air 30°C ambient, 90°C conductor temperature.
 ALL-TEMP INDUSTRIRITE® color code: 1) Black 2) White 3) Red 4) Green 5) Orange 6) Blue
 The data herein is approximate and subject to normal manufacturing tolerances.

© DRAKA - A Brand of The Prysmian Group. 2017 All Rights Reserved. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend any specifications without notice. These specifications are not contractually valid unless authorized by Prysmian Group. Issued May 2017.

Prysmian Group
 700 Industrial Drive | Lexington, SC 29072 | +1-800-845-8507 | na.prysmiangroup.com
Sales and Distribution:
 22 Joseph E. Warner Blvd. | North Dighton, MA 02764 | +1-508-822-5444