



CS34ZC Category 6 U/UTP Cable, low smoke zero halogen, white jacket, 4 pair count, 305 m length CommPak® box


Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair cable
Regional Availability	EMEA

Standards And Qualifications

EN50575 CPR Cable EuroClass	Cca s1a d1 a1
------------------------------------	---------------------

Cross Section Drawing



Construction Materials

Jacket Material	Low Smoke Zero Halogen (LSZH)
Conductor Material	Bare copper
Insulation Material	Polyolefin
Separator Material	Polyolefin

Dimensions

Cable Length	305 m 1001 ft
Cable Weight	25.60 lb/kft
Diameter Over Jacket, nominal	5.918 mm 0.233 in
Jacket Thickness	0.559 mm 0.022 in

Electrical Specifications

ANSI/TIA Category	6
Characteristic Impedance	100 ohm
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	7.61 ohms/100 m
Delay Skew, maximum	45 ns
Mutual Capacitance	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	69 %
Operating Frequency, maximum	250 MHz
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class E
Dielectric Strength, minimum	1500 Vac 2500 Vdc
Note	All electrical transmission tests include swept frequency measurements

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Smoke Test Method	IEC 61034-2
Acid Gas Test Method	EN 50267-2-3
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Packaging Type	CommPak® box
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	White
Product Number	CS34ZC
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Separator Type	Tape separator

Mechanical Specifications

Pulling Tension, maximum 11 kg | 25 lb

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

CENELEC

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

EN 50575 compliant, Declaration of Performance (DoP) available



Electrical Performance

CS	CommScope
Std	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above
IL	Insertion Loss (dB/100m)
NEXT	Near End Crosstalk (dB/100m)
ACR	Attenuation to Crosstalk Ratio (dB/100m)
PSNEXT	Power Sum Near End Crosstalk (db/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)
ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
PSACRF	Power Sum Attenuation to Crosstalk Ratio – Far End (dB/100m)
RL	Return Loss (dB)
TCL	Transverse Conversion Loss (dB/100m)
ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL		TCL		ELTCTL	
	CS	Std	CS	Std	CS	Std	CS	Std	CS	Std	CS	Std	CS	Std	CS	Std	CS	Std	CS	Std
1	2.0	2.0	75.3	74.3	73.3	72.3	72.3	72.3	70.3	70.3	68.0	67.8	65.0	64.8	20.0	20.0	40.0	40.0	35.0	35.0
4	3.8	3.8	66.3	65.3	62.5	61.5	63.3	63.3	59.5	59.5	56.0	55.8	53.0	52.8	23.0	23.0	40.0	40.0	23.0	23.0
8	5.3	5.3	61.8	60.8	56.4	55.4	58.8	58.8	53.4	53.4	49.9	49.7	46.9	46.7	24.5	24.5	40.0	40.0	16.9	16.9
10	6.0	6.0	60.3	59.3	54.3	53.3	57.3	57.3	51.3	51.3	48.0	47.8	45.0	44.8	25.0	25.0	40.0	40.0	15.0	15.0
16	7.6	7.6	57.2	56.2	49.7	48.7	54.2	54.2	46.7	46.7	43.9	43.7	40.9	40.7	25.0	25.0	38.0	38.0	10.9	10.9
20	8.5	8.5	55.8	54.8	47.3	46.3	52.8	52.8	44.3	44.3	42.0	41.8	39.0	38.8	25.0	25.0	37.0	37.0	9.0	9.0
25	9.5	9.5	54.3	53.3	44.8	43.8	51.3	51.3	41.8	41.8	40.0	39.8	37.0	36.8	24.3	24.3	36.0	36.0	7.0	7.0
31.25	10.7	10.7	52.9	51.9	42.2	41.2	49.9	49.9	39.2	39.2	38.1	37.9	35.1	34.9	23.6	23.6	35.1	35.1		
62.5	15.4	15.4	48.4	47.4	33.0	32.0	45.4	45.4	30.0	30.0	32.1	31.9	29.1	28.9	21.5	21.5	32.0	32.0		
100	19.8	19.8	45.3	44.3	25.5	24.5	42.3	42.3	22.5	22.5	28.0	27.8	25.0	24.8	20.1	20.1	30.0	30.0		
155	25.2	25.2	42.4	41.4	17.3	16.3	39.4	39.4	14.3	14.3	24.2	24.0	21.2	21.0	18.8	18.8	28.1	28.1		
200	29.0	29.0	40.8	39.8	11.8	10.8	37.8	37.8	8.8	8.8	22.0	21.8	19.0	18.8	18.0	18.0	27.0	27.0		
250	32.8	32.8	39.3	38.3	6.5	5.5	36.3	36.3	3.5	3.5	20.0	19.8	17.0	16.8	17.3	17.3	26.0	26.0		