

MIC® Tight Buffer Indoor Cable

24F G50 MMF ClearCurve® OM3 0.9mm TB3, Cca-s1a,d1,a1

CORNING

Corning LANscape® indoor cables can be deployed indoor as building backbone (riser) cabling as well as for the cabling between floor distributors.

The tight-buffered construction facilitates easier termination for low-fibre-count applications in the local area network (LAN) and eliminates need for fan-out kits.

The cables can be installed in conduits and shafts inside buildings.

Features and Benefits

All-dielectric cable construction

Requires no grounding or bonding

Small diameter and bend radius

Easy installation in space-constrained areas

TB3 tight buffered construction

Easy and consistent stripping over 10cm

Silicon-free outer jacket

The cable jacket and the outer jacket of subunits (not valid for 900µm tight buffers) are free of harmful to paint structures

Flame retardant

LSZH™/FRNC

Standards

Flame Test Method

Flame retardant to IEC 60332-1-2 (single cable); IEC 60332-3-24 (bunch of cables)

Reaction to fire according to EN 50575 and EN 13501-6

Low Smoke to IEC 61034 and Zero Halogen to IEC 60754-1

Non Corrosive to IEC 60754-2

MIC[®] Tight Buffer Indoor Cable

24F G50 MMF ClearCurve[®] OM3 0.9mm TB3, Cca-s1a,d1,a1

CORNING

Specifications

General Specifications	
Environment	Indoor
Application	Vertical Riser, General Purpose Horizontal, Indoor horizontal, General building applications
Cable type	Tight buffered
Product type	Dielectric
Flame rating	LSZH [™] /FRNC
Fibre Category	50 µm MM (OM3)
Coding according to EN 60794-1-1 (DIN VDE 0888-100-1)	J-V(ZN)H
Previous part number	LCXLI2-L5024-H700
Previous coding following DIN VDE 0888-3	J-VH
Product category	Core product / Fastship
Reaction to fire	Cca -s1a,d1,a1

Temperature Range	
Installation and assembly	-5 °C to 50 °C
Operation	-20 °C to 60 °C
Storage	-25 °C to 70 °C

Cable Design	
Central Element	Aramid yarn
Fibre Count	24
Buffering Diameter	900 µm
Tight Buffer Type	TB3 (strippable up to 10 cm)
Tight buffer colour, layer 1	Blue, Orange, Green, Brown, Grey, White, Red, Black, Yellow
Tensile Strength Elements and/or Armouring - Layer 1	Aramid yarn
Tight buffer colour, layer 2	Violet, Pink, Turquoise, Blue*, Orange*, Green*, Brown*, Grey*, White*, Red*, Black*, Yellow*, Violet*, Pink*, Turquoise*
Tensile strength elements and/or armouring - Layer 2	Aramid yarn
Number of ripcords	1
Outer jacket material	Flame-retardant, non-corrosive/low-smoke, zero-halogen (FRNC/LSZH) material
Outer jacket colour	Turquoise

MIC® Tight Buffer Indoor Cable

24F G50 MMF ClearCurve® OM3 0.9mm TB3, Cca-s1a,d1,a1

CORNING

Cable Design

Outer jacket nominal thickness	0.8 mm
Cable marking	Metre - Handset - CE 17 EN 50575 Cca-s1a,d1,a1 - Sine - CORNING - Fibre Optic Cable - Year - MIC(R) J-V(ZN)H 24 OM3CC TB3 0.9 LSZH(TM)/FRNC

Notes: Fibres indicated by * have black rings (white with double ring replaces black with single ring)

Mechanical Characteristics Cable

Nominal Outer Diameter	8 mm
Weight	59 kg/km
Min. Bend Radius Installation	120 mm
Min. Bend Radius Operation	80 mm
Max. tensile strength for installation	1000 N
Crush resistance (reversible)	1000 N/10 cm
Fire Load	1.13 MJ/m

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Fibre Specifications

Optical Characteristics (cabled)

Fibre name	G50/125 ULTRA-BEND 7.5
Fibre code	T
Fibre core diameter	50 µm
Fibre Category	OM3
Wavelengths	850 nm / 1300 nm
Maximum attenuation	2.8 dB/km / 1.0 dB/km
Typical attenuation	2.4 dB/km / 0.8 dB/km
Serial 1 gigabit ethernet	1000 m / 600 m
Serial 10 gigabit ethernet	300 m / 333 m
Min. overfilled launch (OFL) bandwidth	1500 MHz*km / 500 MHz*km
Minimum effective modal bandwidth (EMB)	2000 MHz*km / -
Induced attenuation @ 7.5 mm radius	< 0.2 dB / -

MIC® Tight Buffer Indoor Cable

24F G50 MMF ClearCurve® OM3 0.9mm TB3, Cca-s1a,d1,a1

CORNING

Notes: 1) 50 µm multimode fibre macrobend loss ≤ 0.2 dB at 850 nm for two turns around 7.5 mm radius mandrel
2) Meets 0.75 ns optical skew when used in all Corning Plug and Play™/EDGE™ systems solutions.
3) Improved attenuation and bandwidth options available
4) Bend-insensitive single-mode fibres available on request.
5) Contact a Corning Customer Care Representative for additional information

Ordering Information

Part Number	024T8Z-32188E2G
Product Description	MIC® Tight Buffer Indoor Cable 24F G50 MMF ClearCurve® OM3 0.9mm TB3, Cca-s1a,d1,a1
EAN Code	4042673326496

Shipping Information

Maximum delivery length	2,000 m
-------------------------	---------



Corning Optical Communications GmbH & Co. KG · Leipziger Strasse 121 · 10117 Berlin, GERMANY

00 800 2676 4641 · FAX: +49 30 5303 2335 · www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified.

© 2017 Corning Optical Communications. All rights reserved.

CORNING