

LIFETIME

00

WARRANTY

EXCLUSIVE

SUBSTATION

RLFDX(485,232)M2/(24DC,48DC,HV) Series

HARDENED

-40° to 85° C

 $TX \leftrightarrow F)$

ELECTRICAL

OPTICAL

CONVERTER



The ComNet RLFDX series of serial data link/repeaters are substation-rated and industrially hardened form, fit, function and completely backwards-compatible replacements for the popular Garrettcom/Dymec 5843, 5844, 5845, and 5846-series of serial data link/repeaters. They are designed for deployment in environments where high levels of electromagnetic noise and interference (EMI) and severe voltage transients and surges are routinely encountered, such as electrical utility substations and switchyards, heavy manufacturing facilities, trackside and roadside electronic equipment, and other difficult out-of-plant applications. Optical connectivity provides significantly extended transmission distances compared to copper media; high levels of electrical isolation; enhanced reliability and protection for peripheral IEDs, RTUs, and other equipment; and operational safety.

CLASS 1 DIV 2

The RLFDX series of serial data link/repeaters are easily field-configurable for point-to-point, pointto-multipoint/master-slave, loop, or bus topologies. They may be also used for electrical data protocol conversion: an RLFDX232 RS-232 modem and IED/RTU can communicate directly with an RLFDX485 RS-422/RS-485 modem and IED/RTU.

The extremely versatile and simple-to-install RLFDX series is ideal for any mission-critical application where very high levels of reliability and network availability are of the utmost importance.

FEATURES

- Fully electrically, mechanically, and optically identical to and backward-compatible with the Garrettcom/Dymec 5843, 5844, 5845, and 5846 Series. A ComNet RLFDX may directly replace a Dymec unit anywhere within the network.
- > Full-duplex, half-duplex, or simplex transmission of RS-232, RS-422, RS-485 2/4-wire data, or TTL logic
- > Tested and certified to meet or exceed the requirements of IEEE 1613 Class 2 for electrical utility substations
- > RS-232 Version: DTE/DCE switching
- Diagnostic test mode feature tests the copper and optical connections before the connected IED or RTU is active within the network.
- Extended ambient operating temperature range of -40° to +85° C, with no fan/forced air cooling, for use in virtually any environment
- > Optical transmission distances of up to 5 km
- > +9 to 36 VDC, +/-36 to 59 VDC, or HV AC/DC (+/-88 to 300 VDC/85-264 VAC) operating power options. HV DC input permits operation directly from station battery bus power.
 48 VDC and HV models' DC inputs are isolated from ground, allowing operation from positive or negative DC sources.
- Internal/self-contained high-reliability power supply a screw terminal block connects directly to the power source for permanent, reliable, and maintenance-free operation
- > LED status indicators confirm operating status
- > Rugged galvannealed and powder-coated panel-mount enclosure

- > IP-30 rated for ingress protection (2.5 mm objects)
- Conformal coating of the circuit boards is optionally available, for use in humidity with condensation conditions (extra charge, see ordering information).
- › Made in the USA
- > Lifetime Warranty

APPLICATIONS

- Electrical substation automation & SCADA networks, protective relaying systems
- Power transmission & distribution systems, remote wind farm, hydroelectric, and solar/photovoltaic power generation facilities, and other electrical utility-specific applications
- Controlled access to electrical substations and power generating facilities, and other high-value, mission-critical sites
- Industrial/Factory Automation & Process Control SCADA Networks
- Chemical and petrochemical refining and processing facilities, oil and gas pipelines/transmission systems, and mining installations
- › Food processing operations
- > Wastewater treatment plants
- > Railway/trackside control and monitoring systems
- > ITS/Transportation traffic signalization networks
- > Integrated data transmission networks

SPECIFICATIONS (RS232 Models)

Data

Data Rate	DC to 250 kbps
Data Transmission	Asynchronous, simplex OR Full Duplex
Bit Error Rate	10-E9 Max.
Point to Point Latency	4 μS
Repeat Latency	400 nsec Max.

Fiber Optical Parameters

(At Maximum Operating Terr	iperature)
Optical Budget Typical	19.5dB
Output Power Typical	-10.5 dBm peak
Receiver Sensitivity Typical	-30 dBm peak (62.5 μ/125)
Wavelength	850 nm
Transmission Distance	Up to 5 km (62.5 µ/125 Cable @ 3 dB/km)
Compatible Fiber Type	50-200 μm

Configuration Switches

DTE/DCE AC/DC Coupled Link/Repeat Pin 8 Drive Current Pin 6 +5 VDC (DSR or CTS pull up) **Diagnostic Mode**

Connectors

Optical	ST
Data	DB-9 (9 Pin D-Type Female)
Power	Removable, 3-pin Screw Terminal Block

Electrical Parameters

```
Inputs
  I/O Data Format
  Input Impedance
  Input Voltage
Outputs
  Output Impedance
  Driver Output
  Pin 8 Output
```

EIA RS232; CCITT v.24 >3000 Ω +/-30 Volts Max. >300 Ω

+/- Volts into 3000 Ω 0 to 5 V 67 or 207 Ω Source Impedance

Power Required

24 VDC 48 VDC ΗV

Mechanical

+9 to 36 VDC @ 250 mA (3W) +/-36 to 59 VDC @ 250 mA (4W) +/-88 to 300 VDC @ 35 mA (4 W) or 85 to 264 VAC @ 35 mA (4 W)

Power Dissipation BTU/H

24 VDC HV & 48 VDC

Indicating LEDs

Circuit Board

Actual Weight

8.2 BTU/hr 10.9 BTU/hr

Power Transmit Fiber **Transmit Electrical Receive Fiber Receive Electrical** Meets IPC Standard HV & 48 VDC: 1.06 lb / 0.48 kg 24 VDC: 0.56 lb / 0.26 kg

Dimensions ($W \times L \times H$) HV & 48 VDC: 24 VDC:

Environmental

MTBF **Operating Temperature** Storage Temperature **Relative Humidity**

 $4.1\times5.1\times1.3$ in (10.41 \times 12.95 \times 3.3 cm) 2.0 × 5.1 × 1.3 in (5.08 × 12.95 × 3.3 cm)

>250,000 hours -40°C to +85°C -40°C to 85°C

0% to 95% (non-condensing)¹

ORDERING INFORMATION (RS-232/TTL Models)

Model	Data Format	Fiber Type	Input Power	Equivalent Dymec Model
RLFDX232M2/24DC	RS-232/TTL	Multimode	9 to 36 VDC	5843HRT
RLFDX232M2/HV	RS-232/TTL	Multimode	88 to 300 VDC / 85 to 264 VAC	5844HRT-H
RLFDX232M2/48DC	RS-232/TTL	Multimode	36 to 59 VDC	5844HRT-L
Options	[1] Add suffix '/C' for Conformally Coated Circuit Boards to extend to condensation conditions (Extra charge, consult factory)			

NOTE: This product requires a fiber installation with a minimum 30 dB connector return loss. The use of Super Polish Connectors is recommended. Complies with FDA Performance Standard for Laser Products, Title 21, Code of Federal Regulations, Subchapter J In a continuing effort to improve and advance technology, product specifications are subject to change without notice.

SPECIFICATIONS (RS422/485 Models)

Data

Data Rate	DC to 2 Mbps
Data Transmission	Asynchronous, simplex OR Full Duplex
Bit Error Rate	10-E9 Max.
Point to Point Latency	500 nsec Max.
Repeat Latency	400 nsec Max.

Fiber Optical Parameters

(At Maximum Operating Tem	perature)
Optical Budget Typical	19.5 dB
Output Power Typical	-10.5 dBm peak
Receiver Sensitivity Typical	-30 dBm peak (62.5 μ/125)
Wavelength	850 nm
Compatible Fiber Type	50-200 μm
Transmission Distance	Up to 5 km (62.5 µ/125 Cable @ 3 dB/km)
Configuration Switches	Half/Full Duplex
	AC/DC
	Link/Repeat
	Biasing Resistors In/Out

Data Inversion Mode Enable Holdover (4 settings) Diagnostic Mode

Connectors

Optical	
Data	
Power	

ST DB-9 (9 Pin D-Type Female) Removable, 3-pin Screw Terminal Block

Electrical Parameters

Inputs			
I/O Data Format	EIA 422/485		
Input Impedance	750 Ω		
Input Voltage	+12 to -7 Volts Max referenced to signal common		
	+/-6 Volts differential Max		
Outputs			
Output Impedance	>250 Ω		
Driver Output	50 mA		
Power Required			
24 VDC	+9 to 36 VDC @ 250 mA (3 W)		
48 VDC	+/-36 to 59 VDC @ 250 mA (4 W)		
HV	+/-88 to 300 VDC @ 35 mA (4 W)		
	or 85 to 264 VAC @ 35 mA (4 W)		
Power Dissipation BTU/	'H		
24 VDC	10 BTU/hr		
HV & 48 VDC	20 BTU/hr		
Mechanical			
Indicating LEDs	Power Transmit Fiber Transmit Electrical		
J AND J	Receive Fiber Receive Electrical		
Circuit Board	Meets IPC Standard		
Actual Weight	HV & 48 VDC: 1.06 lb / 0.48 kg		
5	24 VDC: 0.56 lb / 0.26 kg		
Dimensions (W \times L \times H)	-		
HV & 48 VDC:	4.1 × 5.1 × 1.3 in (10.41 × 12.95 × 3.3 cm)		
24 VDC:	2.0 × 5.1 × 1.3 in (5.08 × 12.95 × 3.3 cm)		
Environmental			
MTBF	>250,000 hours		
Operating Temperature	-40°C to +85°C		
Storage Temperature	-40°C to 85°C		
Relative Humidity	0% to 95% (non-condensing) ¹		

ORDERING INFORMATION (RS-422/RS-485 Models)

Model	Data Format	Fiber Type	Input Power	Equivalent Dymec Model
RLFDX485M2/24DC	RS-422/485	Multimode	9 to 36 VDC	5845HRT
RLFDX485M2/HV	RS-422/485	Multimode	88 to 300 VDC / 85 to 264 VAC	5846HRT-H
RLFDX485M2/48DC	RS-422/485	Multimode	36 to 59 VDC	5846HRT-L
Options	[1] Add suffix '/C' for Conformally Coated Circuit Boards to extend to condensation conditions (Extra charge, consult factory)			

NOTE: This product requires a fiber installation with a minimum 30 dB connector return loss. The use of Super Polish Connectors is recommended. Complies with FDA Performance Standard for Laser Products, Title 21, Code of Federal Regulations, Subchapter J In a continuing effort to improve and advance technology, product specifications are subject to change without notice.



3 CORPORATE DRIVE | DANBURY, CONNECTICUT 06810 | USA | T: 203.796.5300 | F: 203.796.5303 | TECH SUPPORT: 1.888.678.9427 | INFO@COMNET.NET

Communication Networks 8 TURNBERRY PARK ROAD GILDERSOME MORLEY LEEDS, UK LS27 7LE T: +44 (0)113 307 6400 F: +44 (0)113 253 7462 INFO-EUROPE@COMNET.NET

© 2017 Communication Networks. All Rights Reserved. "ComNet" and the "ComNet Logo" are registered trademarks of Communication Networks.

OUTLINE & INSTALLATION DWG. A For Models: RLFDX232M2/24DC RLFDX485M2/24DC



16 Nov 2017



OUTLINE & INSTALLATION DWG. B



Low Power Consumption



For Models:

RLFDX232M2/HV

RLFDX485M2/HV

RLFDX232M2/48DC

RLFDX485M2/48DC

3 CORPORATE DRIVE | DANBURY, CONNECTICUT 06810 | USA | T: 203.796.5300 | F: 203.796.5303 | TECH SUPPORT: 1.888.678.9427 | INFO@COMNET.NET

Communication Networks 8 TURNBERRY PARK ROAD | GILDERSOME | MORLEY | LEEDS, UK LS27 7LE | T: +44 (0)113 307 6400 | F: +44 (0)113 253 7462 | INFO-EUROPE@COMNET.NET

© 2017 Communication Networks. All Rights Reserved. "ComNet" and the "ComNet Logo" are registered trademarks of Communication Networks.