

Model: A11-V43-100 A11-V43-101

The A11-V43-100 Wideband Indoor Dome Server Antenna receives and transmits signal in a 360° pattern and are compatible with the 698 – 2700 MHz frequency ranges that include 3G and 4G signals. Available with either an N-type or SMA connector.

FEATURES

- 3G/4G/LTE wideband cellular antenna
- Omni-directional

SPECIFICATIONS

ELECTRIC SPECIFICATION

Frequency Range	698-960 MHz	1710-2700 MHz
Gain	2.5dBi	3.5dBi
VSWR	≤1.8	≤1.5
Polarization	Vertical	
Horizontal Beamwidth	360°	
Vertical Beamwidth	90°/55°	
Input Impedance	50 Ω	
Max.Power	50 W	

MECHANICAL SPECIFICATION

Connector Types (A11-V43-100)	SMA male
(A11-V43-101)	N-type female
Cable	2m coax
Dimensions	Ø186×86 mm
Packing Size	170×180×180 mm
Weight	0.25 kg
Reflector Material	Aluminum
Radome Material	ABS
Operating Temperature	-40°C to +65 °C

Copyright © 2018 by Nextivity, Inc, U.S. All rights reserved. The Nextivity and Cel-Fi logos are registered trademarks of Nextivity Inc. All other trademarks or registered trademarks listed belong to their respective owners. Designed by Nextivity in California. brief-Antenna-OmniDirectional-Eng_18-1101

