

49-in. 4K LCD Monitor

Ultra High-definition Monitor



- 4K Ultra High-definition Resolution
- Industrial Level DID LCD Panel for Continuous Operation
- High-fidelity Digital Signal Processing for Vivid Video
- Built-in 3D Comb Filter and 3D Noise Reduction
- Fast Response Time (8 ms) with no Image Ghosting
- 16.7 Million Colors
- Smart Brightness Detection and Smart Power
- Supports HDMI, DVI, VGA, CVBS, USB Video Input













Technical Specification

System

Viewable Picture Area	48.5 in. (measured diagonally)
Aspect Ratio	16:9
Resolution	3840 x 2160 (UHD)
Backlight	LED
Brightness/Luminance	500 cd/m ²
Contrast	1100:1
Angle of View	Horizontal: 178° Vertical: 178°

Interface

Standard Inputs	 Two (2) HDMI One (1) VGA (D-sub) One (1) CVBS (BNC) One (1) DVI-D One (1) RS232 One (1) USB
Optional Inputs	 One (1) Audio (RCA) One (1) RJ-45 One (HDCVI) One (1) SDI One (1) DP


Electrical

Power Supply	100 VAC to 240 VAC (±10%), 50/60 Hz
Consumption	Standard: 70 W Standby: ≤ 1 W

Construction/Environmental

Dimensions (without base)	1127.10 x 667.30 mm x 51.90 mm (44.37 in. x 26.27 in. x 2.04 in.)
VESA	300 mm x 300 mm (11.81 in. x 11.81 in.)
Weight	18.0 kg (39.68 lb)
Operating Temperature	0 °C to 50 °C (32 °F to 122 °F)

Dimensions (mm/in.)



Rear Panel

AC100 ~ 240V 1.2A 50/60 HZ	ON										
AC IN	OFF		0			(C)			44		
	•	- €-	Hamii	Hami2	DVI-D	VGA	CVBS	AUDIO-IN	AUDIO-007	LAN in	LAN out
<u>F</u> SOM®					0	00	0	0	0	•••••	