

12 MP 3.7 mm to 16 mm Vari-focal Lens



- 12 MP 1/1.7-in. Image Format
- 3.7 mm to 16 mm Vari-focal Lens
- CS-type Mount
- IR Correction
- Designed for Extreme Temperature Environments

Technical Specifications

Image Format	1/1.7-in.
Focal Length	3.7 mm to 16 mm
Resolution	12 MP
Aperture	F1.5
Mount	CS
Field of View (D x H x V)	Wide: 145.0° x 109.0° x 79.0° Tele: 35.6° x 28.5° x 21.4°
Lens Control	Focus: Manual Zoom: Manual Iris: DC-Iris
IR Correction	Supported
Minimum Object Distance	0.50 m (1.64 ft)
Dimensions	ø54.0 mm x 82.85 mm (ø2.12 in. x 3.26 in.)
Weight	0.27 kg (0.60 lb)
Operating Temperature	-30° C to 70° C (-22° F to 158° F)
Operating Humidity	< 90% RH

Certifications

Electromagnetic Compatibility (EMC)	FCC 47 CFR Part 15 Subpart B ANSI C63.4 EN 55032, EN 55024, EN50130-4
-------------------------------------	---

Ordering Information

Type	Part Number	Description
Lens	DH-PLZ20C0-D	12 MP 1/1.7-in. 3.7 mm to 16 mm Vari-focal Lens

Dimensions (mm/in.)

