

Pole Mount Bracket



- SECC and SUS304 Stainless Steel Construction
- Designed for Reliability and Aesthetics

Technical Specifications	
Material	SECC and SUS304 Stainless Steel
Dimensions (W x H x D)	134.0 mm x 170.0 mm x 45.0 mm (5.13 in. x 6.69 in. x 1.77 in.)
Compatible Mast Diameter	ø80 mm to ø150 mm (ø3.15 in. to ø5.91 in.)
Weight	1.10 kg (2.34 lb)
Load Bearing Capacity	10.0 kg (22.05 lb)
Operating Temperature	−40 °C to 60 °C (−40 °F to 140 °F)
Humidity	0% to 90% RH

Ordering Information		
Type	Part Number	Description
Pole Mount	PFA150	Pole Mount Bracket
Package Contents	1	Pole Mount Bracket
	4	M8 x 25 Screws
	1	Hex Wrench
	3	80 mm to 150 mm Metal Hoops

