



WYE TAP SPLICE (HVSY) FOR 1/C POLY-POLY, PILC-PILC, AND PILC-POLY CABLE (15 KV)

KEY FEATURES

- Internal moisture seals provide a redundant seal against water intrusion
- Splices accept a wide range of main and tap cable sizes
- Qualified to IEEE 404
- Compact shape simplifies cable training

TE Connectivity's (TE) Raychem HVSY-1520S series tap splices are for use on copper tape, wire shield, lead sheath, and UniShield cables.

HVSY-1580D series is for use as a wye splice where the main and/or tap cables may be paper-insulated, lead-covered (PILC) cable; varnished cambric-insulated, or lead-covered (VCLC) cable.

TE's HVSY series is designed to seal against moisture ingress by including a branch clip and the heavy-duty MBSM wraparound sleeve

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



PRODUCT SELECTION INFORMATION: DIMENSIONS IN INCHES (mm)								
Description	POLY Conductor Size (AWG/kcmil)		Insulation Diameter (min. - max.)		Connector Length (max)	Kit Installed Length	Required Installation Space	Burndy Connector
	Main	Tap	Main	Tap				
HVSY-1520S (15 kV Polymeric Wye, for use with Soldered Connectors)								
HVSY-1522S	#2 - 4/0	#2 - 4/0	0.65 - 1.05 (17 - 27)	0.65 - 1.05 (17 - 27)	3.0 (75)	30 (750)	45 (1125)	
HVSY-1523S	250 - 750	#2 - 750	0.95 - 1.45 (24 - 37)	0.65 - 1.45 (17 - 37)	3.5 (90)	30 (750)	45 (1125)	
HVSY-1520S (15 kV Polymeric Wye, for use with Burndy YSH Crimp Connectors for Copper Conductors only)								
HVSY-1522S	#2 - 4/0	#2 - 4/0	0.65 - 1.05 (17 - 27)	0.65 - 1.05 (17 - 27)	3.0 (75)	30 (750)	45 (1125)	YSH-2929
HVSY-1523S	250 - 500	4/0 - 500	0.85 - 1.25 (22 - 32)	0.85 - 1.25 (22 - 32)	3.5 (90)	30 (750)	45 (1125)	YSH-3434
HVSY-1523S	500 - 750	350 - 750	1.10 - 1.45 (28 - 37)	1.00 - 1.45 (25 - 37)	3.5 (90)	30 (750)	45 (1125)	YSH-3939
HVSY-1580D (15 kV PILC and PILC-Poly Wye)								
HVSY-1582D	#2 - 4/0	#2 - 4/0	0.65 - 1.05 (17 - 27)	0.65 - 1.05 (17 - 27)	1.20 (30)	3.0 (75)	30 (750)	45 (1125)
HVSY-1583D	250 - 750	#2 - 750	0.95 - 1.45 (24 - 37)	0.65 - 1.45 (17 - 37)	1.50 (38)	3.5 (90)	30 (750)	45 (1125)

* All selections are based on the typical dimensions of 100% and 133% insulated cables and dimensions of commonly used connectors manufactured in accordance with AEIC. Kits do not contain connectors. For connector information contact your local TE sales representative for information. For HVSY-1520S kits with copper conductors only, H-tap compressed connectors, available from Burndy (800-346-4175), may be used in place of the half-duplex connector. For 15 kV H-configuration connections on 1/C shielded power cable, order the HVSH-1520 mod kit for use in conjunction with appropriate HVSY-1520S kit.

ORDERING INFORMATION

1. Select the appropriate catalog number. All selections are based on the typical dimensions of 100% and 133% insulated cables and dimensions of commonly used connectors manufactured in accordance with AEIC standard. Nominal Insulation thickness (100%): 165 mils (PILC/VCLC) 175 mils (poly). Nominal thickness (133%): 220 mils (poly).
2. For cables manufactured to other specifications, confirm selection with cable and connector dimensions.
3. Kits do not contain connectors. For connector information, contact your local TE sales representative. For HVSY-1520S kits with copper conductors only, H-tap, compressed connectors, available from Burndy (800-346-4175), may be in place of the half-duplex connector.
4. Check poly cable insulation diameter to help ensure a proper fit.
5. For 15 kV H-configuration connections on 1/C shielded power cable, order the HVSH-1520 mod kit for use in conjunction with appropriate HVSY-1520S kit.
6. Standard package: 1 kit/box.

TEST REPORT

HVSY-1520S: EDR-5236, EDR-5256
 HVSY-1580D: EDR-5235

te.com/energy

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved. E576 10/2014

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA: +1 800 327 6996
 France: +33 380 583 200
 UK: +44 0870 870 7500
 Germany: +49 896 089 903
 Spain: +34 916 630 400
 Benelux: +32 16 351 731
 Canada: +1 (905) 475-6222
 Mexico: +52 (0) 55-1106-0800
 Latin/S. America: +54 (0) 11-4733-2200
 China: +86 (0) 400-820-6015