

Glazed Lantern

Architectural exterior LED lighting

- Stylish contemporary design
- Durable die-cast aluminium construction
- Toughened glass lantern with E27 lamp holder
- IP54 protection against dust and moisture
- Matching colour temperature and finish to the Architectural Exterior range
- Suitable for use with LED lamps



NEW

New product
for 2018



3 year
ext. warranty*



See p. 291
for matching bollard



^ Rubber gasket lamp holder

Classification

⚡ Class 1
IP54 | 240V

Lamp

E27 15W Max
Lamp not supplied


Finishes

Anthracite (**BLK**), White (**WH**)

Construction

Body: Aluminium
Diffuser: Glass

JC17007



Code **Description**

JC17007 Glazed Lantern

For Anthracite add **BLK** suffix, for White add **WH** suffix

*Requires online registration.

All data sheets and installation sheets
available at jcc.co.uk