


Best Surveillance Storage for SMB/Client Viewer

Vess A3120



Features

Optimized for Surveillance

Storage appliance optimized for IP video surveillance.


Small Installation & SMB

Ideal for less than 64ch full-HD IP cameras, perfect for banking, retail, prison, hotel, and more.

Easy to Administer & Maintain

Hot swappable drive bays, and One Plug Auto Service (OPAS) ensure Vess is easy to administer and maintain.

Promise Alliance Partners



Optimized for Video Surveillance

PROMISE proprietary SMARTBOOST™ Technology provides the most stable and high performance storage solution for your system. Promise SMARTBOOST™ Technology significantly improves performance that is otherwise limited by storage equipment bottlenecks. SMARTBOOST™ Technology provides the best stability and performance with the best C/P ratio.

Storage Appliances + Client Viewer provides Wider Applications

PROMISE Vess A3120 is a Storage Appliance for SMB/small installation video surveillance recording. It includes a Client Viewer for applications that require 24/7 monitoring. It is certified for several VMS for a complete surveillance system solution, using varied software features across multiple VMS.

Built-In GPU for better IVA Performance

Vess A3120 speeds up the graphic card performance and other processing using a built-in GPU, Intel Media SDK and thoroughly tested Graphic card implementation. Intelligent Video Analytics (IVA) has placed increased performance demands on surveillance systems; Vess A3120 handles basic recording AND better performing IVA tasks simultaneously.

4K Resolution Streaming Supported

4K camera support is an essential feature for areas that require high resolution camera monitoring. The Vess A3120 features 4K camera streaming for local display to provide high definition imaging of crucial areas.

Reduce the complexity of Maintenance by OPAS

One Plug Auto Service (OPAS) is a unique feature of Promise Vess App solutions that provides user convenience, reduces complexity for maintenance, and streamlines technical support. OPAS enables users to collect all the necessary logs and data used by the Promise support team to analyze the status of Vess A-Series Storage appliances.

Technical Specifications



Vess A3120

Model

| General Information | |
|----------------------------|--|
| Camera Range ¹ | 64 |
| Form Factor | 1U, 19" Rackmount |
| Number Of Drives | 4 Drives (3.5") |
| Drive Type | 6Gbs SATA @ 3.5" |
| # of Controllers | Single |
| System Processor | Intel® Core™ i3-7101E |
| System Memory | 4GB x 2 Default (Max 32GB) |
| I/O Interface | 2 x Gigabit Ethernet |
| Internal Storage (M.2) | 128GB |
| Storage Expansion | Optional Vess SAS and iSCSI Storage |
| Max # of HDDs Supported | Up to 112 drives through iSCSI/SAS JBOD expansion |
| Other Interfaces | |
| # of USB Ports | 5 x USB 3.0, 2 x USB 2.0 |
| PCI Express Ports | 1 x 8-lane Gen3 |
| Graphics | 1 x VGA, 1x HDMI, 1x Display Port |
| Serial Interfaces | 1 x Serial Port |
| Audio I/O | 3 x 3.5mm Audio Jack and SPDIF |
| RAID Operational Feature | |
| RAID Levels | 0, 1, 1E, 3, 5, 6, 10, Any combination can exist at the same time |
| Hot Spares | Multiple global or dedicated hot-spare drives with revertible option |
| Max. LUNs per System/Array | 256/32 |
| Software | |
| OS Supported (64-bit) | Windows 10 |
| Management Tools | Graphical UI/SNMP via Ethernet, CLI/CLU via Ethernet or Graphics, OPAS Service via USB, SDK or API for Integration |
| Appliance Mode | Surveillance Optimization @ Arrays in Normal and Degraded |
| Event Notification | Email, SNMP, Buzzer, LEDs |
| System Information | |
| AC Input | 100 ~ 240 VAC, 47 ~ 63Hz |
| Current (Maximum) | 7A |
| Power Supply | 350W Single ATX |
| Temperature | 5° ~ 40°C (-40° ~ 60°C non-operational) |
| Dimensions (H x W x D) | 44.2 x 446.4 x 398 mm |
| Weight | System W/O HDD: 6.48 kg System W/ HDD: 9.16 kg |
| Safety/EMI | CE, FCC, VCCI, RCM, (EMI Class A), cULus |
| Warranty and Support | |
| Warranty | 3 year limited warranty |
| Optional Accessories | Sliding Rail, 4/8/16 GB DDR Memory |

¹ The ideal camera ranges were output of fully populated enclosure by pure recording and 8GB memory under 30FPS, H.264, 5Mbps Bitrate and 1080P resolution

*The final spec may vary without further notice, please check with Promise website for the latest information

Contact us



© 2018 PROMISE Technology, Inc. All Rights Reserved. PROMISE, the PROMISE logo, VTrak, SmartStor, SuperTrak, FastTrak, VessRAID, Vess, PerfectPATH, PerfectRAID, SATA150, ULTRA133 VTrak S3000, BackTrak, HyperCache, HyperCache-R, HyperCache-W, DeltaScan and GreenRAID are registered or pending trademarks of PROMISE Technology, Inc. in the U.S. and other countries. All other trademarks are the property of their respective owners. Information regarding products, services and offerings may be superseded by subsequent documents and are subject to change without notice. For the latest information and specifications regarding PROMISE Technology, Inc. and any of its offerings or services, please contact your local PROMISE office or the corporate headquarters. Visit www.promise.com for more information on PROMISE products. P/N: G6130A312000000

2018 August

visit www.promise.com for more information on PROMISE products