



SAFETY DATA SHEET

1. Identification

Product identifier Isopropyl Alcohol Precision Cleaner

Other means of identification

Product code 03201

Recommended use Electronic cleaner

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufactured or sold by:

Company name CRC Industries, Inc.

Address 885 Louis Dr.
Warminster, PA 18974 US

Telephone

General Information 215-674-4300

Technical Assistance 800-521-3168

Customer Service 800-272-4620

24-Hour Emergency (CHEMTREC) 800-424-9300 (US)

703-527-3887 (International)

Website www.crcindustries.com

2. Hazard(s) identification

Physical hazards	Flammable aerosols	Category 1
	Gases under pressure	Liquefied gas
Health hazards	Serious eye damage/eye irritation	Category 2
	Specific target organ toxicity, single exposure	Category 3 narcotic effects
	Aspiration hazard	Category 1
Environmental hazards	Not classified.	
OSHA defined hazards	Not classified.	
Label elements		



Signal word Danger

Hazard statement Extremely flammable aerosol. Contains gas under pressure; may explode if heated. May be fatal if swallowed and enters airways. Causes serious eye irritation. May cause drowsiness or dizziness.

Precautionary statement

Prevention

Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Do not apply while equipment is energized. Pressurized container: Do not pierce or burn, even after use. Extinguish all flames, pilot lights and heaters. Vapors will accumulate readily and may ignite. Use only with adequate ventilation; maintain ventilation during use and until all vapors are gone. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing mist or vapor. Avoid breathing gas. Wash thoroughly after handling. Wear eye/face protection.

Response

If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention.

Storage

Store in a well-ventilated place. Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Exposure to high temperature may cause can to burst.

Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	Static accumulating flammable liquid can become electrostatically charged even in bonded and grounded equipment. Sparks may ignite liquid and vapor. May cause flash fire or explosion.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Isopropyl alcohol		67-63-0	70 - 80
1,1-Difluoroethane	HFC-152a	75-37-6	20 - 30

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Rinse skin with water/shower. Get medical attention if irritation develops and persists.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Irritation of nose and throat. Aspiration may cause pulmonary edema and pneumonitis. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Alcohol resistant foam. Water fog. Carbon dioxide (CO ₂). Dry chemical powder, carbon dioxide, sand or earth may be used for small fires only.
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Contents under pressure. Pressurized container may explode when exposed to heat or flame. This product is a poor conductor of electricity and can become electrostatically charged. If sufficient charge is accumulated, ignition of flammable mixtures can occur. Static electricity accumulation may be significantly increased by the presence of small quantities of water or other contaminants. Material will float and may ignite on surface of water. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire-fighting equipment/instructions	In case of fire: Stop leak if safe to do so. Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapor pressure build up.
General fire hazards	Extremely flammable aerosol. Contents under pressure. Pressurized container may explode when exposed to heat or flame.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Keep out of low areas. Remove all possible sources of ignition in the surrounding area. Many gases are heavier than air and will spread along ground and collect in low or confined areas (sewers, basements, tanks). Wear appropriate protective equipment and clothing during clean-up. Avoid breathing mist or vapor. Avoid breathing gas. Emergency personnel need self-contained breathing equipment. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Use appropriate containment to avoid environmental contamination. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. Stop the flow of material, if this is without risk. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS. Prevent entry into waterways, sewer, basements or confined areas.

Environmental precautions

Avoid discharge into drains, water courses or onto the ground. Use appropriate containment to avoid environmental contamination.

7. Handling and storage

Precautions for safe handling

Minimize fire risks from flammable and combustible materials (including combustible dust and static accumulating liquids) or dangerous reactions with incompatible materials. Handling operations that can promote accumulation of static charges include but are not limited to: mixing, filtering, pumping at high flow rates, splash filling, creating mists or sprays, tank and container filling, tank cleaning, sampling, gauging, switch loading, vacuum truck operations. Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. Use caution around energized equipment. The metal container will conduct electricity if it contacts a live source. This may result in injury to the user from electrical shock and/or flash fire. Avoid breathing mist or vapor. Avoid breathing gas. Avoid contact with eyes. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Observe good industrial hygiene practices. For product usage instructions, please see the product label.

Conditions for safe storage, including any incompatibilities

Level 2 Aerosol.

Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C/122 °F. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Avoid spark promoters. These alone may be insufficient to remove static electricity. Store in a well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits**US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)**

Components	Type	Value
Isopropyl alcohol (CAS 67-63-0)	PEL	980 mg/m3
		400 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
Isopropyl alcohol (CAS 67-63-0)	STEL	400 ppm
	TWA	200 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Isopropyl alcohol (CAS 67-63-0)	STEL	1225 mg/m3
		500 ppm
	TWA	980 mg/m3 400 ppm

US. AIHA Workplace Environmental Exposure Level (WEEL) Guides

Components	Type	Value
1,1-Difluoroethane (CAS 75-37-6)	TWA	2700 mg/m3
		1000 ppm

Biological limit values**ACGIH Biological Exposure Indices**

Components	Value	Determinant	Specimen	Sampling Time
Isopropyl alcohol (CAS 67-63-0)	40 mg/l	Acetone	Urine	*

* - For sampling details, please see the source document.

Appropriate engineering controls	Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Wear safety glasses with side shields (or goggles).
Skin protection	
Hand protection	Wear protective gloves such as: Neoprene. Polyvinyl alcohol (PVA).
Other	Wear suitable protective clothing.
Respiratory protection	If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
General hygiene considerations	When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Form	Aerosol.
Color	Clear. Colorless.
Odor	Alcoholic.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	-127.3 °F (-88.5 °C) estimated
Initial boiling point and boiling range	179.6 °F (82 °C) estimated
Flash point	54 °F (12.2 °C) Tag Closed Cup
Evaporation rate	Very fast.
Flammability (solid, gas)	Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%)	2 % estimated
Flammability limit - upper (%)	12 % estimated
Vapor pressure	2056.7 hPa estimated
Vapor density	2 (air = 1)
Relative density	0.82 estimated
Solubility (water)	Miscible.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	750.2 °F (399 °C) estimated
Decomposition temperature	Not available.
Viscosity (kinematic)	Not available.
Percent volatile	100 %

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.

Conditions to avoid	Heat, flames and sparks. Contact with incompatible materials.
Incompatible materials	Acids. Aldehydes. Alkalis. Amines. Chlorinated hydrocarbons. Halogens. Strong oxidizing agents. Isocyanates. Chlorine.
Hazardous decomposition products	Carbon oxides.

11. Toxicological information

Information on likely routes of exposure

Ingestion	Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.
Inhalation	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Prolonged inhalation may be harmful.
Skin contact	Prolonged skin contact may cause temporary irritation.
Eye contact	Causes serious eye irritation.
Symptoms related to the physical, chemical and toxicological characteristics	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Irritation of nose and throat. Aspiration may cause pulmonary edema and pneumonitis. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.

Information on toxicological effects

Acute toxicity	May be fatal if swallowed and enters airways. Narcotic effects.
-----------------------	---

Product	Species	Test Results
Isopropyl Alcohol Precision Cleaner		
Acute		
<i>Dermal</i>		
LD50	Rabbit	18719.959 mg/kg estimated
<i>Inhalation</i>		
LC50	Rat	21548.1543 ppm, 4 hours estimated 52.9277 mg/l, 4 hours estimated
<i>Oral</i>		
LD50	Rat	6329.77 mg/kg estimated

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation	Prolonged skin contact may cause temporary irritation.
Serious eye damage/eye irritation	Causes serious eye irritation.
Respiratory sensitization	Not available.
Skin sensitization	This product is not expected to cause skin sensitization.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	May cause drowsiness and dizziness.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	May be fatal if swallowed and enters airways. If aspirated into lungs during swallowing or vomiting, may cause chemical pneumonia, pulmonary injury or death.
Chronic effects	Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
--------------------	--

Product		Species	Test Results
Isopropyl Alcohol Precision Cleaner			
Aquatic			
<i>Acute</i>			
Crustacea	EC50	Daphnia	11817.8154 mg/l, 48 hours estimated
Fish	LC50	Fish	10091.7188 mg/l, 96 hours estimated
Components		Species	Test Results
Isopropyl alcohol (CAS 67-63-0)			
Aquatic			
<i>Acute</i>			
Crustacea	EC50	Water flea (Daphnia magna)	7550 - 13299 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	3200 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability Readily biodegradable formula.

Bioaccumulative potential No data available.

Partition coefficient n-octanol / water (log Kow)

1,1-Difluoroethane	0.75
Isopropyl alcohol	0.05

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal of waste from residues / unused products If discarded, this product is considered a RCRA ignitable waste, D001. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Dispose in accordance with all applicable regulations.

Hazardous waste code D001: Waste Flammable material with a flash point <140 F

Contaminated packaging Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport information

DOT

UN number	UN1950
UN proper shipping name	Aerosols, flammable, Limited Quantity
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	N82
Packaging exceptions	306
Packaging non bulk	None
Packaging bulk	None

IATA

UN number	UN1950
UN proper shipping name	Aerosols, flammable, Limited Quantity
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Packing group	Not applicable.
Environmental hazards	No.
ERG Code	10L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

Other information

Passenger and cargo aircraft Allowed.
Cargo aircraft only Allowed.

IMDG

UN number UN1950
UN proper shipping name AEROSOLS, LIMITED QUANTITY
Transport hazard class(es)
Class 2
Subsidiary risk -
Packing group Not applicable.
Environmental hazards
Marine pollutant No.
EmS Not available.
Special precautions for user Read safety instructions, SDS and emergency procedures before handling.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.
All components are on the U.S. EPA TSCA Inventory List.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

Not listed.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

1,1-Difluoroethane (CAS 75-37-6)

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Section 311/312 Immediate Hazard - Yes
Hazard categories Delayed Hazard - No
Fire Hazard - Yes
Pressure Hazard - Yes
Reactivity Hazard - No

SARA 302 Extremely hazardous substance No

US state regulations**US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)**

Not listed.

US. New Jersey Worker and Community Right-to-Know Act

1,1-Difluoroethane (CAS 75-37-6)
Isopropyl alcohol (CAS 67-63-0)

US. Massachusetts RTK - Substance List

1,1-Difluoroethane (CAS 75-37-6)

Isopropyl alcohol (CAS 67-63-0)

US. Pennsylvania Worker and Community Right-to-Know Law

Isopropyl alcohol (CAS 67-63-0)

US. Rhode Island RTK

1,1-Difluoroethane (CAS 75-37-6)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

Volatile organic compounds (VOC) regulations**EPA****VOC content (40 CFR 51.100(s))** 74.3 %**Consumer products (40 CFR 59, Subpt. C)** Not regulated**State****Consumer products** This product is regulated as an Electronic Cleaner. This product is compliant for use in all 50 states.**VOC content (CA)** 74.3 %**VOC content (OTC)** 74.3 %**International Inventories**

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	Yes
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	08-28-2014
Prepared by	Allison Cho
Version #	01
Further information	CRC # 921
HMIS® ratings	Health: 1 Flammability: 4 Physical hazard: 0 Personal protection: B
NFPA ratings	Health: 1 Flammability: 4 Instability: 0

NFPA ratings

Disclaimer

CRC cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries.