



Part Number: SPIDER Giga 2TX PoE EEC

Industrial Ethernet PoE Injector

Product Description

Unmanaged Industrial Ethernet DIN Rail Mount Power over Ethernet Injector with extended temperature range, 10/100/1000 Mbit/s RJ45

Technical Specifications

Product description

Part Number:	942 059-001
Port type and quantity:	2 x 10/100/1000BASE-T(X), 1 x PoE+ according to IEEE802.3at, TP-cable, RJ45 sockets

More Interfaces

Power supply/signaling contact:	1 x plug-in terminal block, 6-pin, no signaling contact
---------------------------------	---

Network size - length of cable

Twisted pair (TP):	0-100 m
--------------------	---------

Power requirements

Operating Voltage:	24 V DC - 48 V DC redundant
Power consumption:	max. 33,8 Watt (with PoE), 115,4 Btu(IT)/h

Diagnostics features

Diagnostic functions:	LEDs (Power, PoE)
-----------------------	-------------------

Ambient conditions

MTBF (Telcordia SR-332: Gb 25 °C):	1419817 h
Operating temperature:	-40+70 °C
Storage/transport temperature:	-45+85 °C
Relative humidity (non-condensing):	5-95 %

Mechanical construction

Dimensions (WxHxD):	30 mm x 140 mm x 95 mm
Weight:	420 g
Mounting:	DIN Rail, Wall mounting
Protection class:	IP30

Mechanical stability

IEC 60068-2-6 vibration:	3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1g, 9 Hz-150 Hz, 10 cycles, 1 octave/min
IEC 60068-2-27 shock:	15 g, 11 ms duration

EMC interference immunity

EN 61000-4-2 electrostatic discharge (ESD):	4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field:	10 V/m (80-1000 MHz)
EN 61000-4-4 fast transients (burst):	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage:	power line: 0.5 kV (line/earth), 0.5 kV (line/line)
EN 61000-4-6 Conducted Immunity:	10 V (150 kHz-80 MHz)

EMC emitted immunity

EN 55022:	EN 55022 Class A
FCC 47CFR Part 15:	FCC 47CFR Part 15, Class A
FCC CFR47 Part 15:	FCC 47CFR Part 15, Class A

Approvals

Safety of industrial control equipment:	cUL 508
---	---------

Scope of delivery and accessories

Variants

Item #
942059001

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.