



KRAMER

VS-48HDCPxI

4x8 DVI (HDCP) Matrix Switcher

| DVI | Ethernet - RJ-45 | HDCP Compliant



The VS-48HDCPxI is a high-performance matrix switcher for DVI and HDMI signals on a DVI-D connector. It reclocks and equalizes the signal and can route any input to any or all outputs simultaneously

FEATURES

Max. Data Rate - 6.75Gbps (2.25Gbps per graphic channel)

HDCP Compatible

HDTV Compatible

HDMI Support - Deep Color, x.v.Color™, 3D Pass-Through, HDMI Compressed Audio Channels

Kramer Equalization & re-Klocking™ Technology - Rebuilds the digital signal to travel longer distances

EDID Capture - Copies and stores the EDID from a display device

Output Disconnect - For each output

Front Panel Control Lockout

Memory Locations - Stores multiple switches as presets to be recalled and executed when needed

Flexible Control Options - Front panel, IR remote, RS-232 (K-Router™ Windows®-based software is included), Ethernet (Windows®-based Ethernet Configuration Manager & Virtual Serial Port Manager is included)

Worldwide Power Supply - 100-240V AC

Standard 19" Rack Mount Size - 2U. Rack "ears" included



KRAMER

TECHNICAL SPECIFICATIONS

INPUTS:	4 DVI connectors
OUTPUTS:	8 DVI connectors
BANDWIDTH:	6.75Gbps (2.25Gbps per graphic channel)
COMPLIANCE WITH STANDARDS:	Supports DVI and HDCP
RESOLUTION:	Up to UXGA; 1080p
POWER CONSUMPTION:	100-240V AC, 50/60Hz, 33VA
CONTROLS:	Front panel buttons, infrared remote control transmitter, RS-232, Ethernet
INCLUDED ACCESSORIES:	Power cord, IR transmitter, rack "ears"
PRODUCT DIMENSION:	19" x 9.29 x 2U (43.6cm x 23.60cm 8.80cm) W, D, H
PRODUCT WEIGHT:	2.7kg (6.0lbs) approx
SHIPPING DIMENSION:	55.00cm x 34.00cm x 15.50cm (21.65" x 13.39" x 6.10") W, D, H
SHIPPING WEIGHT:	0.0kg (0.0lbs) approx

