

CONFIG PART #


840ENT4042SSS-NS
 EN FRAME 84"H x 40"W x 42"D WITH 2 PAIR OF 45 RMU #10-32 TAPPED RAILS, CABLE MANAGEMENT FINGERS ON ALL RAILS, SOLID TOP, SPLIT PERF FRONT DOOR & REAR DOOR AND NO SIDES

840EN4042SSS-NS
 EN FRAME 84"H x 40"W x 42"D WITH 2 PAIR OF 45 RMU M6 RAILS, CABLE MANAGEMENT FINGERS ON ALL RAILS, SOLID TOP, SPLIT PERF FRONT DOOR & REAR DOOR AND NO SIDES


TOP PANEL OPENING (273 sq.in.); SOLID, VENTED, OR w/ EXHAUST FANS FLOWING UP TO 1100 CFM

INDEPENDENT MOUNTING LOCATIONS FOR LADDER RACK BRACKETS OR TOP MOUNTED CABLE TROUGH OPTIONS

19" EIA, 310-D COMPLIANT REF PART # FOR #10-32UNF TAPPED EQUIPMENT MTG HOLES & SCREWS -or- 3/8" SQUARE EQUIPMENT MTG HOLES FOR M6 CAGE NUTS & SCREWS




DETAIL C




SECTION B-B DOORS REMOVED

4.25 x 17.25 CABLE PASS THROUGH KNOCKOUTS (73.3 sq.in.), 2 PLACES


6.63 x 18.50 CABLE PASS THROUGH KNOCKOUTS (122.6 sq.in.), 4 PLACES




TOP VIEW




SPLIT MESH FRONT & REAR DOORS, PART #8402EN40SM
 TOP VIEW




CLOSED VIEW



SECTION A-A




FRONT VIEW DOORS REMOVED



FRONT VIEW

LEVELING GLIDES (8) INCLUDED 1/2-13 UNC THREADED HOLES



RIGHT SIDE VIEW

SPECIFICATIONS:

CONFIG. # KIT INCLUDES: QTY. 1 8401EN4042, BASIC FRAME UNIT WITH RAILS
 QTY. 2 8402EN40SM, SPLIT MESH REAR DOOR ASSEMBLIES

DIMENSIONS: 84.0"H x 40.0"W x 42.0"D

RACK SPACES: 45 RMU w/ NUMBERED RMU INDICATORS, 19" EIA 310-D COMPLIANT.

COLOR: DURABLE TEXTURED BLACK POWDER COATING

CONSTRUCTION: FULL WELDED STEEL FRAME WITH RECESSED #12 GA CORNER POSTS (1 PAIR) FIXED #12 GA RAILS, (1 PAIR) ADJUSTABLE DEPTH #12 GA RAILS DOORS #16 C.R.S.

HARDWARE: PACKAGE OF (QTY 50); #10-32 SCREWS -or- M6 SCREWS W/ CAGE NUTS, INCLUDED.

EST. WEIGHT : 357.82 lbmass



INTERPRET DRAWING PER ASME Y14.5M-1994
 DIMENSIONAL LIMITS APPLY AFTER APPLICATION OF FINISH
 DRAWING NOT TO SCALE
 TOLERANCE UNLESS OTHERWISE NOTED:
 ANGULAR +/- .1"
 .XXXX +/- .010
 .XXX +/- .015
 .XX +/- .030
 .X FOR REF. ONLY
 UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES

NOTICE:
 Use of this document is subject to a confidentiality and nondisclosure agreement with Great Lakes Case & Cabinet Co., Inc. (GLCC) and may not be reproduced, disclosed or utilized in whole or in part without prior written authorization from GLCC.

PART NUMBER: SEE CHART
 QTY PER UNIT: 1
 MATERIAL TYPE:
 MATERIAL GAUGE:
 FINISH:
 DRAWN: DATE 5/12/2014
 FED: DATE 5/12/2014
 CHECKED & APP. DATE 5/12/2014
 WSS

TITLE: EN FRAME, 84"H x 40"W x 42"D, w/ SPLIT PERF FRONT & REAR DOORS & NO SIDES
 GREAT LAKES CASE & CABINET CO., INC.
 P.O. BOX 551 EDINBORO, PA 16412
 PHONE (814) 734-7303 FAX (814) 734-3907
 E-MAIL glcc@greatcabinets.com
 DWG NO. SEE CHART
 REV. SEE CHART
 SHEET: 1 OF 1