



Product: BRS40-00120000-STCY99HHSES07.4.pdf

Configurator: BOBCAT

Configurator Description

The Hirschmann BOBCAT Switch is the first of its kind to enable real-time communication using TSN. To effectively support the increasing real-time communication requirements in industrial settings, a strong Ethernet network backbone is essential. This compact managed switches allow for expanded bandwidth capabilities by adjusting your SFPs from 1 to 2.5 Gigabit – requiring no change to the appliance.

Technical Specifications

Product description

Type	BRS40-8TX/4SFP (Product code: BRS40-00120000-STCY99HHSESXX.X.XX)
Description	Managed Industrial Switch for DIN Rail, fanless design All Gigabit type
Part Number	942170009
Port type and quantity	12 Ports in total: 8x 10/100/1000BASE TX / RJ45, 4x 100/1000Mbit/s fiber 1. Uplink: 2 x SFP Slot (100/1000 Mbit/s) 2. Uplink: 2 x SFP Slot (100/1000 Mbit/s)

More Interfaces

Power supply/signaling contact	1 x plug-in terminal block, 6-pin
Digital Input	1 x plug-in terminal block, 2-pin

Network size - length of cable

Twisted pair (TP)	0 - 100 m
Single mode fiber (SM) 9/125	see SFP fiber modules see SFP fiber modules
Single mode fiber (LH) 9/125	see SFP fiber modules see SFP fiber modules
Multimode fiber (MM) 50/125	see SFP fiber modules see SFP fiber modules
Multimode fiber (MM) 62.5/125	see SFP fiber modules see SFP fiber modules

Network size - cascadiability

Line - / star topology	any
------------------------	-----

Power requirements

Operating voltage	2 x 12 V DC ... 24 VDC
Power consumption	11 W
Power output in Btu (IT) h	38

Software

Switching	Independent VLAN Learning, Fast Aging, Static Unicast/Multicast Address Entries, QoS / Port Prioritization (802.1D/p), TOS/DSCP Prioritization, Interface Trust Mode, CoS Queue Management, Flow Control (802.3X), Egress Interface Shaping, Ingress Storm Protection, Jumbo Frames, VLAN (802.1Q), GARP VLAN Registration Protocol (GVRP), Voice VLAN, GARP Multicast Registration Protocol (GMRP), IGMP Snooping/Querier per VLAN (v1/v2/v3), Unknown Multicast Filtering, Multiple VLAN Registration Protocol (MVRP), Multiple MAC Registration Protocol (MMRP), Multiple Registration Protocol (MRP)
Redundancy	HIPER-Ring (Ring Switch), Link Aggregation with LACP, Link Backup, Media Redundancy Protocol (MRP) (IEC62439-2), Redundant Network Coupling, RSTP 802.1D-2004 (IEC62439-1), RSTP Guards
Management	Dual Software Image Support, TFTP, SFTP, SCP, LLDP (802.1AB), LLDP-MED, SSHv2, HTTP, HTTPS, Traps, SNMP v1/v2/v3, Telnet
Diagnostics	Management Address Conflict Detection, MAC Notification, Signal Contact, Device Status Indication, TCPDump, LEDs, Syslog, Persistent Logging on ACA, Port Monitoring with Auto-Disable, Link Flap Detection, Overload Detection, Duplex Mismatch Detection, Link Speed and Duplex Monitoring, RMON (1,2,3,9), Port Mirroring 1:1, Port Mirroring 8:1, Port Mirroring N:1, System Information, Self-Tests on Cold Start, SFP Management, Configuration Check Dialog, Switch Dump

Configuration	Automatic Configuration Undo (roll-back), Configuration Fingerprint, Text-based Configuration File (XML), BOOTP/DHCP Client with Auto-Configuration, DHCP Server: per Port, DHCP Server: Pools per VLAN, AutoConfiguration Adapter ACA21/22 (USB), HiDiscovery, Command Line Interface (CLI), CLI Scripting, Full-featured MIB Support, Context-sensitive Help
Security	MAC-based Port Security, Port-based Access Control with 802.1X, Guest/unauthenticated VLAN, Integrated Authentication Server (IAS), RADIUS VLAN Assignment, Denial-of-Service Prevention, Access to Management restricted by VLAN, Device Security Indication, Audit Trail, CLI Logging, HTTPS Certificate Management, Restricted Management Access, Appropriate Use Banner, Configurable Password Policy, Configurable Number of Login Attempts, SNMP Logging, Multiple Privilege Levels, Local User Management, Remote Authentication via RADIUS, User Account Locking
Time synchronisation	Buffered Real Time Clock, SNTP Client, SNTP Server
Miscellaneous	Digital IO Management, Manual Cable Crossing, Port Power Down

Ambient conditions

Operating temperature	0-+60 °C
Storage/transport temperature	-40-+70 °C
Relative humidity (non-condensing)	1- 95 %

Mechanical construction

Dimensions	73 mm x 138 mm x 115 mm
Weight	570 g
Housing	Plastic
Mounting	DIN Rail
Protection class	IP30

Mechanical stability

IEC 60068-2-6 vibration	5 Hz ... 8.4 Hz with 3,5 mm amplitude; 2 Hz ... 13,2 Hz with 1 mm amplitude; 8,4 Hz ... 200 Hz with 1 g; 13,2 Hz ... 100 Hz with 0,7 g
IEC 60068-2-27 shock	15 g, 11 ms duration

EMC interference immunity

EN 61000-4-2 electrostatic discharge	6 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80-2000 MHz); 5 V/m (2000-2700 MHz); 3 V/m (5100-6000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 2 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth) and 1 kV (line/line); data line: 2 kV
EN 61000-4-6 conducted immunity	10 V (150 kHz-80 MHz)

EMC emitted immunity

EN 55022	EN 55032 Class A
FCC CFR47 Part 15	FCC 47CFR Part 15, Class A

Approvals

Basis Standard	CE, FCC, EN61131, EN62368-1
Safety of industrial control equipment	cUL61010

Scope of delivery and accessories

Accessories	AutoConfiguration Adapter ACA22-USB-C (IEC) 942239001; 6-pin terminal block with screw lock (50 pieces) 943 845-013; 2-pin terminal block with screw lock (50 pieces) 943 845-009; Industrial HiVision Network Management Software 943 156-xxx
Scope of delivery	1 × Device 1 × General safety instructions 1 × Terminal block for supply voltage and signal contact; 1 × Terminal block for the digital input

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.