



**SAFETY DATA SHEET
MA310 ACTIVATOR**

Commission Regulation (EU) No 2015/830 of 28 May 2015.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name MA310 ACTIVATOR
REACH registration notes CAS 80-62-6: 01-2119452498-28-XXXX

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Activator.

1.3. Details of the supplier of the safety data sheet

Supplier

ITW Performance Polymers
Bay 150
Shannon Industrial Estate
Co. Clare
Ireland
V14 DF82
353(61)771500
353(61)471285
mail@itwpp.com

1.4. Emergency telephone number

Emergency telephone +44(0)1235 239 670 (24h)

SECTION 2: Hazards identification


2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Flam. Liq. 2 - H225
Health hazards Skin Irrit. 2 - H315 Skin Sens. 1 - H317 STOT SE 3 - H335
Environmental hazards Not Classified

2.2. Label elements

Pictogram



Signal word

Danger

Hazard statements

H225 Highly flammable liquid and vapour.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H335 May cause respiratory irritation.

MA310 ACTIVATOR

Precautionary statements	<p>P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.</p> <p>P261 Avoid breathing vapour/ spray.</p> <p>P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.</p> <p>P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/ shower.</p> <p>P304+P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.</p>
Contains	METHYL METHACRYLATE
Supplementary precautionary statements	<p>P240 Ground/ bond container and receiving equipment.</p> <p>P241 Use explosion-proof electrical equipment.</p> <p>P242 Use only non-sparking tools.</p> <p>P243 Take precautionary measures against static discharge.</p> <p>P264 Wash contaminated skin thoroughly after handling.</p> <p>P271 Use only outdoors or in a well-ventilated area.</p> <p>P272 Contaminated work clothing should not be allowed out of the workplace.</p> <p>P302+P352 IF ON SKIN: Wash with plenty of water.</p> <p>P312 Call a POISON CENTER/ doctor if you feel unwell.</p> <p>P321 Specific treatment (see medical advice on this label).</p> <p>P332+P313 If skin irritation occurs: Get medical advice/ attention.</p> <p>P333+P313 If skin irritation or rash occurs: Get medical advice/ attention.</p> <p>P362+P364 Take off contaminated clothing and wash it before reuse.</p> <p>P370+P378 In case of fire: Use foam, carbon dioxide, dry powder or water fog to extinguish.</p> <p>P403+P233 Store in a well-ventilated place. Keep container tightly closed.</p> <p>P403+P235 Store in a well-ventilated place. Keep cool.</p> <p>P405 Store locked up.</p> <p>P501 Dispose of contents/ container in accordance with national regulations.</p>

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

METHYL METHACRYLATE	60-100%
CAS number: 80-62-6	EC number: 201-297-1
	REACH registration number: 01-2119452498-28-0000
Classification	
Flam. Liq. 2 - H225	
Skin Irrit. 2 - H315	
Skin Sens. 1 - H317	
STOT SE 3 - H335	
3,5-diethyl-1,2-dihydro-1-phenyl-2-propylpyridine	10-30%
CAS number: 34562-31-7	
Classification	
Acute Tox. 4 - H302	
Acute Tox. 4 - H312	
Skin Irrit. 2 - H315	
Eye Irrit. 2 - H319	

MA310 ACTIVATOR

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Avoid contact with skin and eyes. Do not breathe vapour/spray. In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).
Inhalation	Move affected person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Get medical attention if any discomfort continues.
Ingestion	Do not induce vomiting. Give plenty of water to drink. Get medical attention.
Skin contact	Remove affected person from source of contamination. Wash skin thoroughly with soap and water. Get medical attention if irritation persists after washing.
Eye contact	Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes and get medical attention. Get medical attention if irritation persists after washing.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
----------------------------	---

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	No specific recommendations. If in doubt, get medical attention promptly.
-----------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	Extinguish with foam, carbon dioxide or dry powder.
-------------------------------------	---

5.2. Special hazards arising from the substance or mixture

Specific hazards	Highly flammable Avoid breathing fire gases or vapours. Vapours are heavier than air and may spread near ground and travel a considerable distance to a source of ignition and flash back. Polymerises easily with evolution of heat.
-------------------------	---

5.3. Advice for firefighters

Protective actions during firefighting	Keep up-wind to avoid fumes. Do not use water jet as an extinguisher, as this will spread the fire. Cool containers exposed to flames with water until well after the fire is out. Control run-off water by containing and keeping it out of sewers and watercourses.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions	Warn everybody of potential hazards and evacuate if necessary. Provide adequate ventilation. No smoking, sparks, flames or other sources of ignition near spillage. Avoid inhalation of spray mist and contact with skin and eyes. Wear protective clothing as described in Section 8 of this safety data sheet.
-----------------------------	--

6.2. Environmental precautions

Environmental precautions	Avoid the spillage or runoff entering drains, sewers or watercourses. Spillages or uncontrolled discharges into watercourses must be reported immediately to the Environmental Agency or other appropriate regulatory body.
----------------------------------	---

6.3. Methods and material for containment and cleaning up

MA310 ACTIVATOR

Methods for cleaning up Absorb spillage with non-combustible, absorbent material. Collect and place in suitable waste disposal containers and seal securely. Containers with collected spillage must be properly labelled with correct contents and hazard symbol.

6.4. Reference to other sections

Reference to other sections Wear protective clothing as described in Section 8 of this safety data sheet.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Provide adequate general and local exhaust ventilation. Observe any occupational exposure limits for the product or ingredients. Avoid inhalation of vapours/spray and contact with skin and eyes. Take precautionary measures against static discharges. Storage tanks and other containers must be earthed. No smoking, sparks, flames or other sources of ignition near spillage. Good personal hygiene procedures should be implemented.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store in tightly-closed, original container in a dry, cool and well-ventilated place. Store away from incompatible materials (see Section 10).

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

Occupational exposure limits

METHYL METHACRYLATE

Long-term exposure limit (8-hour TWA): WEL 50 ppm 208 mg/m³

Short-term exposure limit (15-minute): WEL 100 ppm 416 mg/m³

WEL = Workplace Exposure Limit

Ingredient comments WEL = Workplace Exposure Limits

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate general and local exhaust ventilation. Observe any occupational exposure limits for the product or ingredients.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses. Personal protective equipment for eye and face protection should comply with European Standard EN166.

Hand protection

Wear protective gloves made of the following material: Rubber or plastic. To protect hands from chemicals, gloves should comply with European Standard EN374. The selected gloves should have a breakthrough time of at least 8 hours.

Other skin and body protection

Wear chemical protective suit.

MA310 ACTIVATOR

Hygiene measures	Provide eyewash station and safety shower. Keep away from food, drink and animal feeding stuffs. Good personal hygiene procedures should be implemented. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site. Do not eat, drink or smoke when using the product. Change work clothing daily before leaving workplace.
Respiratory protection	If ventilation is inadequate, suitable respiratory protection must be worn. Respirator selection must be based on exposure levels, the hazards of the product and the safe working limits of the selected respirator. Check that the respirator fits tightly and the filter is changed regularly. Wear a respirator fitted with the following cartridge: Organic vapour filter. Gas filter, type A2. Half mask and quarter mask respirators with replaceable filter cartridges should comply with European Standard EN140.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

Appearance	Paste.
Colour	Yellow. or Black.
Odour	Slight pungent.
pH	pH (diluted solution): 4.5-5.5 5%
Initial boiling point and range	101°C @
Flash point	10°C
Evaporation rate	3 (butyl acetate =1)
Upper/lower flammability or explosive limits	Upper flammable/explosive limit: 12.5 Lower flammable/explosive limit: 2.1
Vapour pressure	28mmHg @ °C
Vapour density	3.5
Relative density	0.96 @ 20 °C°C
Viscosity	40,000 -60,000 cP @ 25°C

9.2. Other information

Other information	Not available.
--------------------------	----------------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	The following materials may react with the product: Strong oxidising agents.
-------------------	--

10.2. Chemical stability

Stability	Stable at normal ambient temperatures and when used as recommended. May polymerise.
------------------	---

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Not available. May polymerise.
---	--------------------------------

10.4. Conditions to avoid

Conditions to avoid	Heating may generate flammable vapours. Vapours may form explosive mixtures with air. Avoid heat, flames and other sources of ignition. Avoid excessive heat for prolonged periods of time. Avoid exposure to high temperatures or direct sunlight.
----------------------------	---

MA310 ACTIVATOR

10.5. Incompatible materials

Materials to avoid Avoid contact with oxidising agents.

10.6. Hazardous decomposition products

Hazardous decomposition products Oxides of carbon. Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours. Fire or high temperatures create: Nitrous gases (NOx). Cyanides.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

ATE oral (mg/kg) 50,000.0

Acute toxicity - dermal

ATE dermal (mg/kg) 110,000.0

Inhalation Vapours in high concentrations are narcotic. Symptoms following overexposure may include the following: Headache. Fatigue. Dizziness. Nausea, vomiting. Vapours in high concentrations are anaesthetic. Symptoms following overexposure may include the following: Headache. Fatigue. Dizziness. Central nervous system depression.

Ingestion Irritating. Symptoms following overexposure may include the following: Nausea, vomiting. Stomach pain.

Skin contact May be absorbed through the skin. Irritating to skin. Prolonged or repeated exposure may cause severe irritation. May cause sensitisation by skin contact. May cause sensitisation or allergic reactions in sensitive individuals.

Eye contact Irritating to eyes. A single exposure may cause the following adverse effects: Corneal damage.

Target organs Prolonged or repeated exposure may cause the following adverse effects: May cause damage to the liver and kidneys. Respiratory system, lungs Central nervous system

SECTION 12: Ecological Information

Ecotoxicity Avoid release to the environment.

12.1. Toxicity

Toxicity Not considered toxic to fish.

12.2. Persistence and degradability

Persistence and degradability Methyl methacrylate monomer : Biochemical oxygen demand within 5 days (BOD5) = .14 g/g - 0.9 g/g.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

12.4. Mobility in soil

Mobility Do not discharge into drains or watercourses or onto the ground.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

MA310 ACTIVATOR

Other adverse effects Not available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information	When handling waste, the safety precautions applying to handling of the product should be considered.
Disposal methods	Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.
Waste class	08 04 09

SECTION 14: Transport information

14.1. UN number

UN No. (ADR/RID)	1133
UN No. (IMDG)	1133
UN No. (ICAO)	1133
UN No. (ADN)	1133

14.2. UN proper shipping name

Proper shipping name (ADR/RID)	ADHESIVES
Proper shipping name (IMDG)	ADHESIVES
Proper shipping name (ICAO)	ADHESIVES
Proper shipping name (ADN)	ADHESIVES

14.3. Transport hazard class(es)

ADR/RID class	3
ADR/RID classification code	F1
ADR/RID label	3
IMDG class	3
ICAO class/division	3
ADN class	3

Transport labels



14.4. Packing group

ADR/RID packing group	II
IMDG packing group	II
ADN packing group	II
ICAO packing group	II

14.5. Environmental hazards

MA310 ACTIVATOR

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

EmS F-E, S-D

ADR transport category 2

Emergency Action Code •3YE

Hazard Identification Number 33
(ADR/RID)

Tunnel restriction code (D/E)

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision date 05/04/2018

Revision 11

Supersedes date 08/02/2018

Hazard statements in full H225 Highly flammable liquid and vapour.
H302 Harmful if swallowed.
H312 Harmful in contact with skin.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.