

DS-2DE5225IW-AE**2 MP Outdoor 25× IR Network Speed Dome**

- **1/2.8" Progressive Scan CMOS**
- **Up to 1920 x 1080 Resolution**
- **Minimum Illumination:**
Color: 0.005 Lux @ (F1.6, AGC ON)
B/W: 0.001 Lux @ (F1.6, AGC ON)
0 Lux with IR
- **Up to 490 ft (150 m) IR Distance**
- **H.265+/H.265 Video Compression**
- **25x Optical Zoom, 16x Digital Zoom**
- **Electronic Image Stabilization**
- **EIS, Defog**
- **120 dB WDR**
- **Smart Detection: Line Crossing,**
- **Intrusion, Region Enter/Exit**
- **IP66 Protection**
- **24 VAC and Hi-PoE (maximum 30 W)**

Hikvision DS-2DE5225IW-AE Network IR Speed Dome Cameras produce images with a resolution of up to 1920 x 1080 pixels.

The embedded 1/2.8" progressive scan CMOS chip supports 120 dB WDR, and the 25x optical zoom allows for greater detail to be collected over more expansive areas.

The Network IR Speed Dome Camera also features a wide range of smart functions, including intrusion detection, and line crossing detection, which allows for key events and objects to be recorded for further forensic needs.

The camera features Electronic Image Stabilization (EIS), an image enhancement technique that reduces blurring and provides compensation in adverse environmental conditions.












Available models:
DS-2DE5225IW-AE



Specifications

DS-2DE5225IW-AE	
Camera Module	
Image Sensor	1/2.8" progressive scan CMOS
Minimum Illumination	Color: 0.005 Lux @(F1.6, AGC ON); B/W: 0.001 Lux @(F1.6, AGC ON), 0 Lux with IR
Shutter Time	1/1 to 1/30,000 s
White Balance	Auto / manual / ATW (auto-tracking white balance) / indoor / outdoor / fluorescent lamp / sodium lamp
AGC	Auto / manual
Day and Night	IR cut filter
Digital Zoom	16×
Privacy Mask	24 programmable privacy masks
Focus Mode	Auto / semi-automatic / manual
Digital WDR	120 dB
Rapid Focus	Supported
Lens	
Focal Length	4.8 mm to 120 mm, 25× Optical
Zoom Speed	Approximately 3.6 s (optical lens, wide to tele)
Angle of View	Horizontal field of view: 57.6° to 2.5° (wide to tele); vertical field of view: 34.4° to 1.4° (wide to tele) diagonal field of view: 64.5° to 2.9° (wide to tele)
Minimum Working Distance	10 mm to 1,500 mm (wide to tele)
Aperture Range	F1.5 to F3.5
IR	
IR Distance	Up to 490 ft (150 m)
Smart IR	Supported
PTZ	
Movement Range (Pan)	360° endless
Pan Speed	Configurable, from 0.1°/s to 210°/s, Preset Speed: 120°/s
Movement Range (Tilt)	From -15° to 90°
Tilt Speed	Configurable, from 0.1°/s to 80°/s, Preset Speed: 80°/s
Proportional Zoom	Supported
Presets	300
Patrol Scan	8 patrols, up to 32 presets for each patrol
Pattern Scan	4 pattern scans, record time over 10 minutes for each scan
Power-off Memory:	Supported
Park Action	Preset / pattern scan / patrol scan / auto scan / tilt scan / random scan / frame scan / panorama scan
PTZ Status Display	On/off
Preset Freezing	Supported
Scheduled Task	Preset / pattern scan / patrol scan / auto scan / tilt scan / random scan / frame scan / panorama scan / dome reboot / dome adjust / aux output
Compression Standard	
Video Compression	Main stream: H.265+ / H.265 / H.264+ / H.264; sub-stream: H.265 / H.264 / MJPEG; third stream: H.265 / H.264 / MJPEG
H.264 Type	Baseline profile / main profile / high profile
H.264+	Supported
H.265 Type	Main profile
H.265+	Supported
Video Bitrate	32 kbps to 16,384 kbps
SVC	Supported
Smart Features	
Basic Event	Motion detection, video tampering detection, exception
Smart Event	Intrusion detection, line crossing detection, region entrance detection, region exiting detection, object removal detection, unattended baggage detection
Smart Record	ANR (Automatic Network Replenishment), Dual-VCA
ROI	Main stream, sub-stream, and third stream respectively supports four fixed areas
Image	
Maximum Resolution	1920 × 1080
Main Stream	30 fps (1920 × 1080, 1280 × 960, 1280 × 720), 60 fps (1280 × 960, 1280 × 720)
Sub-Stream	30 fps (704 × 480, 640 × 480, 352 × 240)
Third Stream	30 fps (1920 × 1080, 1280 × 960, 1280 × 720, 704 × 480, 640 × 480, 352 × 240)
Image Enhancement	HLC / BLC / 3D DNR / Defog / EIS / Regional Exposure / Regional Focus
Network	
Network Storage	Built-in memory card slot, support microSD / SDHC / SDXC, up to 256 GB; NAS (NPS, SMB/ CIFS), ANR
Alarm Linkage	Alarm actions, such as preset, patrol scan, pattern scan, memory card video record, trigger recording, notify surveillance center, upload to FTP / memory card / NAS, send email, etc.
Protocols	IPv4 / IPv6, HTTP, HTTPS, 802.1x, Qos, FTP, SMTP, UPnP, SNMP, DNS, DDNS, NTP, RTSP, RTCP, RTP, TCP/IP, DHCP, PPPoE, Bonjour
API	Open-ended, supports ONVIF, CGI, HIKVISION SDK, and third-party management platforms
Simultaneous Live View	Up to 20
User/Host	Up to 32 users; 3 levels: administrator, operator, and user
Security Measures	User authentication (ID and PW), host authentication (MAC address); HTTPS encryption; IEEE 802.1x port-based network access control; IP address filtering
Client	iVMS-4200, iVMS-4500, iVMS-5200, Hik-Connect
Web Browser	IE 8 to 11, Chrome 31.0 to 44, Firefox 30.0 to 51
Interface	
Network Interface	1 RJ45 10 M/100 M Ethernet Interface, Hi-PoE
General	
Power	24 VAC (maximum 30 W); Hi-PoE (maximum 10 W)
Working Temperature	-22° F to 149° F (-30°C to 65°C); humidity: ≤ 90%
Protection Level	IP66 standard, TVS 6000V lightning protection, surge protection and voltage transient protection
Material	ADC 12, PC, PC + 10 % GF
Dimensions	Ø 8.19" × 13.58" (Ø 208 mm × 345 mm)
Weight	Approximately 7.28 lb (3.3 kg)

Accessories

										
WMP-L Wall Mount PTZ Long	CMP Corner Mount for WMP-S/L	PMP Pole Mount for WMP-S/L	JBPW-L Power Box Mount w/Wall Bracket	CMP-JB Corner Mount for JBPW-L	PMP-JB Pole Mount for JBPW-L	CPM-S Short Ceiling Pendant Mount	CPM-L Long Ceiling Pendant Mount	CPMPE Ceiling Pendant Mount Extension Pipe	PMP-V Horizontal Pole Mount for CPM-S/L	RPM Roof Parapet Mount

Dimensions

