

CS8364C

50 Amp, 3-Phase 250V AC, Non-NEMA, 3P, 4W, Black & White Locking Connector, Industrial Grade, Grounding, California-Style(CS)- BLACK-WHITE



Color: Black-White

UPC Code: 07847732639

Country Of Origin: Mexico

NEMA:
Non-NEMA



Leviton's Black & White 50 Amp, Non-NEMA line of industrial grade locking blade devices feature rugged construction that resists impact, sunlight, chemicals and rough use. All contacts and blades are solid one-piece construction for superior conductivity. Corrosion resistant versions feature nickel plated contacts and blades, plus stainless steel shrouds and screws. The ergonomic, fluted-body design with radial gripping edge is ideal for gripping and pulling. The unique cord clamp accepts a wide range of cord sizes, providing a secure grip without damaging the cord. And, they are backed by a limited lifetime warranty.

Technical Information

Electrical Specifications

Amperage: 50 A

Current Interrupting: Certified for current interrupting at full rated current

Dielectric Voltage Withstand: 2000V minimum per UL 498

Grounding: Grounding

Maximum Working Voltage: 3-Phase 250V as rated

Phase: 3-Phase

Pole: 3

Temperature Rise: Max 30°C temp rise at full-rated current after 150 cycles of OL at 150% rated DC current

Voltage: 250 VAC

Wire: 4

Environmental Specifications

Environment: Dry

Flammability: UL94V-2

Operating Temperature: -40°C to 75°C

Material Specifications

Assembly Screws: Brass

Cable Clamp Screw: Philips Head, SS 304

Center Pin: SS 302/304

Color: Black-White

Contact - Binding Plate: 0.100inch thick Brass

Contact - Spring Value: 0.041inch thick Brass

Contact Rivet: Brass

Dust Shield: Santoprene TPE

Face Module: Nylon

Ground Post: Brass

Ground Shunt: Bronze

Housing Material: Nylon

Standard Cable Clamp: Nylon

Terminal Block: 0.062inch thick Copper

Terminal Set Screw: SS 302/304

Wiring Chamber: Nylon

Mechanical Specifications

Cord Range: .680 - 1.125

Product ID: Ratings and Catalogue No. molded into face and stamped into shroud

Terminal Accom.: #10 min to #4max AWG Solid or Stranded Wire

Terminal ID: X, W, Y, Z and Green for ground

Product Features

Brand: Black and White

Color: Black-White

Device Type: Locking Connector

NEMA: Non-NEMA

Standards and Certifications


CSA C22.2 No. 42: File 152105

NOM: 057

RoHS: Compliant

UL 498: File E13399

Warranty: Lifetime Limited



SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

