


18 AWG 2-Pair Shielded Ethernet Cable – Patent Pending



1. Construction:

- 1.1. Conductors: 18 AWG Solid Bare Copper 0.040"
Nominal Diameter (1.01 mm)
- 1.2. Tape: Flame Retardant Tape
- 1.3. Insulation: LSZH Thermoset Fire-Roc™, 0.130"
(3.30 mm) Nominal Diameter, 0.035"
(0.88 mm) Nominal Wall Thickness
- 1.4. Pairs: Conductors Twisted to Varying Lays
- 1.5. Color: Red & Black Printed
- 1.6. Cable: Cable 2 Pairs
- 1.7. Drain: 18 AWG (0.82 mm²) Stranded Bare Copper
- 1.8. Shield: 0.005" (0.12 mm) Copper/Polyester Shield,
25% Minimum Overlap
- 1.9. Jacket: Red Non-Halogen Flame Retardant
Polyolefin, 0.465" (11.8 mm) Nominal
Diameter, Nominal Wall Thickness, 0.042"
(1.067 mm)

1.10. Jacket Print:

COMTRAN LSZH VITALink® c(UL)us CMR-LS or (UL)
FPLR-LS/CL3R-LS 2P18 AWG SHLD 105C FT4 SUN RES
WET or FAS105 ST1 FT4 LL14444 FRR-2HR FOR USE IN
FHIT & FHIT7 SYSTEMS 40A MAX VOLTAGE 72V PN
36512 (MMYY) 000002 (01-12345) PATENT PENDING

MMYY is 4 Digit Month/Year
(01-12345) = Traceability Code
000002 FT – Sequential Footage every 2 feet

2. Compliance:

- 2.1. c(UL)us Listed Type CMR-LS
- 2.2. (UL) Listed Type FPLR-LS
- 2.3. (UL) Listed CL3R-LS
- 2.4. CSA Listed FAS105 ST1 FT4
- 2.5. UL Subject 444 Communications Cable, 300V/105°C
Classified
- 2.6. UL Subject 1424 Power Limited Fire Alarm Circuits;
300V/105°C Classified
- 2.7. UL Subject 13 Power Limited Circuit Cables; 300V/105°C
Classified
- 2.8. ANSI/UL 2196 2-Hour Fire Rating for use in FHIT System
40A
- 2.9. CAN/ULC-S139 2-Hour Fire Rating with Hose Stream for
use in FHIT7 System 40A
- 2.10. NFPA 70 & 72
- 2.11. NFPA 130
- 2.12. California State Fire Marshal Approved
- 2.13. RoHS Compliant

3. Electrical Characteristics:

- 3.1. Meets Category 3 Channel Requirements per TIA-568-C.2
throughout UL2196 Flame and Hose Stream Testing
- 3.2. DC Resistance of Conductor: 6.52 Ω/1000' Nominal

4. Physical Characteristics:

- 4.1. Cable Weight: 95 Lbs./1000 Ft.
- 4.2. Min Bend Radius: 3.5"
- 4.3. Maximum Pull Tension – Straight Runs: 52 Lb./Ft.

TITLE:		DESCRIPTION		COMTRAN 330A Turner Street South Attleboro, MA 02703 Phone: 508-399-7004 Fax: 508-399-8839		 COMTRAN Innovative Systems. Engineered Solutions.  A Marmon Wire & Cable/Berkshire Hathaway Company	
DS36512		18AWG 2-Pair Shielded VITALink® Ethernet Cable – Patent Pending					
Rev	Date	Detail		Eng.	App.		
3	01/29/19	Update diameter, rebranding; add Patent information		PB	WC		
2	12/3/18	Update print remove preliminary mark		WC	RN		
1	10/5/18	Initial Concept		WC	RN	CD0887/S-2096-1	