STI Select-Alert





STI-SA5000-A

STI-SA5000-G



STI-SA5000-W



STI-SA5000-B

KEY FEATURES

General Information

- This controller helps prevent unauthorised use of important devices.
- Three year guarantee against breakage of polycarbonate in normal use (one year on electromechanical and electronic components).

Design

- Both a visual and audible alarm, it can serve as an inexpensive way to protect valuable units against theft and vandalism.
- Can be used as a cabinet alarm, door alarm, linked with push button/switch or as a burglar alarm.

Construction

· Polycarbonate is UV-stabilised.

Installation

 Highly versatile, includes a tamper switch which prevents it from being removed from a wall.

Electronics

 9 VDC battery or external 12 - 30 volts input power options, allows independent strobe and siren timing of 15 seconds, 30 seconds, 60 seconds or continuous. One Form "C" dry relay contact output.

Options

- Additional white mounting plate with key switch or white 40mm back box.
- May be set for a piercing 100 dB alarm or a softer 85 dB.
- · Super bright flashing LED.
- · Low battery indicator.



PRODUCT OVERVIEW

STI-SA5000-R

This controller helps prevent unauthorised use of important devices. The STI Select-Alert is a highly effective way to alert you to unauthorised use, theft or vandalism of important devices. The combination of alarm and super bright LEDs also offers excellent protection for an array of circumstances and allows the user to choose its function. Select-Alert can be used as a cabinet alarm, door/exit alarm, flashing light linked with a push button/switch, tornado siren, burglar alarm or an alert for any type of emergency situation.

HOW IT WORKS

If the protected unit is opened, the electronic Select-Alert emits a selected ear piercing siren and the LEDs flash – drawing attention in a hurry. The alarm and strobe have independent timing choices of: 15 seconds, 30 seconds, 60 seconds or continuous. Select-Alert can be powered by a 9 VDC battery or external 12-30 volts. Flush or surface mounted Select-Alert is available in amber, green, blue, red or white.

STI Select-Alert


Dimensions and Technical Information

MODELS AVAILABLE

STI-SA5000-A	Select-Alert in amber
STI-SA5000-B	Select-Alert in blue
STI-SA5000-G	Select-Alert in green
STI-SA5000-R	Select-Alert in red
STI-SA5000-W	Select-Alert in white
Accessories:	
KIT-71100 A-W	Back box kit
KIT-H18075	Replacement key for Select-Alert alarm
KIT-E18151	N.C. reed switch and magnet
KIT-SA505	Key switch mounting bracket (includes key switch)
BAT 9VDC	9 volt battery
KIT-H19016	Tamper proof screw and wrench

SPECIFICATIONS

Operating voltage	Internal 9 VDC battery (not included) Remote power 12-30 VDC
Power Consumption	Stand by: 50µA Siren low volume: 85mA Siren high volume: 90mA Strobe: 25mA
Siren Volume	Low: 85 dB High: 100 dB
Alarm & Strobe Timing	Independent control for siren and strobe: 15s, 30s, 60s and continuous
Low Battery Warning	LEDs flash once every 30 seconds
Form C dry contacts	0-30VAC/DC, 1 Amp Contacts reset after longest alarm setting
Key switch	Alarm on: normally closed
Alarm switch	Stand by: normally open contact required
Alarm tone	32 selectable sounds





Safety Technology ^{14y} International ^{14y} ^{Bro}

Taylor House 34 Sherwood Road Bromsgrove Worcestershire B60 3DR, England Tel: +44 (0)1527 520 999 Fax: +44 (0)1527 501 999 info@sti-emea.com www.sti-emea.com 2306 Airport Road Waterford, Michigan 48327, USA Tel: 248-673-9898 Fax: 248-673-1246 Toll-free:0800-888-4784 info@sti-usa.com www.sti-usa.com