

DVI over Cat5/Cat6 Passive Extender, Video Receiver, 1920x1080 at 60Hz, Up to 100-ft., TAA

MODEL NUMBER: **B140-1P0**



Transmit a DVI-D Single-Link signal up to 100 ft. away using a single Cat5e/6 patch cable

Description

The B140-1P0 is a receiver unit that is used with the B140-002 and B140-004 extender/splitter transmitter units, and it transmits a DVI-D Single-Link signal up to 100 ft. away using a single Cat5e/6 patch cable. To achieve maximum distance and resolution, use 24AWG Solid Wire Cat5e/6 cable (Tripp Lite's N202-Series). The B140-1P0 is compatible with all operating systems, and is plug and play, with no external power, software or drivers required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Installation is simple. Connect a B140-002 or B140-004 transmitter (not included) to a DVI source using a Tripp Lite P561-Series DVI cable (not included). Connect the B140-1P0's built-in DVI connector to a display. Finally, the receiver unit is connected to an RJ45 port on the transmitter unit using a single Cat5e/6 cable. A 1920 x 1080 @ 60Hz signal can be extended up to 50 ft. from the source, or a 1024 x 768 @ 60Hz signal up to 100 ft.

Features

- Transmit a DVI-D Single-Link signal up to 100 ft. away using a single Cat5e/6 patch cable
- For use with B140-002 or B140-004 extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 50 ft., or a 1024 x 768 @ 60Hz signal up to 100 ft.
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- HDCP compatible
- Compatible with all operating systems
- Plug and play; no external power, software or drivers required

Highlights

- For use with B140-002 or B140-004 extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 50 ft., or a 1024 x 768 @ 60Hz signal up to 100 ft.
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- Compatible with all operating systems
- Plug and play, no external power, software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B140-1P0 DVI Over Cat5 Passive Extender Remote Unit
- Owner's manual



- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332156655
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	5.08 x 16.00 x 18.29
Shipping Dimensions (hwd / in.)	2.00 x 6.30 x 7.20
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	100
Max 480P Range (ft)	100
Max 1440 x 900 Range (ft)	100
Max 1080i Range (ft)	50
Max 1080P Range (ft)	50
Max 480i Range (ft)	100
Max 640 x 480 Range (ft)	100
Max 800 x 600 Range (ft)	100
Max 1600 x 1200 Range (ft)	100
Max 720P Range (ft)	100
CONNECTIONS	
Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	DVI-D SINGLE LINK (MALE)
FEATURES & SPECIFICATIONS	
Technology	DVI
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>