



Part Number: FSNS11HBNC-25

ProSNS RG-11 Universal BNC Coax Compression Connector

Product Description

ProSNS RG11 Universal BNC male connector, (standard or tri-shield) non-blind entry with split ferrule design, polymer compression sleeve for easy insertion & lowest possible tool compression force.

Technical Specifications

Product Overview

Environmental Space:	Indoor/Outdoor
Suitable Applications:	CCTV, Security Cameras, Video

Physical Characteristics (Overall)

Conductor Size:	14 AWG
Packaging:	25 Pack
Number of Pieces:	1

Connectors

Materials

Description	Material
Nut	Nickel/Tin Plated Brass
O-Ring	Ethylene Propylene
Body	Nickel/Tin Plated Brass
Contact	Gold Plated

Electrical Characteristics

Impedance

Nominal Characteristic Impedance
75 Ohms

Return Loss (RL)

Frequency [MHz]
≥-21 dB up to 1 GHz typical
≤ -0.2 dB up to 1 GHz typical

Temperature Range

Operating Temp Range:	-40°F (-40°C) to 140°F (60°C)
-----------------------	-------------------------------

Mechanical Characteristics

Footprint/Type:	Coax
Connector Interface Type:	BNC
Gender:	Male - plug
Connector Series Name:	ProSNS
Color Band:	Black
Locking:	No

Tool Compatibility:	SNSUNI (compression), PS11 (strip)
Termination Type:	Compression
Cable Center Conductor Diameter Limits:	.0634 - .0647 inch
Cable Dielectric Diameter Limits:	.280 - .294 inch
Cable Outer Jacket Diameter Limits:	.390 - .417 inch
Cable Insertion Force:	20 lbf

Standards

RG Type:	11/U Type
Series Type:	Series 11

Applicable Environmental and Other Programs

EU CE Mark:	Yes
-------------	-----

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color
FSNS11HBNC-25	No Color

Patent:	https://www.belden.com/resources/patents
---------	---

Product Notes

Notes:	Salt Fog: Passes 1000 hours ANSI/SCTE 143 2007, RFI Shielding: -85 dB (60% bonded foil)
--------	---

© 2019 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.