

REFERENCE:

PERFORMANCE REQUIREMENTS:

- 1. FIR TREE PUSH IN FORCE: 45 NEWTONS (10 LBS) MAX IN A 6.50mm HOLE AND A PLATE THICKNESS OF 1.8mm.
- 2. FIR TREE PULL OUT FORCE: 110 NEWTONS (25 LBS) MIN IN A 6.50mm HOLE AND A PLATE THICKNESS OF 1.8mm.
- 3. SHEET METAL THICKNESS RANGE: 0.60mm 6.65mm

4. APPLICABLE HOLE SIZE:


A. 6.50mm +0.50/- 0.40

B. 6.35mm +/- 0.25 HEX

5. CABLE TIE MIN LOOP TENSILE STRENGTH: 225 NEWTONS (50 LBS)

6. BUNDLE RANGE: 2.0mm TO 50.0mm

Revision Level		Revision Record	Changed	Date	Approved	Date	
Drawing	State	Part	revision record	Onlangea		прргочес	Bate
09.2	Design Release	D	SEE ECN# 012626	KVH	4/3/14	EJH	4/3/14



T50ROSFT6SO12.5A



Material	Units	millimeters	
SEE CHART			
COLOR: SEE CHART			
	Tolerance defined on each dimension		

ASSEMBLY VIEW

SCALE 1:1

The copyright of this drawing is reserved by HellermannTyton. It is issued on condition that it is not reproduced, copied or disclosed to a third party, either wholly or in part, without the consent of HellermannTyton.

` [Hellermann Won				
	Approved	SJA	3/30/12		
	Drawn	SJA	3/24/11		

PA46

BROWN

North America Email: corp@htamericas.com Web: www.hellermann.tyton.com

	11-0581	Sheet	1/1	
	Drawing-No	PRODUCTION : Phase	Format	AH
Ŋ	FIR TREE (A SERIES)		11-0581	
	Title T50ROS V	WITH 12.5mm OFFSET AND FT6	Project Nur	mber
	Article/Type-No	SEE CHART	Scale	3:4