



Model: A32-V32-100 A32-V32-101

The Cel-Fi Wideband Directional Antenna is an outdoor vertically polarized directional antenna; with 10dB gain in the low bands and 11dB gain in the high bands. The weather resistant housing is built with UV stabilized ABS plastic. Optimized for Cel-Fi products, the Cel-Fi Wideband Directional Antenna can be used with the Cel-Fi WAVE Antenna positioning app. The unit includes standard brackets for mounting, and can also be used with the Cel-Fi Pole Mount.

FEATURES

- · Boosts Cell Signal by up to 11dBi
- 700 2700 MHz Frequency
- Vertical Polarization
- Directional

SPECIFICATIONS

ELECTRIC SPECIFICATION

Frequency Range	698-960 MHz	1710-2700 MHz
Gain	10dBi	11dBi
Horizontal Beamwidth	70°	
Vertical Beamwidth	50°	
F/B Ratio	≥15dB	
VSWR	≤2.0	≤1.5
Input Impedance	50 Ω	
Polarization	Vertical	
Maximum Power	50W	

MECHANICAL SPECIFICATION

Connector Types (A32-V32-100)	SMA male
(A32-V32-101)	N-type female
Cable	2m coax
Dimension	450x210x65mm
Weight	1.1 kg
Operating Temp:	-40°C - 65°C

Copyright © 2018 by Nextivity, Inc, U.S. All rights reserved. The Nextivity and Cel-Fi logos are registered trademarks of Nextivity Inc. All other trademarks or registered trademarks listed belong to their respective owners. Designed by Nextivity in California.

