## SI-IES-111D-LRT

# **Unmanaged Hardened PoE+ Injector/Converter**



(1) 100/1000Base-X SFP Slot + (1) 10/100/1000Base-T PoE+ Port



The SI-IES-111D-LRT is a (2) port unmanaged hardened PoE+ injector that adds up to 30 Watts of power from it's PoE+ Port onto a network segment. The gigabit speed SFP slot provides the ultimate flexibility by allowing fiber SFP uplink ports with varying communication distances.

### **Ordering Information**

#### SI-IES-111D-LRT

(1) 100/1000Base-X SFP slot + (1) 10/100/1000Base-T PoE+ port

Optional Accessories (sold separately)

#### **SFP Modules**

**Industrial Power Supplies:** 

#### 25130

Input: 88-264VAC, 120-370VDC Output: 48-55VDC, 0.83A, 39.8Watts

#### 25131

Input: 88-264VAC, 124-370VDC Output: 48-55VDC, 1.6A, 76.88Watts

### **Features**

- IEEE 802.3at PoE+ to supply 30 Watts on 10/100/1000Base-T port
- Supports IEEE 802.3af
- Supports dual speed for SFP slot
- Non-blocking architecture
- · Compact size
- IP31 housing protection
- Link Pass Through
- Extended operating temperature (-40°C to 75°C)
- DIN Rail mount / optional wall mount brackets included
- Full/half-duplex flow control
- Auto-MDI/MDIX
- Auto-Negotiation
- Store-and-forward transmission
- 10K byte jumbo frames

### **Specifications**

Standards	IEEE 802.3 IEEE 802.3x IEEE 802.3u IEEE 802.3ab IEEE 802.3at IEEE 802.3z IEEE 802.3z
Max Frame Size	10K byte jumbo frames
Connectors	(1) DATA IN SFP Ethernet Port (1) DATA OUT PoE+ RJ-45 Ethernet Port 30 Watts
Status LEDs	Copper Port: Link/ACT Copper Port: Gigabit Transmission SFP Port: Link/ACT PoE Power Input Power
Dimensions	Width: 1.44" [36.7 mm] Depth: 3.72" [94.5 mm] Height: 4.26" [108.4 mm]
Power Consumption	3.53 Watts (No PoE) 32.725 Watts (1 port PoE)
Power Input	48-57VDC Higher Voltage (50-53VDC) may be required for some high powered PD loads
Ingress Protection	IP31
Environment	Operating: -40°C to 75°C Storage: -40°C to 85°C Humidity: 5% to 95% (non-condensing) Altitude: 0 – 10,000 ft.
Weight	1.3 lbs. [0.59 kg]
Compliance	Safety: UL508 Class I, Division 2, Groups A, B, C, and D Hazardous Locations, FCC Class A, CE Mark, EN61000-4, EN61000-6-2, EN61000-4-2 (ESD), EN61000-4-3 (RS), EN61000-4-4 (EFT), EN61000-4-5 (Surge), EN61000-4-6(CS) EN61000-4-8 (Magnetic Field), EN61000-6-4 (EMC), IEC60068-2-27(Shock), IEC60068-2-32 (Free fall), IEC60068-2-6 (Vibration) IEC61850-3
Warranty	Lifetime