SM24TAT2SA Smart Managed Gigabit Ethernet PoE+ Switch

(24) 10/100/1000Base-T Ports + (2) 100/1000Base-X SFP Slots



Features

Server

Syslog

PoE Features

PoE configuration

System (DMS)

Floor view, Map view

and link management

Traffic Monitoring

Auto Power Reset (APR)

Device Management

Graphical Monitoring - Topology view,

Troubleshooting - Network diagnostic,

protection mechanism, performance

•

•

•

IPv6 Access Management

standard/extended ACL

Support Jumbo Frame up to 9K bytes Authentication - RADIUS, TACACS+

DHCP Relay, DHCP Snooping, DHCP

L2/L3/L4 ACLs Support MAC ACL, IP

LLDP (Link Layer Discovery Protocol) IEEE 802.3az Energy Efficiency

IP Source Guard, Port Security

Compliant with IEEE 802.3at PoE+

Compliant with IEEE 802.3af PoE

This switch is a next generation smart managed switch with 52Gbps switching capacity. It provides (24) 10/100/1000Base-T copper ports with IEEE 802.3at PoE+ capability and (2) additional 100/1000 dual speed SFP slots. The embedded Device Management System (DMS) software provides the benefits of ease of use in IP surveillance, Wireless Access Point and other applications. The DMS capability built into the switch provides time-saving features enabling security integrators or network administrators to establish and document a baseline deployment, automatically discover and remotely configure attached IP-powered devices (PDs).

Specifications

Specifications	
Standards	IEEE 802.3 IEEE 802.3u IEEE 802.3z IEEE 802.3ae IEEE 802.3ad IEEE 802.1D IEEE 802.1V IEEE 802.1V IEEE 802.1s IEEE 802.1Q IEEE 802.1p IEEE 802.1ad IEEE 802.3af IEEE 802.3at IEEE 802.3az
Connectors	(24) 10/100/1000 RJ-45 ports (2) 100/1000 SFP slots
Protocols	CSMA/CD
Technology	Store-and-Forward switching architecture
MAC Address	8K MAC address table
Backplane	52 Gbps
Dimensions	Width: 17.4" [442 mm] Depth: 8.3" [211 mm] Height: 1.73" [44 mm]
Power Input	100-240VAC
Power Consumption	438 Watts (full load with PoE)
Power-over-Ethernet	Max PoE budget 370 Watts 30 Watts for (12) ports simultaneously 15.4 Watts for (24) ports simultaneously
Surge Protection	6KV
Environment	Operating: 0°C to +50°C Humidity: 10% to 90% (non-condensing)
Weight	6.6 lbs. [3.0 kg]
Compliance	FCC Class A, CE Safety: IEC60950, UL listed
Warranty	Lifetime



Ordering Information

SM24TAT2SA

(24) 10/100/1000Base-T ports + (2) 100/1000Base-X SFP slots (includes 19" rack mount brackets)

Optional Accessories (sold separately)

SFP Modules

		Power Cord Included
		To order the corresponding country specific power cord, add the extension from the list below to the end of the SKU; Ex: SM24TAT2SA-NA
		-NA = Country Code -NA = North America -LA = Latin America -EU = Europe -UK = United Kingdom -SA = South Africa -JP = Japan -OZ = Australia -BR = Brazil
	So	ftware Features
ports		Management: Web Management, SN V1/V2c/V3, Telnet, CLI
hing architecture		Port Trunk: Supports IEEE 802.3ad port trunk with link aggregation cont protocol (LACP) and static trunk
		Multicast: Support IGMP Snooping V V2, MVR, MLD Snooping V1/V2
PoE)		Quality of Service: Supports 8 hardw queues. Strict priority and WRR, Ingr policer, Egress shaping and per port rate limiting
tts multaneously simultaneously		Spanning Tree: Supports IEEE 802.1 MSTP, IEEE 802.1w RSTP and IEEE 802.1D STP Compliant

- VLAN: Port Based VLAN, IEEE 802.1Q tag-based, up to 4k VLAN entries, QinQ, MAC based VLAN, Private VLAN
- Firmware Update through TFTP and • HTTP

- ent, SNMP
- 2.3ad on control nk
- oping V1/ 12
- hardware RR, Ingress per port
- 802.1s d IFFF

+1.952.941.7600 | www.transition.com | sales@transition.com