

BRADY B-184 ALUMINUM FOIL TAPE

TDS No. B-184
Effective Date: 01/11/2019

Description:

GENERAL

Print Technology: Dot Matrix

Material Type: Dead Soft Aluminum Foil

Finish: Matte

Adhesive: Permanent Acrylic

APPLICATIONS

Dot matrix printable or write-on aluminum foil label. B-184 can also be used as a wiremarker because of its excellent conformability around wire.

RECOMMENDED RIBBONS

Brady Series R2000

Brady Series R5000

REGULATORY APPROVALS

For information on the Weee-RoHS compliance status for a Brady Product go to one of the following websites:

In Canada: www.bradycanada.ca/weee-rohs

In Europe: www.bradyeurope.com/rohs

In Japan: www.brady.co.jp/products/labelsuse/rohs

All other regions: www.bradyid.com/weee-rohs

SPECIAL FEATURES

The aluminum foil used in B-184 is conductive. B-184 has excellent "memory" when wrapped on a wire, and may remain wrapped around a wire or cable even if the adhesive fails.

Details:

PHYSICAL PROPERTIES	TEST METHODS	AVERAGE RESULTS
Thickness	ASTM D 1000 -Topcoat -Substrate (foil) -Adhesive -Total	0.0009 inch (0.023 mm) 0.0026 inch (0.066 mm) 0.0011 inch (0.028 mm) 0.0046 inch (0.116 mm)
Adhesion to: -Stainless Steel	ASTM D 1000 20 minute dwell 24 hour dwell	60 oz/in (66 N/100 mm) 70 oz/in (77 N/100 mm)
-Textured ABS	20 minute dwell 24 hour dwell	20 oz/in (22 N/100 mm) 25 oz/in (27 N/100 mm)
-Polypropylene	20 minute dwell 24 hour dwell	50 oz/in (55 N/100 mm) 55 oz/in (60 N/100 mm)
Tack	ASTM D 2979 Polyken™ Probe Tack 1 second dwell	19 oz (550 g)
Tensile Strength and Elongation	ASTM D 1000	25 lbs/in (438 N/100 mm), 10%
Application Temperature	Lowest application temperature to steel	50°F (10°C)

The following testing is performed with the B-184 printed with the Brady Series R2000 and Brady Series R5000 ribbons. All samples allowed to dwell 24 hours prior to testing.

PERFORMANCE PROPERTIES	TEST METHODS	TYPICAL RESULTS
High Service Temperature	30 days at various temperatures	Very slight label discoloration at 130°C. At higher temperatures up to 160°C label

		is still functional, but discolors to a brownish/gold color.
Low Service Temperature	30 days at -40°F (-40°C)	No visible effect
Humidity Resistance	30 days at 100°F (37°C), 95% R.H.	No visible effect
UV Light Resistance	30 days in UV Sunlighter™ 100	Very slight label discoloration
Weatherability	ASTM G155, Cycle 1 30 days in Xenon Arc Weatherability	Slight Series 2000 and 5000 print fade
Salt Fog Resistance	ASTM B 117 30 days in 5% salt fog solution chamber	Salt precipitated on label surface, label print difficult to read
Abrasion Resistance	Taber Abraser, CS-10 grinding wheels, 500 g/arm (Fed. Std. 191A, Method 5306)	Series 2000 and 5000 print still legible after 600 cycles

PERFORMANCE PROPERTY	CHEMICAL RESISTANCE
-----------------------------	----------------------------

Samples were printed with Brady Series R2000 and Brady Series R5000 ribbons, laminated to aluminum panels, and dwelled 24 hours prior to test. Testing consisted of 5 cycles of 10 minute immersions in the specified chemicals followed by 30 minute recovery periods. After the final immersion the samples were rubbed with cotton swabs. Testing was conducted at room temperature.

CHEMICAL REAGENT	SUBJECTIVE OBSERVATION OF VISUAL CHANGE	
	APPEARANCE OF TAPE	APPEARANCE OF SERIES R2000 AND R5000 PRINT
Methyl Ethyl Ketone	Topcoat turns slightly white; topcoat removed when rubbed.	Print removed when rubbed
1,1,1-Trichloroethane	Topcoat removed when rubbed	Print removed when rubbed
Isopropyl Alcohol	No visible effect	No visible effect
JP-4 Jet Fuel	No visible effect	No visible effect
ASTM Reference Fuel B	No visible effect	No visible effect
SAE 20 WT Oil	No visible effect	No visible effect
Mil-H-5606 Oil	No visible effect	No visible effect
Speedi Kut Cutting Oil 332	No visible effect	No visible effect
Rust Veto® 377	No visible effect	No visible effect
Skydrol® 500B-4	Topcoat softened	Print smear when rubbed
Super Agitene®	No visible effect	No visible effect
Deionized Water	No visible effect	No visible effect
3% Alconox® Detergent	No visible effect	No visible effect
Northwoods™ Buzz Saw Citrus Degreaser	Label edge lift; topcoat degraded	Print removed

Unless reported differently, results were the same for Brady Series R2000 and Brady Series R5000 ribbons.

Shelf life is two years from the date of receipt for this product as long as this product is stored in its original packaging in an environment below 80° F (27° C) and 60% RH. It remains the responsibility of the user to assess the risk of using this product. We encourage customers to develop testing protocols that will qualify a product's fitness for use in their actual application.

Trademarks:

Alconox® is a registered trademark of Alconox Co.
Northwoods™ is a trademark of the Superior Chemical Corporation.
Polyken™ is a trademark of Testing Machines Inc.
Rust Veto® is a registered trademark of the E.F. Houghton & Co.
Skydrol® is a registered trademark of the Monsanto Company
Sunlighter™ is a trademark of the Test Lab Apparatus Company
Super Agitene® is a registered trademark of Graymills Corporation
ASTM: American Society for Testing and Materials (U.S.A.)
SAE: Society of Automotive Engineers (U.S.A.)
All S.I. Units (metric) are mathematically derived from the U.S. Conventional Units.

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2019 Brady Worldwide, Inc. | All Rights Reserved
Material may not be reproduced or distributed in any form without written permission.

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289