



NV-WA40W-RC Remote Control (sold separately)

- 1. Volume:** These buttons increase and decrease the signal output of the amplifier.
- 2. A/B:** This button toggles between the A and B hardwired inputs on the back panel or the individual front panel inputs. Use of the front panel inputs will override those on the back panel.
- 3. Power:** This button turns the amplifier on and off as a toggle function.

NV-WA40W-AMP

Power Amplifier Output

Continuous Average Output Power	40W (20W x 2)
Both channels	1kHz / 1% THD
Rated Distortion (½ power)	0.40%
Rated Impedance	4 Ohms
Frequency Response (20-20kHz)	±2 dB

Source Input

Front	3.5mm Stereo Jack
Input Impedance	20K Ohms
Input Sensitivity for Rated Power	300mV RMS

Back

Variable Input	Screw Terminal
Input Impedance	20K Ohms
Input Sensitivity for Rated Power	300mV RMS
Fixed Input	Screw Terminal
Input Impedance	20K Ohms
Input Sensitivity for Rated Power	300mV RMS

Power Requirements

Power Supply	16VDC
Power Consumption at maximum available output	45W
Power Consumption with music (typical)	10W
Power Consumption no signal	2.1W
Power Consumption standby	0.5W
Auto Shut-off Time	20mins

WA40W-AMP Approvals

CE-EMC (EU), FCC (USA and Canada)

Physical Specifications

Unit Size	50mm x 50mm x 29mm 1.97" x 1.97" x 1.14"
Shipping Size	424mm x 306mm x 395mm 16.7" x 12" x 15.5"
Unit Weight	0.11 Kg / 0.24 lbs
Shipping Weight	7.0 Kg / 15.4 lbs

NV-WA40W-SPK Speaker

Electrical

Power	10 ~50W
Impedance	4 Ohms

Physical Specifications

Unit Size	190mm x 160mm x 90mm 7.5" x 6.3" x 3.54"
Shipping Size	400mm x 350mm x 245mm 15.75" x 13.78" x 9.65"

NV-WA40W-RC Remote Control

(sold separately)

Electrical

IR Frequency	38.7 kHz
Batteries	AAA x 2

Physical Specifications

Unit Size	110mm x 42mm x 14mm 4.33" x 1.65" x 0.55"
Shipping Size	296mm x 245mm x 280mm 11.65" x 9.65" x 11"

NuVo reserves the right to change specifications without notice.