

# L-PJM10A

## Unidirectional Projection Loudspeaker

### FEATURES

- Intelligible voice and superior sound reproduction
- Ceiling or wall mount installation
- Meets virtually any indoor and outdoor requirement
- Complies with IP65 standard
- Complies with international safety laws



### PRODUCT DESCRIPTION


L-PJM10A is a high-performance 10W public address unidirectional projection loudspeaker. It provides a broad frequency response range, low distortion and high sound pressure level for accurate and intelligible broadcast of evacuation messages and high quality sound reproduction. It can be used in indoor, outdoor, dry, or wet applications, providing reliable operations over wide temperature and humidity ranges. Its low-profile, white color design blends easily with most interiors in locations such as hotels, conference rooms, cinemas, theme parks, factories and exhibitions.

In case of a fire emergency, its aluminum enclosure and high-temperature ceramic wiring connector protect the speaker's internal components from the increased heat often present in fire conditions, extending its ability to remain operational and broadcast important information during a fire emergency. In addition, the loudspeaker's front cover and bracket are also made of aluminum, making them durable and corrosion proof. The loudspeaker is also supplied with a temperature fuse that protects it from overheating due to improper loading.


### TECHNICAL SPECIFICATIONS

| Model                           | L-PJM10A                                                 |
|---------------------------------|----------------------------------------------------------|
| Max power                       | 20 W                                                     |
| Rated power                     | 10 W                                                     |
| Power taps @ 100V               | 10 W / 5 W / 2.5 W / 1.25 W                              |
| SPL at 10 W / 1 W (2 KHz , 1m)  | 100 dB / 91 dB                                           |
| Frequency response(-10 dB)      | 150 Hz -15 KHz                                           |
| Dispersion angle(1 KHz / -6 dB) | 180°                                                     |
| Rated input voltage             | 100 V / 70 V                                             |
| Rated impedance                 | 1 K $\Omega$ / 2K $\Omega$ / 4 K $\Omega$ / 8 K $\Omega$ |
| Connector                       | Fire-resistant cable                                     |
| Dimensions                      | $\Phi$ 140 × 195 mm                                      |
| Weight                          | 2.62 Kg                                                  |
| Color                           | White( RAL9003 )                                         |
| Speaker size                    | 5.25"                                                    |
| Operating temperature           | -25 °C to +55 °C                                         |
| Storage temperature             | -40 °C to +70 °C                                         |
| Relative humidity               | < 95 %                                                   |


## FREQUENCY RESPONSE




## CIRCUIT DIAGRAM



## POLAR DIAGRAM



## THREE-VIEW DIAGRAM



## Honeywell Audiovisuals

No. 257, Junye Road  
Guangzhou GETDD East  
510530 China  
Tel: +86 20 2839 9600  
Fax: +86 20 2820 8706  
www.honeywellav.com

1020905011\_EN2.3  
Nov 2012  
© 2012 Honeywell International Inc.

**Honeywell**