EPMU-05(-S) EPMU-06(-S) EPMU-07(-S) EPMU-08(-S)



FEATURES

- Wind rated up to 110 mph, elevation 200ft (60m), Category "D" when fixed tilt mechanism in engaged
- Designed specifically for outdoor use and constructed from weatherproof materials
- Tilt settings ot 0°, 2°, 5°, 10° or 15°, for the perfect viewing angle
- Swivel feature allows for the display to face the necessary direction without adjusting the pedestal
- 8ft column meets ADA requirements

Wind Rated Pedestal Tilt Mount for 32" to 65" Outdoor Flat Panel Displays

Outdoor TVs are taking entertainment to new places, and the Peerless-AV Wind Rated Outdoor Pedestal Mount provides a sure way to make outdoor flat panels secure in all conditions. It's made of heavy gage steel with a corrosion resistant E-Coat and stainless steel hardware so it can handle the elements.





peerless-AV

Model Numbers

EPMU-05(-S):5' Wind Rated Pedestal Tilt Mount for 32" to 65" Outdoor Flat Panel DisplaysEPMU-06(-S):6' Wind Rated Pedestal Tilt Mount for 32" to 65" Outdoor Flat Panel DisplaysEPMU-07(-S):7' Wind Rated Pedestal Tilt Mount for 32" to 65" Outdoor Flat Panel DisplaysEPMU-08(-S):8' Wind Rated Pedestal Tilt Mount for 32" to 65" Outdoor Flat Panel Displays

Product Specifications

DIMENSIONS (W × H × D)			PRODUCT WEIGHT	LOAD CAPACITY	FINISH	AVAILABLE COLORS	
EPMU-05(-S) EPMU-06(-S) EPMU-07(-S) EPMU-08(-S)	101.51" x 30.75" x 15"	(1969 x 781 x 381mm) (2274 x 781 x 381mm) (2578 x 781 x 381mm) (2883 x 781 x 381mm)	118lb (53.6kg) 128lb (58kg) 138lb (62.7kg) 148lb (67kg)	200lb (91kg)	Powder coat	EPMU models: Black EPMU-S models: Stone Gray	

Package Specifications


	PACKAGE SIZE (W x H x D)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE	PACKAGE CONTENTS	UNITS IN PACKAGE
EPMU-05 EPMU-05-S EPMU-06 EPMU-06-S EPMU-07 EPMU-07-S EPMU-08 EPMU-08-S	65" x 18" x 16" (1651 x 457 x 406mm) 65" x 18" x 16" (1651 x 457 x 406mm) 65" x 18" x 16" (1651 x 457 x 406mm) 65" x 18" x 16" (1651 x 457 x 406mm) 65" x 18" x 16" (1651 x 457 x 406mm) 77" x 18" x 16" (1955 x 457 x 406mm) 77" x 18" x 16" (1955 x 457 x 406mm) 89" x 18" x 16" (2260 x 457 x 406mm) 89" x 18" x 16" (2260 x 457 x 406mm)	120lb (54kg) 120lb (54kg) 130lb (58kg) 130lb (58kg) 140lb (63kg) 140lb (63kg) 150lb (68kg) 150lb (68kg)	735029272397 735029272434 735029272403 735029272441 735029272410 735029272458 735029272458 735029272427 735029272465	Mount, hardware, concrete fasteners, security fasteners	1

NOTE:

Each product is shipped in 2 separate boxes.

1 box is the same size containing the plate and vertical adapter brackets while the pedestal is shipped in a different sized box.

Pedestal boxes are listed above. The wall plate w/vertical brackets box - 34.25" x 10.18" x 3.12" (870 x 258 x 79mm) Product ships via fright on a dedicated skid.



ARCHITECTS SPECIFICATIONS

The Wind Rated Tilt Pedestal Mount for Outdoor Flat Panel Displays shall be a Peerless-AV model number EPMU% and located where indicated on the plans. Assembly and installation shall be done according to instructions provided by the manufacturer. Mount is made of heavy gauge cold rolled steel. Mount is finished with textured black or gloss ASA-70 gray protective paint.

Peerless Industries, Inc. 2300 White Oak Circle Aurora, IL 60502 (800) 865-2112 (630) 375-5100 Fax: (800) 359-6500 www.peerless-av.com

Visit www.peerless-av.com to see the complete line of AV solutions from Peerless-AV, including flat panel mounts, projector mounts, carts/stands, furniture, cables, screen cleaners and a full assortment of accessories.

peerless-AV