

AXIS Q1645-LE Network Camera

High-speed video with 1/2" sensor and OptimizedIR

With AXIS Q1645-LE Network Camera it's easier than ever to capture details even in challenging lighting or low light. With a 1/2" sensor and i-CS lens, AXIS Q1645-LE ensures high-resolution images at up to 120 fps and provides superior light sensitivity with Forensic WDR and Lightfinder. The robust aluminum housing resists extreme temperatures, and comes with built-in IR LED illumination for surveillance in complete darkness. AXIS Q1645-LE enables proactive surveillance with pre-installed AXIS Guard Suite and orientation aid for quick orientation with multiple monitors. Zipstream optimizes the video stream to maintain high video quality while saving bandwidth and storage.

- > **2 MP resolution at up to 100/120 fps**
- > **1/2" sensor**
- > **Forensic WDR and Lightfinder**
- > **Electronic image stabilization (EIS)**
- > **AXIS Motion Guard, AXIS Fence Guard and AXIS Loitering Guard**



AXIS Q1645-LE Network Camera

Camera	
Image sensor	1/2" progressive scan RGB CMOS
Lens	Vari-focal, IR corrected, CS-mount 3.9–10.0 mm, F1.5 2 MP (16:9): Horizontal field of view: 92°–42° Vertical field of view: 50°–23° i-CS lens
Day and night	Automatically removable infrared-cut filter
Minimum illumination	1080p 25/30 fps with WDR and Lightfinder: Color: 0.05 lux, at 50 IRE F1.5, B/W: 0.01 lux, at 50 IRE F1.5 1080p 50/60 fps with WDR and Lightfinder: Color: 0.1 lux, at 50 IRE F1.5, B/W: 0.02 lux, at 50 IRE F1.5 1080p 100/120 fps: Color: 0.2 lux, at 50 IRE F1.5, B/W: 0.04 lux, at 50 IRE F1.5 1080p 25/30 fps with WDR and Lightfinder: Color: 0.02 lux, at 50 IRE F0.9, B/W: 0.004 lux, at 50 IRE F0.9
Shutter time	1/100000 to 2 s
Pan/Tilt/Zoom	Digital PTZ, uploadable PTZ driver (Pelco D pre-installed)
Video	
Video compression	H.264 (MPEG-4 Part 10/AVC), Main, Baseline and High Profile Motion JPEG
Resolution	1920x1080 to 320x180
Frame rate	HDTV 1080p (1920x1080) with WDR: Up to 50/60 fps with power line frequency 50/60 Hz HDTV 1080p (1920x1080) without WDR: Up to 100/120 fps with power line frequency 50/60 Hz
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Axis Zipstream technology in H.264 Controllable frame rate and bandwidth VBR/ABR/MBR H.264
Image settings	Saturation, contrast, brightness, sharpness, Forensic WDR – 120 dB, white balance, day/night threshold, exposure mode, exposure zones, compression, orientation: auto, 0°, 90°, 180°, 270°, mirroring of images, dynamic text overlay, image overlay, privacy masks, defogging, noise reduction, electronic image stabilization, barrel distortion correction, orientation aid, fine tuning of behavior at low light Scene profiles: forensic, vivid, traffic overview, backlit entrance
Audio	
Audio streaming	Two-way
Audio compression	AAC-LC 8/16/32/48 kHz, G.711 PCM 8 kHz, G.726 ADPCM 8 kHz, Opus 8/16/48 kHz Configurable bit rate
Audio input/output	External balanced/unbalanced microphone or line input, line output 24 bit AD/DA-conversion
Network	
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1x (EAP-TLS) ^a network access control, digest authentication, user access log, centralized certificate management, brute force delay protection, signed firmware
Supported protocols	IPv4, IPv6 USGv6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMPv1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SFTP, SRTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH, LLDP, CDP.
System integration	
Application Programming Interface	Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform; specifications at axis.com AXIS Guardian with One-Click Connection ONVIF Profile G, ONVIF Profile S, and ONVIF Profile T, specifications at onvif.org
Analytics	Included AXIS Video Motion Detection, AXIS Fence Guard, AXIS Motion Guard, AXIS Loitering Guard, active tampering alarm, audio detection Supported AXIS Digital Autotracking, AXIS Perimeter Defender

	Support for AXIS Camera Application Platform enabling installation of third-party applications, see axis.com/acap
Event triggers	Analytics, external input, edge storage events Detectors: live stream accessed, video motion detection, audio detection, shock detection Hardware: network, temperature Input Signal: manual trigger, virtual inputs PTZ: error, moving, preset reached, ready Storage: disruption, recording System: system ready Time: recurrence, use schedule
Event actions	File upload: FTP, SFTP, HTTP, HTTPS, network share and email, send video clip Notification: email, HTTP, HTTPS and TCP Overlay text, Send SNMP Trap Video and audio recording to edge storage Pre- and post-alarm video buffering External output activation, day/night vision mode, play audio clip, status LED, WDR mode, defog mode, PTZ control
Data streaming	Event data
Built-in installation aids	i-CS: Remote zoom and focus Other lens: Remote back focus Traffic wizard, pixel counter, levelling assistant, autorotation
General	
Casing	IP66-, IP67-, NEMA 4X- and IK10-rated Metal (Aluminium) Color front: Black - NCS S 9000-N Color chassis: White - NCS S 1002-B
Sustainability	PVC free
Memory	1 GB RAM, 512 MB Flash
Power	Power over Ethernet (PoE) IEEE 802.3at Type 2 Class 4 Typical 12.3 W, max 25.5 W
Connectors	Shielded RJ45 10BASE-T/100BASE-TX PoE I/O: 6-pin 2.5 mm terminal block for four configurable inputs/outputs (12 V DC output, max load 50 mA) RS485/RS422, 2 pcs, 2 pos, full duplex, terminal block 3.5 mm mic/line in, 3.5 mm line out i-CS connector (compatible with P-Iris and DC-iris)
IR illumination	Optimized IR with power-efficient, long-life 850 nm IR LEDs Range of reach 30 m (98 ft) or more depending on the scene
Storage	Support for microSD/microSDHC/microSDXC card Support for SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see axis.com
Operating conditions	Arctic temperature control: Start-up at -40 °C to 60 °C (-40 °F to 140 °F) Humidity 10–100% RH (condensing)
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F) Humidity 5–95% RH (non-condensing)
Approvals	EMC EN 55032 Class A, EN 61000-3-2, EN 61000-3-3, EN 50121-4, IEC 62236-4, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, RCM AS/NZS CISPR 32 Class A Safety IEC/EN/UL 60950-22, IEC/EN/UL 62368-1, IS 13252 Environment IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-27, IEC 60068-2-78, IEC/EN 60529 IP66/67, IEC/EN 62262 IK10, NEMA 250 Type 4X Network/NIST SP500-267 Other IEC 62471
Dimensions	178 x 206 x 494 mm (7 x 8.11 x 19.45 in)
Weight	6350 g (13.2 lb)
Included accessories	AXIS T94Q01A Wall Mount, AXIS T92G20 Outdoor Housing, connector kit, resistor ^x T20 tool, installation guide, Windows [®] decoder 1-user license

Optional accessories	AXIS T90B Illuminators, Axis network cable couplers, AXIS T8129 PoE Extender, AXIS T8415 Wireless Installation Tool, Axis midspans For more accessories, see axis.com	Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see axis.com/warranty
Video management software	AXIS Companion, AXIS Camera Station, video management software from Axis Application Development Partners available at axis.com/vms	a.	<i>This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (openssl.org), and cryptographic software written by Eric Young (ey@cryptsoft.com).</i>
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese	Environmental responsibility:	axis.com/environmental-responsibility